

COOPER LIGHTING - METALUX®

DESCRIPTION

The F-Bay I5 series is an outstanding solution for high mounting height industrial or retail applications. The F-Bay I5 optic has been optimized to provide maximum performance from T5 lamps. Optional uplight component is provided to enable excellent ceiling uniformity. The I5's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to H.I.D. The primary benefits include exceptional color rendering, high system efficacy, 95% lumen maintenance, long lamp life, instant on/instant re-strike, economical dimming, and uniform brightness control. Primary applications include "big box" retail, shopping malls, light industrial, school gymnasiums, etc.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

A... Construction

Specification grade full body housing, end plates and socket tracks are die formed cold rolled steel in 4' or 8' lengths. The housing features an integral ballast channel that adds strength and provides numerous KO's for easy installation.

B... Electrical

Class "P" ballasts are positively secured by mounting bolts. Rotor-lock Bi-Pin lampholders and optional top ballast access plate enables service from above without disturbing the internal optics. Optional modular power receptacle meets UL2459 and NEC 410.73 and is UL/cUL rated for make and break under load from outside the luminaire to speed maintenance. UL/cUL listed. Suitable for damp locations.

C... Finish

Electrostatically applied baked white enamel finish is preceded by a multistage cleaning cycle, iron phosphate coating with rust inhibitor.

D... Downlight/Uplight Optics


Optical modules are fully enclosed inside housing to protect against damage. Die formed reflectors are faceted for efficiency and control with two optical distributions – medium and wide. Medium beam optical modules utilize 95% specular aluminum finish. Open downlight design optimizes performance with uplight slots available as an option for nominal 8% uplight component. An optional attractive thin blade white baffle adds longitudinal shielding. A clear or frosted white acrylic lens is also available. Optional heavy duty wireguard can be used with or without the lens or baffle. Latched retention of shielding options (safety leader restraints) allows for easy access.

Mounting

The I5 series is suited for surface, suspension mounting with optional wire hook and chain set, stem or cable mounting. Top connector box mounting is also available. Narrow 11" housing allows mounting within 12" horizontally from the nearest edge of the sprinkler deflector.

Options


Integral Occupancy Sensor available and provides from 600 sq. ft. (MS) up to 1250 sq. ft. (MSO) of coverage at a maximum mounting height of 40'.





F-BAY I5 Series

4' OR 8'
4 LAMPS


T5 Linear Fluorescent Hi-Bay Lighting System



MOUNTING DATA



LAMP CONFIGURATIONS



ENERGY DATA

Input Watts:
EB Ballast & T5HO Lamps
454T5 = (229)
8T454T5 = (458)

Luminaire Efficacy Rating
LER =68
Catalog Number: I5-454T5-TBW-UPL

Yearly Cost of 1000 lumens,
3000 hrs at .08 KWH = \$3.85

* Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements

** Consult Pre Sales Technical Support.


LAMPS CONTAIN MERCURY. DISPOSE ACCORDING TO LOCAL, STATE OR FEDERAL LAWS

LINEAR DISCONNECT

Safe and convenient means of disconnecting power.




PHOTOMETRICS



I5-454T5-UPL
 (2) Electronic Ballasts
 (4) 54W T5
 F54T5/HO/830K
 lamps
 4400 lumens
 Spacing criterion:
 (H) 1.2 x mounting
 height, (L) 0.8 x
 mounting height
 Efficiency 92.8%
 Test Report:
 I5454AUPL.IES
 LER =70
 Yearly Cost of 1000
 lumens, 3000 hrs at
 .08 KWH = \$3.45

Candela			
Angle	Along H	45°	Across L
0	8392	8392	8392
5	8348	8244	8150
10	8231	7831	7487
15	8038	7212	6631
20	7762	6489	5624
25	7411	5650	4689
30	6983	4770	4058
35	6487	4035	3518
40	5921	3458	2857
45	5294	2916	2228
50	4615	2286	1855
55	3903	1712	1654
60	3164	1365	1601
65	2417	1170	1530
70	1682	1074	1411
75	1026	937	986
80	488	548	347
85	118	30	5
90	1	10	3



I5-454T5-TBW-UPL
 (2) Electronic Ballasts
 (4) 54W T5
 F54T5/HO/830K
 lamps
 4400 lumens
 Spacing criterion:
 (H) 1.1 x mounting
 height, (L) 0.9 x
 mounting height
 Efficiency 81.2%
 Test Report:
 I5A454TBWUPL.IES
 LER =62
 Yearly Cost of 1000
 lumens, 3000 hrs at
 .08 KWH = \$3.85

Candela			
Angle	Along H	45°	Across L
0	7562	7562	7562
5	7465	7452	7411
10	7230	7114	6951
15	6889	6569	6303
20	6466	5897	5444
25	5973	5139	4547
30	5414	4336	3953
35	4818	3643	3436
40	4196	3110	2848
45	3544	2630	2195
50	2882	2122	1799
55	2235	1637	1609
60	1612	1339	1588
65	1046	1086	1516
70	671	874	1335
75	465	650	927
80	281	387	301
85	121	195	42
90	1	90	21

Coefficients of Utilization

rc	Effective floor cavity reflectance 20%																	
	80%			70%			50%			30%			10%			0%		
	70	50	30	70	50	30	70	50	30	70	50	30	70	50	30	0		
0	109	109	109	109	106	106	106	106	100	100	100	94	94	94	89	89	89	86
1	101	97	94	91	98	95	92	89	90	87	85	85	83	81	81	79	78	76
2	93	87	81	77	90	85	80	75	80	76	73	76	73	70	73	70	68	66
3	86	78	71	66	84	76	70	65	72	67	63	69	65	61	66	63	60	58
4	80	70	63	57	77	68	62	57	65	60	55	63	58	54	60	56	53	50
5	73	63	55	50	71	61	54	49	59	53	48	56	51	47	54	50	46	44
6	68	57	49	44	66	56	49	44	54	47	43	51	46	42	49	45	41	39
7	63	52	44	39	61	51	44	39	49	43	38	47	41	37	45	40	37	35
8	59	47	40	34	57	46	39	34	44	38	34	43	37	33	41	36	33	31
9	54	43	35	30	53	42	35	30	40	34	30	39	33	29	37	32	29	27
10	51	39	32	27	49	38	32	27	37	31	27	36	30	26	34	29	26	24

Coefficients of Utilization

rc	Effective floor cavity reflectance 20%																	
	80%			70%			50%			30%			10%			0%		
	70	50	30	70	50	30	70	50	30	70	50	30	70	50	30	0		
0	95	95	95	95	92	92	92	92	87	87	87	82	82	82	77	77	77	75
1	88	85	82	80	85	83	80	78	78	76	74	74	72	71	70	69	67	65
2	82	76	71	67	79	74	70	66	70	67	63	66	64	61	63	61	59	57
3	75	68	63	58	73	66	61	57	63	59	55	60	57	54	57	54	52	50
4	70	61	55	50	68	60	54	50	57	52	48	55	51	47	52	49	46	44
5	64	55	49	44	62	54	48	43	52	46	42	49	45	41	47	43	40	39
6	60	50	44	39	58	49	43	39	47	42	38	45	40	37	43	39	36	35
7	56	46	39	35	54	45	39	34	43	38	34	41	37	33	40	36	32	31
8	52	41	35	31	50	41	35	30	39	34	30	38	33	29	36	32	29	27
9	48	38	31	27	46	37	31	27	36	30	26	34	29	26	33	29	26	24
10	45	35	28	24	43	34	28	24	33	27	24	32	27	23	30	26	23	22

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	5508	31.3	33.7
0-40	8329	47.3	51.0
0-60	12731	72.3	78.0
0-90	15217	86.5	93.2
0-180	16330	92.8	100.0

Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture
0-30	4945	28.1	34.6
0-40	7390	42.0	51.7
0-60	11071	62.9	77.5
0-90	13159	74.8	92.1
0-180	14293	81.2	100.0

Modular F-Bay Power Supply Option

Cooper Lighting's F-Bay Modular Power Supply is standard on all F-Bay products. The modular power supply allows external fixture access for safe and easy servicing. There is no need to remove lamps or reflectors to disconnect fixture power with F-Bay Modular Power Supply. Access to the individual fixture's power supply allows servicing without turning off all the fixtures disrupting occupants. F-Bay Modular Power Supply is a time saver in installation – **simply plug & power.**



1. Modular Power Supply Receptacle supplied mounted into fixture Access Plate
2. Modular Power Cord & Plugs in 120, 277, 347, & 480V configurations for easy plug & power into existing supply

No internal fixture access required for installation or disconnecting power

Modular Motion Sensor Option supplied with Mounting Box and Modular Power Supply Receptacle

Code Compliance

- UL/cUL Certified for Make/Break under load (UL2549)
- Meets NEC requirements for ballast disconnect (NEC 410.73G)
- Allows for addition of Occupancy Sensor without hard connections
- Receptacles complete with insulating/dust cap

ORDERING INFORMATION

SAMPLE NUMBER: 8T15-454T5-TBW-UNV-EBT2-UPL-U

<p>Length Blank=4' Length 8T=8' Length</p> <p>Series I5=T5 Industrial</p> <p>Mounting Arrangement Blank=Stand Alone R=Continuous Row Mount</p> <p>No. of Lamps 4=4 Lamps</p> <p>Lamp Type 28T5=28W T5 Std (4') Lamps 49T5=49W T5HO (4') Lamps 51T5=51W T5HO (4') Lamps 54T5=54W T5HO (4') Lamps</p> <p>Distribution Optic Blank=Medium (Specular Aluminum) G=Wide (High Reflectance White)</p> <p>Shielding Options Blank=Open TBW=Thin White Baffle FL=Frosted Acrylic Lens & Frame⁽²⁾ CL=Clear Acrylic Lens & Door Frame ASY= Asymmetric Directional Louver⁽²⁾ WG=Heavy Duty Wireguard</p>	<p>Voltage⁽³⁾ UNV=Universal 120/277 Voltage UNC=Universal 347/480 Voltage⁽⁷⁾ 120V=120 Volt 277V=277 Volt 347V=347 Volt 480V=480 Volt</p> <p>Options I5 Lamps Installed L5830=T5 Lamp, 85CRI 3000K L5835=T5 Lamp, 85CRI 3500K L5841=T5 Lamp, 85CRI 4100K L5850=T5 Lamp, 85CRI 5000K GL=Single Element Fuse GM=Double Element Fuse EL=Emergency Installed⁽³⁾</p>	<p>Ballast Type T5 Systems EBT =T5 or T5HO Linear Electronic Program Rapid Start. Total Harmonic Distortion < 10%⁽⁴⁾ No. of Ballast 1, 2 or 3 EHT =T5HO Linear Electronic Start High Ambient. Total Harmonic Distortion < 10%⁽⁷⁾⁽⁸⁾ No. of Ballast 1, 2 or 3</p> <p>DIM=Dimming (ballast must be specified)</p>	<p>Options NUA=No Uplight Apertures In Housing (Cannot be combined w/UPL) UPL=Uplight Apertures PI/CPI=Plug-In (1, 2 or 3) TILW=Tandem Inline Wiring MWS=Modular Wiring System⁽¹²⁾ MS=360° or 180° Motion Sensor, 120 through 347, or 480V⁽¹¹⁾ MP=Modular Power Receptacle (Used for all Cord or Cord and Plug options)^{(1), (13)} TAP=Top Access Plate⁽⁹⁾ TCBP=Top Connector Box Plate⁽⁶⁾</p> <p>Accessories (order separately) I5/I8-TCB-KIT-NO-PLATE-U=Top Connector Box only I5/I8-TCB-KIT=Top Connector Box Kit w/TCBP RH-1=Retrofit Hanger FH-1=Fixture Hook FL-1=Fixture Loop SHK=Hook w/ Safety Screw AYC-CHAIN/SET/U=(2) Hooks, 36" Chain Sets w/S-Hooks⁽¹⁰⁾ TOGGLE=Single Toggle, #2 Cable (Specify 10' or 30') LOOP=Loop Hanger, #2 Cable (Specify 10' or 30') MC6=6' Modular Power Cord MPC6=6' Modular Power Cord & Plug (Specify Voltage) MMS=360° or 180° Aisle Motion Sensor with Modular Power Receptacle (120-277V)⁽¹⁾ MDS6=6' Modular Power Cord with MWS 27DS18/2G06MP Connector⁽¹³⁾</p> <p>Door Frames (for Field Installation) I5-FRM/LENS=Frosted Acrylic Lens & Frame (I5) I5-FRM/CL PK=Clear Acrylic Lens & Frame (I5) WG/I5-4FT-B=Heavy Duty Wireguard (I5) 90800PPK=Thin White Blade Baffle (I5) 90801PPK=Asymmetrical Directional Louver (I5)</p>	<p>Packaging U=Unit Pack PAL=Palletized Out of Carton PALC=Palletized In Carton</p>
---	---	--	--	--

NOTES: ⁽¹⁾Requires use of MC_ or MPC_cord accessories, specify voltage for plugs. ⁽²⁾Use with wide distribution optic only. ⁽³⁾Voltage must be specified when ordered with plugs, motion sensor or emergency ballasts. ⁽⁴⁾EBT ballast systems suitable for operation in ambient environments up to 104°F (40°C). ⁽⁵⁾ER8 and EB8 ballast systems suitable for operation in ambient environments up to 122°F (50°C) in open upright configurations. ⁽⁶⁾For use with Top Connector Box options. See accessories. ⁽⁷⁾2 lamp ballast configurations only in T5 UNC versions. 2/3 lamp ballast configurations in EB/PLUS only for T8 UNC. ⁽⁸⁾EHT ballast systems suitable for ambient environments not to exceed 149°F (65°C) in open upright configurations and less lens option. ⁽⁹⁾TAP option available with a maximum of two ballasts, including EM battery pack. ⁽¹⁰⁾Not for use in gymnasiums or similar recreational facilities. ⁽¹¹⁾When ordering MS option, specify UNV (for 120 or 277V), 347 or 480V. ⁽¹²⁾Cannot be combined with Modular Power Receptacle (MP). ⁽¹³⁾For MWS with MP, choose MP in fixture logic and then choose MWS accessory such as MDS6.

STOCK CATALOG ITEMS

I5455=4 lamp, 54W T5HO, Program Rapid Start Ballast, Top Connector Plate, Uplight, 850 Lamps Installed⁽⁷⁾

SHIPPING INFORMATION

Catalog No.	Wt.
I5-454T5-TBW-UPL	15 lbs.
8T15-454T5-TBW-UPL	30 lbs.

PI OPTION ORDERING INFORMATION

Catalog Number Suffix	Number of Circuits	Circuit Wired To Ballast
PI 1 BLK	1	Black
PI 2 BLU	2	Blue
PI 2 BLK	2	Black
PI 3 RED	3	Red
PI 3 BLU	3	Blue
PI 3 BLK	3	Black

Catalog Numbering System


The PI System is available in sections up to 8' in length for continuous row wiring by simply plugging the sections together. Each PI section is factory wired to the ballast leads. Color coding of wires is as follows:

- PI-1 = One Circuit - 2 Wires: one black, one white
- PI-2 = Two Circuits - 3 Wires: one black, one blue, one white
- PI-3 = Three Circuits - 4 wires: one black, one blue, one red, one white

When ordering the PI2/PI3 System it is necessary to specify the number of fixtures required for each circuit. Each circuit in fixture must be ordered as a separate line item, with a different hot wire color specified. All wiring to external feeds, using cord or cord & plug, are responsibility of installing licensed contractor. Cord and cord & plug sets must be ordered separately if PI option is chosen.

PI1 - Single Circuit Plug-In


SAMPLE NUMBER: PI1BLK-WG



For complete product data, reference the Fluorescent Specification binder. Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Representative for availability and ordering information.

PI2 - Two Circuit Plug-In

SAMPLE NUMBER: PI2BLK-WG



PI3 - Three Circuit Plug-In

SAMPLE NUMBER: PI3BLK-WG

