



# APX/APXH Thermoplastic LED Exit



APX



APXH

The APX series is a fully code compliant, thermoplastic LED solution for exit needs. The series has universal mounting flexibility (ceiling, wall, end), has field selectable red or green letters, single or double-sided faces and directional chevrons. Options include a white or black housing and remote capacity that can power the APWR LED remote series.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Red/green selectable letters; single or double-sided; universal mount	Ease of ordering & installation
Optional remote capacity to drive	Design flexibility; labor and material savings

Certification/Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty



**T20** Certified to California Title 20 Appliance Database



## Ordering Information

SAMPLE NUMBER: APX7RG, APX6RG, APX7RGBK, APX6RGBK

Series	Battery	Face Options	Letter Colors	Housing Color	
<b>APX</b> = All-Pro exit	<b>6</b> = no battery (AC only) <b>7</b> = nickel cadmium battery	<b>_</b> = Universal	<b>RG</b> = selectable red or green	<b>_</b> = white <b>BK</b> = black	


SAMPLE NUMBER: APXH7RG2, APXH7RG2BK

Series	Battery	Face Options	Letter Colors	Remote Heads Powered	Housing Color
<b>APXH</b> = All-Pro exit w/remote capacity	<b>7</b> = nickel cadmium battery	<b>_</b> = Universal	<b>RG</b> = selectable red or green	<b>2</b> = two 3.6 V LED heads	<b>_</b> = white <b>BK</b> = black


Series	Remote Heads Powered	Housing Color
<b>APWR</b> = All-Pro emergency remote	<b>1</b> = one LED head <b>2</b> = two LED heads	<b>_</b> = White <b>BK</b> = Black

## Spacing


### APXH7RG2



### APXRG Series



### APXH7RG2 Series





# APC/APCH Thermoplastic LED Exit



Red/Green Selectable coming soon



The APC series is a fully code compliant, thermoplastic LED solution for exit and emergency needs. The series has universal mounting flexibility (ceiling, wall, end), has field selectable red or green letters, single or double-sided faces and directional chevrons. The LED emergency heads can be side or top mounted and will run for a minimum of 90 minutes. Options include a white or black housing and remote capacity that can power the APWR LED remote series.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Red/green selectable letters; single or double-sided; universal mount	Ease of ordering & installation
Optional remote capacity to drive 2 or 4 LED heads	Up to 34 feet of indoor/outdoor egress coverage

Certification/Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty



**T20** Certified to California Title 20 Appliance Database



## Ordering Information

SAMPLE NUMBER: APC7RG, APCH7RG, APC7RGBK, APCH7RGBK



Series	Remote Heads Powered	Battery	Face Options	Letter Colors	Housing Color
<b>APC</b> = All-Pro exit/emergency combo	<b>_</b> = no remote heads <b>H</b> = two 3.6 V LED heads	<b>7</b> = nickel cadmium battery	<b>_</b> = Universal	<b>RG</b> = selectable red or green	<b>_</b> = white <b>BK</b> = black

Series	Remote Heads Powered	Housing Color
<b>APWR</b> = All-Pro emergency remote	<b>1</b> = one LED head <b>2</b> = two LED heads	<b>_</b> = White <b>BK</b> = Black

## Spacing

APC

APC with remote  
(Remote not included)



# APC7RGSQ30



The APC series is a fully code compliant, thermoplastic LED solution for exit and emergency needs. **Updated LED optics provide up to 30 feet egress coverage.** The series has universal mounting flexibility (ceiling, wall, end), has field selectable red or green letters, single or double-sided faces and directional chevrons. The LED emergency heads and EXIT sign will run for a minimum of 90 minutes. Options include a remote capacity model that can power the APWR LED remote series.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Red/green selectable letters; single or double-sided; universal mount	Ease of ordering & installation
Optional remote capacity to drive 2 or 4 LED heads	Up to 47 feet of indoor/outdoor egress coverage

Certification/Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty


**T20** Certified to California Title 20 Appliance Database

## Ordering Information

SAMPLE NUMBER: APC7RGSQ30, APCH7RGSQ30					
Series	Remote Heads Powered	Battery	Face Options	Letter Colors	Housing Color
APC	_ = No Remote Heads H = Two 3.6V LED Heads	7 = nickel cadmium	_ = Universal	RG = Field Selectable Red or Green	_ = white

Head Type	Catalog Numbers
SQ30= Square head with 30' of egress	APC7RGSQ30, APCH7RGSQ30

## Spacing



# APELMINI Polycarbonate LED Emergency



APELMINI



The APELMINI is a fully code compliant, compact 5-1/4" x 4-3/4" polycarbonate LED emergency light. The LED emergency heads will run for a minimum of 90 minutes. It has an improved design to reduce installation time with a universal j-box mounting pattern, 3 conduit entry points and snap fit housing construction.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Adjustable heads	Design flexibility
Compact design: 5-1/4" x 4-3/4"	Better design aesthetics
Junction box mount and 3 conduit entry points	Multiple installation options

Certification/Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty



**T20** Certified to California Title 20 Appliance Database





## Ordering Information

SAMPLE NUMBER: APELMINI


Series	Size	Housing Color
APEL = All-Pro emergency light	MINI = J-box size	- = White

## Spacing

APELMINI



# APEL/APELH2 Polycarbonate LED Emergency



APEL



APELH2

The APEL series is a fully code compliant, polycarbonate LED solution for emergency needs. The LED emergency heads will run for a minimum of 90 minutes. The universal j-box mounting pattern and snap fit housing construction significantly reduce installation time. Options include a white or black housing and remote capacity that can power the APWR LED remote series.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Adjustable heads	Design flexibility
Optional remote capacity to drive 2 LED heads	Up to 34 feet of indoor/outdoor egress coverage


Certification/Warranty
UL 924 damp location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty





## Ordering Information

SAMPLE NUMBER: APEL, APELH2, APELH2BK

Series	Remote Heads Powered	Housing Color
APEL = All-Pro emergency light	_ = no LED heads H2 = two LED heads	_ = White BK = Black
APWR = All-Pro emergency remote	1 = one LED head 2 = two LED heads	_ = White BK = Black



## Spacing



# AP2SQLED30 Thermoplastic Square LED Head Emergency




AP2SQLED30



The AP2SQLED30 is a fully code compliant, next generation square head LED solution for emergency needs. The adjustable LED emergency heads provide up to 30 feet of egress coverage and will run for a minimum of 90 minutes. The universal j-box mounting pattern and snap fit housing construction significantly reduce installation time.

Features	Benefits
LED source with nickel cadmium battery	Up to 10 years with no maintenance
Adjustable heads	Design flexibility
Up to 30 feet emergency egress coverage	Fewer fixtures required

Certification/Warranty
UL 924 wet location listed
NFPA/NEC/OSHA/CEC code compliant
5-year product warranty
7-year prorated battery warranty





## Ordering Information

SAMPLE NUMBER: AP2SQLED30

Series	Heads	Battery	Coverage	Catalog Numbers
AP = All-Pro	2SQLED = two square LED heads	_ = Nickel Cadmium battery	30 = 30 feet	AP2SQLED30

## Spacing

AP2SQLED30



# APWR



APWR2



APWR2BK

The APWR series is fully code compliant, polycarbonate LED solution for emergency needs. The heads are fully adjustable and available with a white or black housing. This product is wet location listed and suitable for outdoor applications.

Features	Benefits
LED source	Up to 10 years with no maintenance
Adjustable heads	Design flexibility
Wet location capable	Up to 17 feet of indoor/outdoor egress coverage

Certification/Warranty
UL 924 wet location listed
NFPA/NEC/OSHA code compliant
5-year product warranty





## Ordering Information

SAMPLE NUMBER: APWR1, APWR2, APWR1BK, APWR2BK

Series	Remote Heads Powered	Housing Color
APWR = All-Pro emergency remote	1 = one LED head 2 = two LED heads	_ = White BK = Black


## Spacing

APWR





# EBPLEDL LED Emergency battery pack



The improved EBPLEDL series enables electrical contractors to add a UL924 code compliant emergency option to an existing LED fixture. While compatible with almost any LED fixture that has an accessible driver, this series offers guaranteed quality and compatibility with Cooper Lighting Solutions products.

Features	Benefits	Certification/Warranty
Field installable	Meet emergency code with no aesthetic impact	UL 924 Classified
Satisfies all wiring configurations as conduit and test button are included	Design ease; less SKU's to stock	NFPA/NEC/OSHA/CEC code compliant
7 watt or 14 watt output creates 600 to 1500 lumens in emergency mode	Design flexibility; superior egress coverage	Guaranteed compatibility w/Cooper Lighting Solutions
Electronic battery disconnect prevents battery discharge during shipping and installation	Ease of mind	

No maintenance, long-life LiFePO<sub>4</sub> battery = Up to 5 years no maintenance




**T20** Certified to California Title 20 Appliance Database



## Ordering Information

SAMPLE NUMBER: EBPLEDL

Series	Battery Type	Output	Run Time
EBPLEDL = LED emergency battery pack	L = LiFePO <sub>4</sub>	7W = 7 Watt	— = 90 minute
		14W = 14 Watt	— = 90 minute



**Lighting Brands**

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
iO  
Iris  
Lumark  
Lumière  
McGraw-Edison  
Metalux  
MWS  
Neo-Ray  
Portfolio  
PrentaLux - 3D Printed Lighting  
RSA  
Shaper  
Streetworks  
Sure-Lites  
Telensa

**Controls Brands**

Greengate  
Fifth Light  
Intelligent Lighting Controls

**Connected Lighting Systems  
and Smart Spaces Platform**

WaveLinx



Cooper Lighting Solutions  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
[www.cooperlighting.com](http://www.cooperlighting.com)

Canada Sales  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

© 2024 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. BR50522424  
December 3, 2024 4:52 PM