

Project		Catalog #		Type	
Prepared by		Notes		Date	



Lumière

Cambria 206 Series

LED / Halogen
Pathways

Typical Applications

- Hospitality • Commerical Landscape • Outdoor Area/Site • Residential
- Architectural

Interactive Menu

- Order Information [page 2](#)
- Product Specifications [page 3](#)
- Cambria 206 LED Photometric Data [page 4](#)
- Cambria 206 MR16 Halogen Photometric Data [page 5](#)
- Product Warranty

Product Certification




Product Features



Top Product Features

- 340° tilt, 360° rotation
- Precision-machined aluminum, brass, bronze, copper or stainless steel
- Stainless steel hardware
- Siphon Protection System (S.P.S.)
- Holds up to three optical accessories
- Three-year warranty

Dimensions



TECHNICAL DATA
Low voltage (per head):
50W Max Halogen MR16
8W LED, L70/60,000 hours at 25°C

Order Information

SAMPLE ORDER NUMBER: 206-8LED2710-12-CS

Domestic Preferences	Series	Source (for LED, select from each column and combine)			Voltage	Finish
Domestic Preferences ⁽¹⁾	Series	Source ⁽³⁾ (for LED, select from each column and combine)			Voltage	Finish ⁽⁴⁾
[Blank] =Standard BAA =Buy American Act BABA =Build America Buy America Act	206 =One Lamp Head, Cambria Path Fixture 206-2 =Two Lamp Heads, Cambria Path Fixture	50MR16 =50W max. Halogen MR16, GU5.3 Base			12 =12V	Painted BK =Black BZ =Bronze CS =City Silver VE =Verde WT =White RALXX =Custom Color
		8LED =8W LED	27 =2700K 30 =3000K 40 =4000K ⁽²⁾	10 =10° Spot 25 =25° Narrow 36 =36° Wide		
		5LED =5W LED	AM =Amber (585-595nm) ⁽²⁾	25 =25° Narrow		
Notes (1) Only product configurations with these prefixes are built to be compliant with the Buy America Act of 1933 (BAA) or Buy America Build America Act (BABA). Please see the Compliance section in Product Specifications for more detail.	Notes	Notes (2) Not Title 20 compliant. (3) Unless noted otherwise, lamps not included.			Notes	Notes (4) Consult factory for premium/natural metals material finish.

Accessories - Order Separately

Filters (2.00" Diameter)	Optical Lenses (2.00" Diameter)	Optical Louvers (2.00" Diameter)	Ground Mounting
Accessories ^(5,6)			
Filters (2.00" Diameter)	Optical Lenses (2.00" Diameter)	Optical Louvers (2.00" Diameter)	Ground Mounting
F71 =Peach Dichroic F72 =Amber Dichroic F73 =Green Dichroic F74 =Medium Blue F75 =Yellow Dichroic F76 =Red Dichroic F77 =Dark Blue Dichroic F78 =Light Blue Dichroic F79 =Neutral Density Dichroic F80 =Magenta Dichroic F22 =Red Color F33 =Blue Color F44 =Green Color F55 =Yellow Color F66 =Mercury Vapor	LSL =Linear Spread Lens (elongates standard beam spread) DIF =Diffused lens (provides even illumination) OSL =Overall Spread Lens (increases standard beam spread)	LVR =45° Hex Cell Louver (reduces glare)	GS01 =1-1/2" x 6-3/4" (38mm x 171mm) cast zinc ground spike. GS03 =2-3/8" x 6-5/8" (960mm x 168mm) aluminum ground spike with integral 12V wiring compartment. Specify powder paint finish (BK,BZ,CS,VE,WT) GS04 =1" x 16-1/2" (25mm x 419mm) aluminum ground spike with integral 12V wiring compartment. Specify powder paint finish (BK,BZ,CS,VE,WT) GS05 =1" x 16-1/2" (48mm x 438mm) black polycarbonate ground spike with 2"-13" height adjustment - requires fixture with extended stem. GS08 =1-7/8" x 8" (48mm x 203mm) black ABS ground spike. GS13 =3-3/4" x 4-1/2" (95mm x 114mm) brass/stainless steel 3 prong ground spike.
Notes (5) See Accessories & Technical Data section of Lumiere catalog for Mounting Accessories. Consult your customer service representative for additional options and finishes. (6) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.			

Product Specifications

Construction

- Housing, hood and mounting stem are precision machined from corrosion-resistant billet stock 6061-T6 aluminum
- Contact factory about Natural Metals such as C360 brass, C932 bronze, C110 copper, and 303 / 304 stainless steel
- Hood is removable for easy relamping and accepts up to three internal accessories at once (lenses, louvers, filters) to achieve multiple lighting effects
- Weep holes prevent water and mineral stains from collecting on the lens even in the straight-up position
- Housing and hood are sealed with a high temperature silicone o-ring gasket to prevent water intrusion
- Model 206 includes an extended length-mounting stem and delivers 340° tilt and 360° rotation from any mounting position
- Model 206-2 has an overall height of 14-3/8" and includes an adjustable mounting tee for two luminaire heads to allow a full range of aiming from any mounting position
- Stainless steel aim-locking mechanisms are standard
- Stem ends with a 1/2" NPS threaded male fitting
- Lumière's exclusive Siphon Protection System (S.P.S.) prevents water from siphoning into the fixture through its own lead wires

Finish

- Fixtures constructed from 6061-T6 aluminum are double protected by an ROHS* compliant chemical film undercoating and polyester powdercoat paint finish
- A variety of standard colors are available. Custom colors available upon request: select "RALXX" option*; additional charges and lead time apply
- Fixtures constructed from brass, bronze*, copper or stainless steel are left unpainted to reveal the natural beauty of the material. Brass, bronze* and copper will patina naturally over time

Optical

- Tempered glass lens, factory sealed with high temperature adhesive to prevent water intrusion and breakage due to thermal shock
- Halogen lamp not included
- SORAA LED lamps are included when "8LED" options are selected
- LED options are available in 2700K, 3000K, and 4000K at 95CRI; in addition to Amber (585-595nm)
- Select from three beam angles: 10° Spot, 25° Narrow, and 36° Wide
- Both color temperature and distribution must be specified when ordering

Electrical

- Remote 12V transformer required (not included)
- Initial power draw on LED equipped fixtures is 12 watts
- When sizing transformer use 12 watts per LED fixture
- Nominal power draw after start up is 8 watts
- LEDs are more voltage sensitive than standard halogen MR16 lamps
- The LED module is designed to operate within the range 12V +/- 1.2V. Any less or more voltage can cause premature failures
- Ceramic socket with 250° C Teflon® coated lead wires and GU5.3 bi-pin base

Compliance

- Tested to IESNA LM-79 and LM-80
- Domestic preference option available to meet BAA requirements
- Domestic preference option available to meet BABA requirements. BABA is the minimum Government compliance requirement for the Buy America Build America standards which is part of the Infrastructure and Investment Jobs Act (IIJA). Individual Government Agencies may have more stringent compliance standards
- Please refer to the [DOMESTIC PREFERENCES](#) website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyze under domestic preference requirements

Warranty

- Lumière warrants its fixtures against defects in materials & workmanship for three (3) years. Auxiliary equipment such as transformers, and lamps carry the original manufacturer's warranty

*For natural bronze ROHS material consult factory.

Cambria 206 LED Photometric Data

LED Lumen and CBCP Table - 3000K

 View IES files

Information provided is for a single head (206)

Beam Angle	Optical Configuration	Flush Hood			Regressed Hood (Black)			Regressed Hood (Silver)		
		CBCP	LUMENS	LPW	CBCP	LUMENS	LPW	CBCP	LUMENS	LPW
10	BASE	5980	351.3	43.6	5541	298.5	37.1	5052	296.9	39.7
	+DIFF	985	286.9	35.8	968	220.4	27.4	930	233.2	31.2
	+LSL	1310	309.9	38.6	1299	253.1	31.4	1200	252.7	33.8
	+LVR	5270	243.0	30.6	4838	235.3	29.2	4633	225.1	30.1
	+OSL	1686	328.6	41.4	1700	285.7	35.5	1609	291.1	39
25	BASE	2690	417.2	53.5	2559	374.2	47.4	2357	361.8	49.4
	+DIFF	761	338.6	43.4	729	267.7	33.9	720	281.4	36.2
	+LSL	795	375.1	48.1	778	316.3	40.2	719	312.0	42.2
	+LVR	2396	285.9	36.7	2294	272.4	34.1	2092	253.3	35.3
	+OSL	1452	383.4	49.1	1414	345.0	43.8	1328	341.2	45.2
36	BASE	1144	409.2	53.1	1125	369.1	47.6	1080	371.7	49
	+DIFF	542	336.3	43.6	532	264.3	34.1	502	268.6	35.1
	+LSL	486	371.1	48.2	480	305.6	39.4	484	317.4	41.7
	+LVR	1030	267.9	34.8	996	252.1	32.4	967	251.8	33.1
	+OSL	930	384.3	49.9	932	337.8	43.6	910	348.6	45.7

Horizontal Illuminance on Surface - Cambria 206 Standard Recessed Hood - 4000K

CONE OF LIGHT	Filename: 206-SS-8LED4010-12-BK.ies			Filename: 206-SS-8LED4025-12-BK.ies			Filename: 206-SS-8LED4036-12-BK.ies		
	Test No.: G2-1802-569-4			Test No.: G2-1802-569-5			Test No.: G2-1802-569-6		
	Distance	FC	Beam Diameter	Distance	FC	Beam Diameter	Distance	FC	Beam Diameter
	2'	1385.2	0.4	2'	639.8	0.6	2'	281.2	1
	4'	346.3	0.8	4'	159.9	1.2	4'	70.3	2.2
	6'	153.9	1.2	6'	71.1	1.8	6'	31.2	3.4
	8'	86.6	1.6	8'	40	2.4	8'	17.6	4.6
	10'	55.4	2	10'	25.6	3	10'	11.2	5.8
	15'	24.6	3.2	15'	11.4	4.6	15'	5	8.6
	20'	13.9	4.2	20'	6.4	6	20'	2.8	11.6
	30'	6.2	6.4	30'	2.8	9.2	30'	1.2	17.4
	40'	3.5	8.4	40'	1.6	12.2	40'	0.7	23.2

CCT Multiplier Table

CCT (K) Color	Multiplier
2700K	0.91
3000K	0.89
4000K	1.00

Note: Multiplier can be used to calculate center beam candle power (CBCP), Lumens and footcandle (FC) values.


NOTES:

- Dimming is dependant on remote transformer compatibility with LED module. Please see [compatibility matrix](#) for dimmer switch and transformer selection.
- When using a magnetic dimmer switch there are two recommended LED compatible 120V magnetic dimming switches:
Lutron Ariadni AVLV-600P and Lutron Diva DVLV-600P
- IMPORTANT: When sizing transformer use 12 watts per LED fixture. Nominal power draw after start up is 8 watts. Any less or more voltage can cause premature failures.

Cambria 206 & 206-2 MR16 Halogen Photometric Data

Information provided is for a single head (206)

Horizontal Illuminance on Surface - Cambria 206 Standard Recessed Hood - 50W MR16



Filename	206-50MR16-12-BK-NSP.ies	
Lamp	50W MR16 NSP	
CBCP	11,000	
Distance	FC	Beam Diameter
2'	2550	1'6"
4'	638	1'0"
6'	283	1'6"
8'	159	2'0"
10'	102	3'0"
15'	45	4'0"

Filename	206-50MR16-12-BK-NFL.ies	
Lamp	50W MR16 NFL	
CBCP	3,200	
Distance	FC	Beam Diameter
2'	725	1'0"
4'	181	2'6"
6'	81	4'0"
8'	45	5'0"
10'	29	6'6"
15'	13	10'0"

View IES files

Wattage Multiplier Table

Lamp wattage	Multiplier
20W	0.32
35W	0.57

Filename	206-50MR16-12-BK-FL.ies	
Lamp	50W MR16 FL	
CBCP	2,000	
Distance	FC	Beam Diameter
2'	431	1'6"
4'	106	3'0"
6'	48	5'0"
8'	27	6'6"
10'	17	8'0"
15'	7	12'0"

Filename	206-50MR16-12-BK-WFL.ies	
Lamp	50W MR16 WFL	
CBCP	1,200	
Distance	FC	Beam Diameter
2'	269	2'0"
4'	67	4'6"
6'	30	7'6"
8'	17	9'0"
10'	11	11'6"
15'	5	17'0"

NOTES:

- Beam diameter is to 50% of maximum footcandles, rounded to the nearest half-foot.
- Footcandle values are initial. Apply appropriate light loss factors where necessary.
- Bare lamp data shown. Consult lamp manufacturers to obtain detailed specifications for their lamps.