

Project		Catalog #		Type	
Prepared by		Notes		Date	



## Metalux

### Vaportite LED

2' Industrial LED Lamp  
Vaportite Industrial Refrigerated Case

#### Typical Applications

Parking Garage • Cold Storage • Canopy • Warehouse • Food Processing •  
Manufacturing • Complex Environments

#### Interactive Menu

- Order Information page 2
- Photometric Data page 3
- Product Warranty

#### Product Certification






#### Product Features




#### Top Product Features

- 2ft, 4ft, and 8ft Sealed and Gasketed Vaportite
- Lumen packages up to 22K lumens
- High-Performance efficacy up to 150 LPW
- LEDs available in 3000K, 3500K, 4000K and 5000K at 80 CRI
- Rated for -40c to 35c ambient
- Impact protection rating IK06 Lens and IK06 Housing
- Options to meet Build America, Buy America, Buy American and other domestic preference requirements


#### Dimensional and Mounting Details



#### Installation Data



**MOUNTING BRACKETS**  
Furnished  
Two per 2' and 4' Unit  
Four per 8' Unit




**OPTIONAL CHAIN HANGING SET**  
(VT2-CHAIN/SET-U)  
Includes 6 ft. of chain, 4 large S-Hooks and 4 small S-Hooks  
Order One (1) Kit for each 2' or 4' Fixture  
Two (2) Kits Recommended For 8' Fixture

## Order Information

SAMPLE ORDER NUMBER: **2VT2-LD5-3-DR-UNV-L840-CD1-WL-U**

Domestic Preferences	Series	Lamp Type	LED Lumens Output	Lens	Distribution	Voltage	Remote Emergency Enclosure
Domestic Preferences <sup>(1)</sup>	Series <sup>(2)</sup>	Lamp Type	LED Lumens Output	Lens	Distribution	Voltage	Remote Emergency Enclosure
<b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act <b>BABA</b> =Build America Buy America Act	2VT2=2' Vaportite	LD5=LED 5.0	2=2000 Lumens 3=3000 Lumens 4=4000 Lumens 5=5000 Lumens <sup>(3)</sup>	DR=Internal Prismatic Lens/15% DR High Impact Additive DR100=Internal Prismatic Lens/100% DR High Impact Additive FR50=Frosted Lens/15% DR High Impact Additive <sup>(4)</sup>	<b>[Blank]</b> =Medium (Standard) <b>W</b> =Wide Distribution	UNV=Universal Voltage 120-277	VT-REM-EL=Emergency Installed, 700 lumens <sup>(5)</sup>
<b>Notes</b> (1) Only product configurations with these prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or the Build America Buy America Act (BABA). BABA is the minimum Government compliance requirement for the Build America Buy America standards which is part of the Infrastructure and Investment Jobs Act (IIJA). Individual Government Agencies may have more stringent compliance standards. Please refer to <a href="#">DOMESTIC PREFERENCES</a> website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	<b>Notes</b> (2) DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium, refer to <a href="#">www.designlights.org</a> for details.		<b>Notes</b> (3) 2ft, 5000 lumen configuration rated up to 30°C max ambient.	<b>Notes</b> (4) Not available in wide distribution.			<b>Notes</b> (5) EL must specify 120-277V.

CCT	Driver Type	Label	Options	Packaging	Accessories
CCT	Driver Type	Label	Options	Packaging	Accessories (order separately) <sup>(9)</sup>
<b>L830</b> =3000K, LED <b>L835</b> =3500K, LED <b>L840</b> =4000K, LED <b>L850</b> =5000K, LED	CD1=1 Dimming Driver	WL=Wet Location Label	SSL=Stainless Steel Latches TH=(2) Top Watertite Hubs TEH=(2) Top and (2) End Watertite Hubs (all Watertite Hubs have 1/2" Conduit Entry) MS=Damp Listed Motion Sensor, Non-dimming MSWL20=Wet Listed Motion Sensor, Non-dimming, 20ft max mounting height WPS4=WaveLinX Wireless Sensor, Sidecar mount, with 1200 sq ft. coverage WLS4=WaveLinX Lite Wireless Sensor, Sidecar mount, 15'-40' Mounting Height <sup>(6)</sup> OF1DZ=Leviton 120-277V PIR Occupancy Sensor with integral 0-10V Dimming <sup>(7), (8)</sup>	U=Unit Pack	<b>VT2-Chain/Set-U</b> =Chain Hanging Set. Includes 6 ft. of chain, 4 large S-Hooks and 4 small S-Hooks Order One (1) Kit for each 2' or 4' Fixture <b>VT2-SS-MBK</b> =Stainless Steel Mounting Bracket 
			<b>Notes</b> (6) WaveLinX LITE devices are not currently compatible with the WaveLinX PRO Wireless Area Controller. (7) Available for UNV (for 120V or 277V) only. (8) Configuration of basic and advanced features using the Leviton Smart Sensor App on any Bluetooth-enabled Android or iOS device.		<b>Notes</b> (9) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

## Product Specifications

### Construction

- Rugged and durable construction
- Fiberglass housing is reinforced polyester and self-extinguishing (ASTM-D635-74) plastic
- Full metal fixture liner
- Watertight housing
- 1/2" conduit entry at each end of housing (standard) for continuous feed
- Polyurethane gasketing provides a continuous seamless seal for the diffuser lens
- Four sturdy cam latches clamp diffuser tightly for a positive seal between housing, gasketing and diffuser
- Surface or chain mounting
- Impact protection rating IK06 Lens and IK06 Housing

### Electrical

- Long-Life LED system coupled with electrical driver for optimal performance
- LED's available in 3000K, 3500K, 4000K and 5000K with a CRI  $\geq$  80
- Projected life is 60,000 hours at 91% lumen output
- Electronic drivers are available for 120-277V applications
- 0-10V dimming control (standard)
- Operating temperature of -40°C to 35°C; Ideal for cold storage environments

### Lens

- High-impact diffuser lens
- Internal Prismatic Lens with 15% DR High Impact Additive (DR) or Internal Prismatic Lens with 100% DR High Impact Additive (DR100)
- Frosted Lens with 15% DR High Impact Additive (FR50) option

### Finish

- Housing is permanent pearl gray color

### Warranty

- Five-year limited warranty

### Compliance

- UL/cUL listed for Wet location
- RoHS compliant
- LED modules comply with IESNA LM-79 and LM-80 standards
- NSF listed
- DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium (refer to [www.designlights.org](http://www.designlights.org) for details)
- The VT2 Series ratings apply to Horizontal Mounting only


### BABA Domestic Preference Compliance

- This Cooper product is manufactured in the US and meets the BABA cost of components rule. To verify a configured product with specific accessories and options meets BABA Domestic Preference Requirements; submit this catalog number to Cooper Lighting Quotation team for validation by our Engineering and Manufacturing teams. Our BABA designation is based on the minimum compliance requirement for BABA. Individual Government Agencies may have more stringent compliance standards. Please refer to the [DOMESTIC PREFERENCES](#) website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.

**WaveLinX LITE devices are not currently compatible with the WaveLinX PRO Wireless Area Controller**


## Photometric Data

 [View IES files](#)



### 2VT2-LD5-4-DR-W-UNV-L840-CD1-WL-U

Electronic Driver  
Linear LED 4000K  
Spacing criterion: (II) 1.22 x mounting height,  
( $\perp$ ) 1.59 x mounting height  
Lumens: 3603  
Input Watts: 28.9W  
Efficacy: 124.7 lm/W  
Test Report:  
2VT2-LD5-4-DR-W-UNV-L840-CD1-WL-U.IES



### 2VT2-LD5-4-DR-UNV-L840-CD1-WL-U

Electronic Driver  
Linear LED 4000K  
Spacing criterion: (II) 1.21 x mounting height,  
( $\perp$ ) 1.23 x mounting height  
Lumens: 4075  
Input Watts: 28.9W  
Efficacy: 141 lm/W  
Test Report:  
2VT2-LD5-4-DR-UNV-L840-CD1-WL-U.IES

## Energy and Performance Data

### Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours)	Theoretical L70 (Hours)
25°C	> 91%	> 237,000

### IK Rating

VT2	IK Rating
Lens	IK06
Housing	IK06

### Shipping Data

Catalog No.	Wt.
2VT2-LD5	10 lbs.

### Input Watts:

2VT2-LD5-2 (2,000 lumens)=17W
2VT2-LD5-3 (3,000 lumens)=22W
2VT2-LD5-4 (4,000 lumens)=29W
2VT2-LD5-5 (5,000 lumens)=39W