

DESCRIPTION

The WSN Series is a specification wraparound luminaire featuring energy efficient performance. The luminaire's characteristic clean, low profile design is both appealing and practically functional. The WSN Series utilizes a clear, low brightness, extruded acrylic refractor with injection molded end caps for high performance and good looks.

The efficient and stylish WSN Series is the perfect wraparound for commercial spaces, schools, dormitories, offices and retail areas.

| | | | |
|--------------------|--|-------------|--|
| Catalog # | | Type | |
| Project | | | |
| Comments | | Date | |
| Prepared by | | | |

SPECIFICATION FEATURES

Construction

Housing die formed code gauge prime cold rolled steel. Six full length ribs for strength. Ballast cover easily removed without tools. Steel end plates with 7/8" KO and light-seal embossment. Couplers for continuous row mounting.

Electrical*

Ballasts are CBM/ETL Class "P" and are positively secured by mounting bolts. Pressure lock lampholders. UL/CUL listed. Suitable for damp locations.

Finish

Multistage, iron phosphate pretreatment ensures maximum bonding and rust inhibitor. Lighting grade, baked white enamel finish.

Frame/Shielding

100% clear full thickness virgin acrylic prismatic refractor/lens. Permanent luminous injection molded end caps. Sides have inside linear prisms and bottom has pyramidal prisms for low brightness control. Lens can be hinged from either side in a lift and shift manner.

Compliance

Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements.




**WSN
232**

**4' OR 8' SURFACE
2 LAMPS**


Specification Wrap

MOUNTING DATA



LIFT & SHIFT REFRACTOR

Easily Removed. Hinges Either Side
(Not Recommended For Sloped Ceiling Applications.)



LAMPS CONTAIN MERCURY. DISPOSE ACCORDING TO LOCAL, STATE OR FEDERAL LAWS


LINEAR DISCONNECT

Safe and convenient means of disconnecting power.



ORDERING INFORMATION

SAMPLE NUMBER: WSN-232A-UNV-EB81-U



ACCESSORIES
(Order Separately)

- SCF**=Fixed Stem Set (Specify Length)
- SCS**=Swivel Stem Set (Specify Length)
- SCA**=Adjustable 48" Stem Set
- A1B/Spacer-U**=Spacer 1-1/2" to 2-1/2" from ceiling (Use 2 per fixture)

Lengths Available: 6, 8, 12, 18, 24, 36, 48

(Additional Accessories Available. See Options and Accessories Section.)

NOTES: ⁽¹⁾Steel endplates with 7/8" KO standard for continuous row mounting. ⁽²⁾Stem mounting not available on 3-lamp fixtures. ⁽³⁾2 point suspension recommended for 2 and 4-lamp fixtures. ⁽⁴⁾Products also available in non-US voltages and frequencies for international markets. ⁽⁵⁾Not available when specifying emergencies, voltage must be specific. ⁽⁶⁾Please specify required voltage, 120V or 277V.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative for availability and ordering information.

DISCONTINUED 09-18-2025

SHIPPING DATA

| Catalog No. | Wt. |
|-------------|---------|
| WSN-232A | 17 lbs. |
| 8TWSN-232A | 33 lbs. |