

Project		Catalog #		Type	
Prepared by		Notes		Date	



PrentaLux

309

A-19 LED Lamp Based Luminaire Decorative

Typical Applications

- Hospitality • Office • Commercial • Education • Retail • Healthcare
- National Accounts • Residential • Multi-Family

Interactive Menu

- Order Information [page 2](#)
- Color Selections [page 3](#)
- Mounting [page 4](#)
- Photometric & UGR Data [page 4](#)

Certifications



Filament only.
See page 6



LIVING BUILDING CHALLENGE


Features




Top Product Features

- PrentaLux 300's are a series of decorative products that utilize Cooper Lighting's 3D Printing technology using an A-19 LED lamp base.
- Modern form available in 8 standard opaque colors and 4 standard transparent/translucent colors with additional On-Demand colors available with possible additional costs and lead times. Please consult factory.
- A19 Lamp based, E26 socket: Frosted lamp, Filament lamp, or no lamp (lamp is provided by others up to 50W), options.
- Voltage is 120V only.
- 3D printed mounting canopy available in disk or conical shape.
- Black or white power cord.
- BAA compliant. RoHS compliant.
- [Declare compliant](#)
- LBC Red List Free
- 5 Year Warranty

Dimensions



Scale



Order Information

SAMPLE CATALOG NUMBER: PRLX-309-FR-120-SLVR-SMGY-CB-BK

--	--	--	--	--

Domestic Preferences	Brand	Series	Source	Voltage	Shade Color
<p>[Blank] = Standard BAA = Buy America Act</p>	PRLX	309	<p>NB = No Lamp Supplied (Lamp by others) FIL = A19, E26 LED Filament lamp, 2700K (60W incandescent equivalent) FR = A19, E26 LED Frosted lamp, 3000K (60W incandescent equivalent)</p>	120 = 120V Voltage	<p>Standard Transparent/Translucent Colors TRWH = Translucent White DIFF = Diffuse CLER = Clear SMGY = Smokey Gray</p> <p>Standard Opaque Colors: WHITE = White BLAK = Black GRAY = Gray ROSE = Rose CAPP = Cappuccino SAGE = Sage BRNZ = Bronze BRSS = Brass</p> <p>XXXX² = On-Demand Color</p>
<p>Notes</p> <p>1. Only product configurations with this designated prefix are built to be compliant with the Buy American Act of 1933 (BAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.</p>	<p>Notes</p>	<p>Notes</p>	<p>Notes</p> <p>1. A19 lamps up to 50W may be used in these fixtures (supplied by others). 2. Dimming is determined by lamp selected</p>	<p>Notes</p> <p>1. See page 3 for color options. 2. On-Demand colors available with possible extended lead times and additional costs. Consult factory. See page 3 for additional color options.</p>	<p>Notes</p>

Continue here to make complete selections

--	--	--

Top Finial Color	Canopy	Cord Color
<p>TFIN¹ = Top Finial Color Same as Outer Shade Color (Recommended)</p> <p>Standard Top Finial Colors: TFWHITE = White TFBLAK = Black TFGRAY = Gray TFROSE = Rose TFCAPP = Cappuccino TFSAGE = Sage TFBRNZ = Bronze TFBRSS = Brass</p> <p>XXXX² = On-Demand Color</p>	<p>DW = Disk - White DB = Disk - Black DC = Disk canopy matches outer shade color (opaque color only)</p> <p>CW = Conical - White CB = Conical - Black CC = Conical canopy matches outer shade color (opaque color only)</p>	<p>BK = Black power cord and black socket WH = White power cord and white socket</p>
<p>Notes</p> <p>1. Translucent White (TRWH) Outer Shade gets White (WHITE) Top Finial by default. Diffuse (DIFF) Outer Shade gets White (WHITE) Top Finial by default. Clear (CLER) Outer Shade gets White (WHITE) Top Finial by default. Smokey Gray (SMGY) Outer Shade gets Black (BLAK) Top Finial by default.</p> <p>2. On-Demand colors available with possible extended lead times and additional costs. Consult factory. See page 3 for additional color options.</p>	<p>Notes</p>	<p>Notes</p>

Product Specifications

Construction

- PrentaLux 300s series consist of a lamp / socket combination that uses an A-19, E26 Socket LED lamp base and a proprietary additive manufacturing process for the polycarbonate shade and components.
- 300 series shades utilize a proprietary, impact resistant polycarbonate for maximum durability
- The polycarbonate used for PrentaLux fixtures is bio-circular and thermally, mechanically and optically optimized for professional/commercial installations. Designed, engineered, and printed in the United States.

LED Lamp

- Available in Filament based LED lamp, Frosted based LED lamp, or no lamp (up to 50W supplied by others), options.
- Frosted LED lamp is 15W (equivalent to 60W incandescent lamp). 15,000 hour lamp life. 3000K @90 CRI. Output is 800 lumens. E26 base A19 lamp shape. Dimmable. Efficacy is 53.3 LPW.
- Filament LED lamp is (15W equivalent to 60W incandescent lamp). 15,000 hour lamp life. 2700K @90 CRI. Output is 800 lumens. E26 base A19 lamp shape. Dimmable. Efficacy is 53.3 LPW.
- Fixture is rated for lamps up to 50W (by others)
- Dimming is determined by the lamp selection

Optics

- Output determined per shade shape, color and transparency/translucency/opaqueness. See polar plots and UGR data on page 4.
- 300 series fixtures include an inner diffuser to create a consistent illumination with transparent or translucent outer shades.
- The 300 series pendants are designed for transparent and translucent outer shades. These options should be selected for maximum impact.

Electrical

- Standard 120V.

Mounting

- Mounting options include UL certified cord and option of 3D printed disk shape or conical shape mounting canopy.

Finish

- Shade available in 8 standard opaque colors and 4 standard transparent/translucent colors with additional On-Demand colors available. Additional costs and lead times may apply. Please consult factory.
- The 'Finial' recommendation is to match the outside shade color, with the following exceptions: When outer shade is transparent or translucent, an opaque finial color must be chosen. Black finial is default selection for Smokey Grey Outer shade color and White finial is default selection for Clear Outer Shade color.

Lengths

- Fixture comes with 10ft cord. Lengths up to 25 ft possible. (Consult factory for length longer than 10ft as longer lead times apply).

Weight

- Product is light weight and much easier to install than traditional pendants.
- 309 fixture weighs approximately 4lbs

Environment

- Suited for 25° ambient. Dry location only.


Compliance

- All products are light weight and much easier to install than traditional pendants.
- Filament material is UL certified.
- Declare Compliant, LBC Red List Free, ISCC certified
- BAA compliant
- RoHS compliant
- Not to be installed in food prep areas and hazardous environments which may expose the product to pollutants such as oil, grease, or VOCs.
- IK02 impact rated. Not for installations in locations such as gymnasiums, arenas, sports complexes, multi-purpose rooms, and any other locations where the fixture potentially will be subject to impacts from external sources.


Sustainable Product Specifications

- PrentaLux 3D printed parts are produced with at least 75% recycled or bio-circular materials (using an ISCC certified mass balance approach).
- ISCC certified. Certification applies only to 3D printed material.
- Declare compliant.
- LBC Red List approved.

Mounting - Canopy Options



Canopy Colors



Standard Transparent/Translucent Shade Colors

Not available for Top Finial



CLER - Clear



DIFF - Diffuse White



TRWH - Translucent White



SMGY - Transparent Smokey Gray


Standard Opaque Shade & Top Finial Colors



WHITE - White



BLAK - Black



GRAY - Gray



ROSE - Rose



CAPP - Cappuccino



SAGE - Sage



BRNZ - Bronze




BRSS - Brass

On-Demand Transparent Shade Colors

These special color options may have extended lead times and/or additional costs. Please consult factory. Not available for Top Finial



TRBL - Transparent Blue




TRGR - Transparent Green



TROR - Transparent Orange



TRYE - Transparent Yellow



TRRE - Transparent Red

On-Demand Opaque Shade & Top Finial Colors

These special color options may have extended lead times and/or additional costs. Please consult factory.



ENGR - Enamel Green




MEGR - Metallic Green



MCHA - Matcha




STBL - Steel Blue



MEBL - Metallic Blue



MYBL - Misty Blue



DKGY - Dark Gray



SLVR - Silver



STBR - Stone Brown



MEPU - Metallic Purple



RGLD - Rose Gold



CITR - Citrona



CRWH - Cream White



BURG - Burgundy

Finial Color Recommendations




TFIN - Top Finial Color Same as Outer Shade Color





TFWHITE - White (if CLER Outer Shade Color option chosen, White top finial is recommended)



TFBLAK - Black (if SMGY Outer Shade Color option chosen, Black top finial is recommended)



Photometric Data

PRENTALUX - 309				
	309 - Frosted Lamp		309 - Filament Lamp	
Filename	309-FR-120-BRMT-BZME.ies		309-FIL-120-BRMT-WHST.ies	
Test No.	G3-2203-583-14		G3-2203-583-13	
Lumcat	309-FR-120-BRMT-BZME		309-FIL-120-BRMT-WHST	
Lumens	546.5 Lm		429.4 Lm	
Input Watts	7.74 W		7.75 W	
Efficacy	70.6 Lm/W		55.4 Lm/W	
CCT	3000K		2700K	
SC (0/90/45)	1.73 / 1.73 / 1.69		2.04 / 2.04 / 1.85	

UGR Data

Fixture Type	CCT	UGR [CIE 190:2010] ⁽¹⁾ (4H, 8H; Reflectance: 70% Ceiling, 50% Wall, 20% Ref. Plane		MAX LUMINANCE [45-90 DEG FROM NADIR] ⁽²⁾ (CD/M ²)	
		90 CRI		90 CRI	
		Frosted	Filament	Frosted	Filament
309	3000K (frosted) /2700K (filament)	14.55	13.30	1947	1696

Notes: (1) For other UGR data for room or reflective ceiling plans please see technical data on website. (2) For other CCT please see technical data on website.
 (3) Averages taken over different colors. Tables available upon request.