

## DESCRIPTION

The Encounter™ redefines ambient lighting by being the first fixture to blend modern contemporary styling with the innovative WaveStream™ technology to deliver exceptional performance and superior energy savings. Encounter's highly efficient LED system with advance optical design delivers an unparalleled combination of optimal light uniformity for enhanced visual comfort and superior efficiency for greater energy savings.

Encounter is compatible with all of today's popular ceiling systems and available in a variety of configurations for application versatility. Its perfect balance of form and function make it an ideal choice for commercial office spaces, schools, hospitals, retail and other indoor ambient applications.

## SPECIFICATION FEATURES

### Construction

Shallow 3-1/4" deep housing is extruded aluminum frame and injected molded composite end plates. End plates are securely attached with screws for strength and rigidity and the elimination of gaps. End plates have accessory grid-lock feature for safety and convenience. Four auxiliary fixture end suspension points are provided. Large access plate for supply connection.

### Controls

Standard a 0-10V continuous dimming driver that works with any 0-10V control/dimmer. Or, go digital with the Digital Addressable Lighting Interface (DALI) drivers, dimmable down to 1% using the HD option. Combine with energy-saving products like occupancy sensors, daylighting controls, and lighting relay panels to maximize energy savings.

### Electrical

Long-life LED system coupled with electrical driver to deliver optimal performance. LED's available in 3000K, 3500K or 4000K with a typical CRI ≤ 85. Projected life is 100,000 hours at X92% lumen output. Electronic drivers are available for 120-277V applications.

### Driver Access

Drivers can be accessed via plenum.

### Finish

Durable frame has high reflectance baked matte white enamel finish for luminous uniformity.

### Optics

Precision formed optical assembly with positively retained high optical grade acrylic lenses provide a directed optical distribution using WaveStream technology.

### Compliance

Components are UL recognized. Indoor luminaires are cULus listed and CE marking for 25° C ambient environments, RoHS compliant, and comply with IESNA LM-79. LEDs comply with LM-80 standards. Options to meet Buy American and other domestic preference requirements.

### Warranty


Five year warranty.




**66EN  
LED**

**600 X 600 TROFFER  
LED MODULE**


Specification Grade Metric  
Troffer



## MOUNTING DATA



## LAMP CONFIGURATIONS



## CEILING COMPATIBILITY

G	F	Ceiling Type	Trim Type
Grid/Lay-in Standard	Drywall Frame Kit	Exposed Grid	G
		Concealed T	G or T
		Slot Grid	G or T
		Flange	G or T

## CERTIFICATION DATA

cULus - 1598 and 2043\*  
CE Marking  
Damp Location Listed  
CSA  
IC Rated  
LM79/LM80 Compliant  
ROHS Compliant

\*Fixture construction is suitable for use in Air-handling and plenum rated spaces in accordance with Section 300.22 (C) of the National Electrical Code, Section 4.3.11.2.6.5 of NFPA 90A and Section 602.2.1.4 of ICC.

## LINEAR DISCONNECT

Safe and convenient means of disconnecting power



PS519074EN  
September 22, 2022 1:50 PM

## ENERGY AND PERFORMANCE DATA BY CATALOG NUMBER

Stock or MTO*	Catalog Logic	Description	Delivered Lumens	Watts	Efficacy (lm/W)
MTO	66EN-LD2-19-UNV-L830-CD1-U	600x600, 1900 Lumens, UNV, 3000K, 0-10V	1907	16.5	116
MTO	66EN-LD2-19-UNV-L835-CD1-U	600x600, 1900 Lumens, UNV, 3500K, 0-10V	1966	16.5	119
MTO	66EN-LD2-19-UNV-L840-CD1-U	600x600, 1900 Lumens, UNV, 4000K, 0-10V	2006	16.5	122
MTO	66EN-LD2-25-UNV-L830-CD1-U	600x600, 2500 Lumens, UNV, 3000K, 0-10V	2416	20.0	121
MTO	66EN-LD2-25-UNV-L835-CD1-U	600x600, 2500 Lumens, UNV, 3500K, 0-10V	2490	20.0	124
MTO	66EN-LD2-25-UNV-L840-CD1-U	600x600, 2500 Lumens, UNV, 4000K, 0-10V	2540	20.0	127
MTO	66EN-LD2-30-UNV-L830-CD1-U	600x600, 3000 Lumens, UNV, 3000K, 0-10V	2807	24.9	113
MTO	66EN-LD2-30-UNV-L835-CD1-U	600x600, 3000 Lumens, UNV, 3500K, 0-10V	2894	24.9	116
MTO	66EN-LD2-30-UNV-L840-CD1-U	600x600, 3000 Lumens, UNV, 4000K, 0-10V	2952	24.9	119
MTO	66EN-LD2-34-UNV-L830-CD1-U	600x600, 3400 Lumens, UNV, 3000K, 0-10V	3166	28.5	111
MTO	66EN-LD2-34-UNV-L835-CD1-U	600x600, 3400 Lumens, UNV, 3500K, 0-10V	3264	28.5	115
MTO	66EN-LD2-34-UNV-L840-CD1-U	600x600, 3400 Lumens, UNV, 4000K, 0-10V	3329	28.5	117
MTO	66EN-LD2-39-UNV-L830-CD1-U	600x600, 3900 Lumens, UNV, 3000K, 0-10V	3629	33.3	109
MTO	66EN-LD2-39-UNV-L835-CD1-U	600x600, 3900 Lumens, UNV, 3500K, 0-10V	3742	33.3	112
MTO	66EN-LD2-39-UNV-L840-CD1-U	600x600, 3900 Lumens, UNV, 4000K, 0-10V	3816	33.3	115
MTO	66EN-LD2-43-UNV-L830-CD1-U	600x600, 4300 Lumens, UNV, 3000K, 0-10V	4085	38.3	107
MTO	66EN-LD2-43-UNV-L835-CD1-U	600x600, 4300 Lumens, UNV, 3500K, 0-10V	4211	38.3	110
MTO	66EN-LD2-43-UNV-L840-CD1-U	600x600, 4300 Lumens, UNV, 4000K, 0-10V	4296	38.3	112

\*Made to order (MTO) requires a typical six week lead time.

## LUMEN MAINTENANCE

Ambient Temperature	TM-21 Lumen Maintenance (100,000 hours) <sup>(1)</sup>	Theoretical L70 (hours) <sup>(2)</sup>
25° C	> 92%	> 448,000

**Notes:** (1) Supported by IESTM-21 standards. (2) Theoretical values represent estimations commonly used; however, refer to the IES position on LED Product Lifetime Prediction, IES PS-10-18, that explains proper use of IESTM-21 and LM-80.

## ORDERING INFORMATION

SAMPLE NUMBER: 66EN-LD2-34-UNV-L835-CD1-U

<b>Domestic Preferences</b> <sup>(9)</sup> <b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act	<b>Rating</b> <b>Blank</b> =Standard  <b>Series</b> <b>66EN</b> =600 x 600 Encounter Series	<b>Lamp Type</b> <b>LD2</b> =LED 2.0  <b>MTO Lumen Outputs</b> <sup>(3), (5)</sup> <b>19</b> =1900 Lumens <sup>(4), (6)</sup> <b>25</b> =2500 Lumens <sup>(4), (6)</sup> <b>30</b> =3000 Lumens <sup>(4), (6)</sup> <b>34</b> =3400 Lumens <sup>(4)</sup> <b>39</b> =3900 Lumens <b>43</b> =4300 Lumens	<b>Optics</b> <b>Blank</b> =Standard  <b>Voltage</b> <sup>(1)</sup> <b>230V</b> =220-240 Volt (CE only) <b>347V</b> =347 Volt <b>UNV</b> =Universal Voltage 120-277  <b>Emergency Options</b> <b>EL7W</b> =7-watt 120V-277V emergency battery pack <sup>(11)</sup> <b>EL10W</b> =10-watt 120V-277V emergency battery pack <sup>(11)</sup> <b>EL14W</b> =14-watt 120V-277V emergency battery pack <sup>(11)</sup> <b>EL10WSD</b> =10W emergency battery pack with self-diagnostic installed <sup>(11), (12)</sup> <b>EL14WSD</b> =14W emergency battery pack with self-diagnostic installed <sup>(11), (12)</sup>	<b>Options</b> <b>CCT</b> <b>L830</b> =3000K <b>L835</b> =3500K <b>L840</b> =4000K <b>Flex</b> Multiple Configurations Available	<b>Driver Type</b> <b>CD</b> =0-10V Driver (10%-100% Dimming) <b>5LTD</b> =DALI Driver (5%-100% Dimming) <sup>(2), (5)</sup> <b>5LTHD</b> =DALI Driver (1%-100% Dimming) <sup>(2), (5)</sup>	<b>Number of Drivers</b> <b>1</b> =1 Driver  <b>Compliance</b> <b>[Blank]</b> =UL Listed <b>CE</b> =CE Marking <sup>(5)</sup>
<b>Product Family</b> <b>S</b> =Integrated Sensor <sup>(7), (8)</sup>  <b>Control Type</b> <b>B</b> =Sensor Mounting, No Sensor <b>V</b> =Analog (0-10V) Output for Local Control <sup>(7)</sup>	<b>Occupancy Technology</b> <b>P</b> =Passive Infrared	<b>Sensing Technology</b> <b>D</b> =Dimming Daylight Harvesting (Closed Loop)	<b>Coverage Pattern</b> <b>1</b> = ~144 Square Feet	<b>Packaging</b> <b>U</b> =Unit Pack <b>PALC</b> =Job Pack, in carton	<b>ACCESSORIES</b> <sup>(10)</sup> <b>T3A END E.Q. BRACKET PARTS BAG</b> (Standard with fixture) <b>DF10P-C</b> =Decorator Dimmer, 0-10V <b>SF10P-.</b> =Decorator Slide Dimmer, 0-10V <b>ISHH-01</b> =Programming Remote for Integrated Sensor <b>ISHH-02</b> =Personal Control Remote for Integrated Sensor	

**NOTES:** <sup>(1)</sup> Products also available in non-US voltages and frequencies for international markets. <sup>(2)</sup> Must be used in conjunction with a DALI control system. For complete DALI solutions, visit [www.cooperlighting.com](http://www.cooperlighting.com) <sup>(3)</sup> Made-to-order (MTO) requires six week lead time. <sup>(4)</sup> 1900, 2500, 3000 and 3400 lumen option are not available with a DALI (5LTD) driver. <sup>(5)</sup> CE versions are not available with DALI (5LTD) driver option. <sup>(6)</sup> CE versions 1,900, 2,500 and 3,000 lumen packages are not available with DALI (5LTHD) driver option. <sup>(7)</sup> Integral sensor works only with "CD" driver and is factory prewired to the driver for stand-alone control. <sup>(8)</sup> Integral sensor option is only available for UL versions. <sup>(9)</sup> Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to [DOMESTIC PREFERENCES](http://DOMESTIC.PREFERENCES) website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. <sup>(10)</sup> Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information. <sup>(11)</sup> Factory installed with integral test switch/indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES-format photometry for luminaire under emergency operation available. Battery option increases total height by 1 inch. <sup>(12)</sup> EL10WSD and EL14WSD not available with 347V.

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative for availability and ordering information.

## SHIPPING DATA

Catalog No.	Wt.
66EN-LD2-25	14 lbs.
66EN-LD2-34	14 lbs.

## INTEGRATED SENSOR


The Encounter and Encounter HP with Integrated Sensor technology provides automatic energy savings without sacrificing performance. Traditionally, these types of energy savings required coordination between the luminaire and a lighting control system. The Encounter delivers superior lighting with integrated occupancy and daylighting controls.

Capture the benefits of traditional lighting controls, without complicated coverage planning or special wiring. Ideal for new construction or retrofit, the Encounter delivers automatic ON to an energy saving light level, while ensuring lighting is turned OFF when the space is unoccupied.

The integral daylight sensor reduces the need for special daylight zone planning. Each luminaire will automatically adjust the light level based on reflected light beneath the sensor in a closed loop method.


Occupied daylight light levels and unoccupied light levels can be adjusted using the integrated sensor programming remote (Catalog Number: ISHH-01). The integrated sensor personal remote (Catalog Number: ISHH-02) provides code compliant manual raise, lower, ON, OFF control.

The Encounter with Integrated Sensor is easy to install with no special wiring and ensures energy savings out-of-the-box with default control settings.




### How it works:


- As the user enters the space controlled by the integral sensor, the lighting turns ON to the default daylight level.
- Lighting will remain at that the daylight level until the space is unoccupied. This will start the occupancy timeout period (default 20 minutes).
- If the space remains unoccupied for half of the timeout period, the lighting will automatically reduce to the Energy Saver light level. This adjustable light level is typically half of the occupied daylight level.
- At the end of the timeout period the lighting will go to the unoccupied light level. This adjustable light level uses the OFF default setting.



### Coverage



### Side View



### Optional Remote Controls



ISHH-01 Programming Remote



ISHH-02 Personal Control Remote