

Certificate of Compliance

Certificate Number:

E328008

Report Reference:

E328008 - 20190619

Issue Date:

2024-MARCH-03

Issued to:

Cooper Lighting, LLC

1121 HIGHWAY 74 S PEACHTREE CITY

GA30269-3019 US

This certificate confirms that representative samples of:

Light-emitting-diode Surface-mounted Luminaires

See Addendum Page for Models

Has been evaluated by UL LLC in accordance with Standard(s) for Safety:

UL 1598 and CSA C22.2 No. 250.0 - Luminaires

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Certification Mark on the product.



David Piecuch

UL Mark Certification Program Owner

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



Certificate of Compliance

Certificate Number: E328008
Report Reference: E328008 - 20190619
Issue Date: 2024-MARCH-03

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

LED Surface Mounted Luminaire – Models, WPSLED10-XX-Y-ZZ-AAA (b), WPMLED10-XX-Y-ZZ-AAA (b), WPMLED15-XX-Y-ZZ-AAA (b), WPMLED25-XX-Y-ZZ-AAA (b), WPLLED15-XX-Y-ZZ-AAA (b), WPLLED25-XX-Y-ZZ-AAA (b), WPLLED45-XX-Y-ZZ-AAA (b), CLCS15, CLCS15-PC, CLCS17, CLCS17-PC, CLCS17S, CLCS17S-PC, CLCS40S, CLCS40S-PC, CLCS40S-HV, CLCS40S-HV-PC, 12SFS-L3C4-UNVZZ [d], 14SFS-L3C4-XXXZZ [d], 18SFS-L3C4-UNVZZ [d], 22SFS-L3C4-XXXZZ [d], 24SFS-L3C4-XXXZZ [d].

(b) - “XX” Represent voltage , can be blank = UNV, 120-277V, HV = high voltage, 347-480V (Espec) “Y” Represent color temperature, can be W = 3000K, blank = 4000K, C = 5000K; “ZZ” Represent can be blank = Bronze, WT = white, BK = black O = Other. “AAA” may be followed by blank PC = photocontrol 120-277V EBP = emergency battery pack 120-277V only.

[d] - XXX represents input voltage, and it can be UNV for input voltage 120-277Vac, or NUV for input voltage 120-347Vac. First Z represents Emergency LED Driver, and it can be EM for product with Emergency LED Driver, or blank for products without Emergency LED Driver. Second Z represents Sensor, and it can be S for product with Sensor, or blank for products without Sensor