


Project		Catalog #		Type	
Prepared by		Notes		Date	



# Neo-Ray

## Define 5

5" LED  
Suspended Pendant  
Direct

### Typical Applications

Office • Education • Healthcare • Hospitality • Retail

### Interactive Menu


- Order Information [page 2](#)
- Product Specification [page 3](#)
- Photometric Data [page 4](#)
- Performance Data [page 4](#)
- VividTune [page 6](#)
- BioUp [page 8](#)



### Top Product Features

- Suspended Slot family in 2", 3", 4" and 5" housing sizes
- Specifiable to the nearest foot
- Satin, Asymmetric and Drop Direct Lensing available
- Independently specifiable Direct / Indirect lumen packages
- 0-10V dimming standard; DALI dimming available
- 2700K, 3000K, 3500K, 4000K, and 5000K correlated color temperatures available
- Available in VividTune and BioUp Technology
- Options to meet Buy American Act requirements

### Dimensional and Mounting Details



additional product diagrams

## Order Information

Icon Key: ∅ Consult factory for availability

SAMPLE ORDER NUMBER: **S125DP-C850D835-C4JB4F0-1T-UDD-F-W-WPS**

Domestic Preference	Series	Light Engine	Lumen Package Down (Lms/ft)	CRI	LED CCT	Suspension Type	Ceiling Type	Mounting HW Color
[Blank]=Standard BAA=Buy American Act	S125DP=Define 5 Direct Pendant S125RDP=Define 5 Regressed Direct Pendant	-C=Core -H=High Performance -V=VividTune ∅ -B=BioUp	375D=375 Lms/ft (2.9W/ft) 610D=610 Lms/ft (4.8W/ft) 850D=850 Lms/ft (6.7W/ft) 1090D=1090 Lms/ft (8.8W/ft) 1270D=1270 Lms/ft (10.6W) —D=Custom Lms/ft ∅	8=80 9=90 B= BioUp	27=2700K 30=3000K 35=3500K 40=4000K 50=5000K 2765=2700K-6500K 3050=3000K-5000K 2750=2700K-5000K	-C4=4ft Aircraft Cable -C10=10ft Aircraft Cable -C20=20ft Aircraft Cable -S4=4ft Stem Mount -S8=8ft Stem Mount	JB=Gypsum Board, Junction Box, Structure T1=15/16" T-Grid (ETG) T9=9/16" T-Grid (FTG) TS=9/16" Slot (STG), Tegular (FTT), Interlude (ITG)	(blank)=White B=Black
<b>Notes</b> Only product configurations with this designated prefix are built to be compliant with the Buy American Act of 1933 (BAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	<b>Notes</b> RDP regress of 1" will add an additional 1" to fixture depth.	<b>Notes</b> See performance table for add'l details. Light engine must be consistent across run length. V option requires lumen package of 850 Lms/ft or greater.	<b>Notes</b> 3500K/80CRI/DIP/F Lens. Please refer to scaling data for other variables. For custom lumen output, please refer to additional information on page 4. 375 Lms/ft not available on 2ft fixture length. Refer to BioUp Driver Tables on page 7 for light level availability.	<b>Notes</b> Additional lead-time and cost may apply for 927, 930, 935 and 940 configurations. 92765 and 93050 VividTune configurations require V light engine and W2A driver. B35, B40, B50, B2750 BioUp configurations require B light engine.  CRI ranges from >80CRI to 96CRI in BioUp Technology and is correlated to Color Temperature.		<b>Notes</b>	<b>Notes</b>	<b>Notes</b> White mounting hardware standard

Luminaire Length (Ft)	Max section length	Circuiting	Additional Section Wiring	Voltage	Driver Type	Shielding Down
—F0=Nominal Length	(blank)=12ft (std) /8=8ft	-1=Single Circuit -S=Secondary Circuit	E=Emergency Circuit B1=7W 120-277V EM battery pack B2=14W 120-277V EM battery pack B3=6W UNV Integral T=UL924 EPC Emergency Bypass Relay	-U=Universal (120V-277V) -1=120V -2=277V -3=347V	DD=Standard 0-10V Dimming (1%-100%) 5L=Fifth Light DALI (1%-100%) LH=Lutron HiLume (LDE1 series) 1%-100% EcoSys W2A=2-Channel 0-10V (VividTune and Dynamic BioUp Only) W2D=2-Channel DALI (Dynamic BioUp Only)	-F=Satin White Diffuser -D=Satin Drop diffuser -A=Asymmetric Diffuser
<b>Notes</b> Minimum fixture length is 2ft. Specify to nearest foot in length.  Refer to BioUp Driver Tables on page 7 for minimum allowable lengths.	<b>Notes</b> Individual fixtures configured as 12ft max by default. Continuous runs configured as 8ft max (12ft not available).	<b>Notes</b> Secondary circuit similar to A/B switching. Price adder applies for "S" configuration.	<b>Notes</b> Battery available on fixture ≥ 4ft in length. B1-B2 and T options not compatible with 347V. Standard battery 4ft battery section located in the beginning of the fixture, but can be relocated using the linear product configurator. When configured with secondary circuit, battery test switch will be located in a plate on the direct side of the fixture.  B1 and B2 battery options not available with W2D driver in BioUp Technology	<b>Notes</b> 347V only available with DD driver option.	<b>Notes</b> Use standard 0-10V (DD) for Static BioUp (B35   B40   B50).  2-Channel 0-10V (W2A) available with VividTune (V) and Dynamic BioUp (B2750) only.  2-Channel DALI (W2D) available with Dynamic BioUp (B2750) only	<b>Notes</b> All lensing options are snap-in lenses.

Finish	Integrated Sensor
<b>W</b> = White <b>S</b> = Silver <b>B</b> = Black  <b>RR</b> = Real Red <b>OO</b> = Oasis Orange <b>YY</b> = Yippee Yellow <b>GG</b> = Gracious Green <b>CC</b> = Cyprus Cyan <b>TT</b> = Totally Turquoise <b>BB</b> = Biosphere Blue <b>PP</b> = Perfect Purple <b>VV</b> = Vacation Violet <b>MM</b> = Magic Magenta  <b>C</b> = Custom Color (RAL) <b>CM</b> = Custom Color (Match)	[Blank]=None  <b>WaveLinX Wireless</b> -WLS (formerly WAB) = WaveLinX LITE Wireless Sensor, Occupancy w/ photocell, Independent & Networked -WPS (formerly WAA) = WaveLinX PRO Wireless Sensor Occupancy w/ photocell, Networked -WLN = WaveLinX LITE Wireless Control Node, without Sensor -WPN = WaveLinX PRO Wireless Control Node, without Sensor
<b>Notes</b> Custom Colors (C and CM) are available as ETO. Performance is based off White (W) and may vary with selected finish.	<b>Notes</b> All sensor options are available with (DD) driver options only.  WPS and WLS sensor options are also available with W2A BioUp Dynamic Option.  Refer to Sensor Placement section for additional details.  Integrated Sensors are available with Single Circuit (1) option only.  Integrated Sensors combined with Emergency Circuit (E) require one UL924 Bypass Relay (T) per emergency fixture.  Integrated Sensors combined with a Battery (B) are available with individual Direct/Indirect (DI) luminaires >4ft in length.  Integrated Sensor options with Regressed or Drop lenses available as ETO. Tilemount Sensor is recommended.

## Product Specifications

### Construction

- Available in Flush and Regressed Housing
- Precision cut housing extruded from 6063 aluminum
- Precision cut & welded end-caps ensure a robust and clean construction
- Nominal 2' -12' illuminated sections used in individual fixtures and 2'-8' illuminated sections used in continuous runs

### Finish

- Electrostatically applied polyester powder coat paint

### LED Module

- Modular LED tray assembly comprising reflector and light engine with quick disconnect wire-harness for ease of installation and maintenance over the life of the luminaire

### Light Engine

- Offered with two next generation Neo-Ray light engines delivering industry leading efficacy and long-life
- LED's are available in 2700K, 3000K, 3500K, 4000K or 5000K
- CRI options of either  $\geq 80$ CRI or  $\geq 90$ CRI (Lumen output will be affected - please refer to the lumen adjustment factor table)

### LED Drivers

- LED system coupled with electrical driver
- Traditional electronic drivers are available for 120-277V and 347V applications

### Controls and Integrated Sensors

- Equipped standard with a 0-10V continuous dimming driver. Compatible with most standard dimming devices
- Additional control types are available (DALI & Lutron) at an additional cost
- WaveLinx and Enlighted wireless sensors as well as stand-alone sensors available

### Mounting

- Suspended

### Lengths

- Available in any length (2ft min) with a resolution of 1 foot. Max section length of 12ft (8ft max used on continuous runs and available for individual fixtures)
- Additional fixture lengths are available please consult factory. All lengths are nominal and do not include end caps.

### Corners and Transition Pieces

- Corners and other transition pieces are fully luminous
- Constructed using precision mitered housing and lens components
- Extrusions are welded to ensure a precise and robust assembly
- Standard 90° horizontal corners as well as custom corners are available
- Consult online linear configurator or the factory for precise corner locations and for ordering
- Alternative transition pieces such as T's, Y's, X's, etc. are also available

### Direct Snap-In lensing Options

- Satin Flush - Flush, high diffusion glare-free lens
- Satin Drop - 1" Drop, high diffusion glare-free lens
- Asymmetric - Flush, low-glare Asymmetric lens
- Flush options ship with our patent-pending underlens solution, the proud lens ships with an injection molded end cap to eliminate light leak

### Reflectors

- Precision formed cold-rolled steel reflectors with high reflectivity
- Ultra high reflectivity used with High Performance light engine

### Lumen Maintenance

- 90% (L90) of initial light output at 61,000+ hrs
- 70% (L70) of initial light output at 237,000+ hrs
- Derived from TM-21 standard @25°C for worst case operating conditions

### Custom Lumen Output

- Custom lumen output expressed option in Lumens

per foot (e.g. -725D for 725 Lms/ft down). Refer to additional detail on page 4.

### Electrical

- Dimming provided as standard
- Dimming wires capped with wire-nuts for non-dimming applications
- Optional battery backup options provided
- Default battery location is internal to fixture
- Default emergency section is 4ft in length and located at the beginning of the fixture unless designated elsewhere
- Estimated lumen output = battery wattage \* min efficacy (see performance table)
- The EPC option will bypass local controls and dimming upon loss of normal power. This option is required when the fixture has both integrated sensors and emergency circuiting

### Integrated Sensors

- Please reference page 5 for details

### Weight

- 5.2 lbs per foot


### Approvals

- cULus - listed for damp locations
- Meets NYC requirements
- Meets CEC requirements
- Tested to IESNA LM-79 and LM-80
- Can be used for State of California Title 24 high efficacy luminaire
- DesignLights Consortium® Qualified and classified for DLC Standard and DLC Premium, refer to [www.designlights.org](http://www.designlights.org) for details and listed configurations.


### Warranty

- Five year warranty standard.


## Standard Finish Options



W - White



S - Silver



B - Black




RR - Real Red  
RAL 3020  
Gloss




OO - Oasis Orange  
RAL 2004  
Gloss



YY - Yippee Yellow  
RAL 1018  
Gloss




GG - Gracious Green  
RAL 6018  
Gloss



CC - Cyprus Cyan  
RAL 6027  
Gloss



TT - Totally Turquoise  
RAL 5018  
Gloss



BB - Bioshere Blue  
RAL 5017  
Gloss



PP - Perfect Purple  
RAL 4005  
Gloss




VV - Vacation Violet  
RAL 4008  
Gloss



MM - Magic Magenta  
RAL 4010  
Gloss

RAL & custom colors available as ETO


## Optic Options



Standard Flush Lens



Standard Proud Lens




Regressed Flush Lens



Asymmetric Lens


## Photometric Data - Static White LED Technology

[View IES files](#)




**FILE NAME:**  
S125RDP-S850D835-4F0-1E-UDD-F  
LUMENS: 3128.1 Lms  
LPW: 118.9 LPW  
CCT: 3500K  
WATTS: 26.3 W  
**TEST NUMBER:** P334412

SATIN FLUSH LENS




**FILE NAME:**  
S125DP-S850D835-4F0-1E-UDD-F  
LUMENS: 3289.9 Lms  
LPW: 125.1 LPW  
CCT: 3500K  
WATTS: 26.3 W  
**TEST NUMBER:** P334342

SATIN REGRESSED DIFFUSER



**FILE NAME:**  
S125DP-S850D835-4F0-1E-UDD-D  
LUMENS: 3159.8 Lms  
LPW: 120.1 LPW  
CCT: 3500K  
WATTS: 26.3 W  
**TEST NUMBER:** P334307

SATIN DROP LENS



**FILE NAME:**  
S125DP-S850D835-4F0-1E-UDD-A  
LUMENS: 3324.2 Lms  
LPW: 126.4 LPW  
CCT: 3500K  
WATTS: 26.3 W  
**TEST NUMBER:** P334272

ASYMMETRIC FLUSH LENS

## Photometric Overview and Performance Data

### Direct Performance Per Linear Foot at 3500K/80CRI

Nominal Output	Standard		High Performance		VividTune	
lms/ft	W/ft	lm/W	W/ft	lm/W	W/ft	lm/W
375	2.9	133	2.9	136	3.0	130
610	4.8	134	4.4	140	4.9	130
850	6.7	131	6.1	141	6.7	129
1090	8.8	129	8.1	138	8.9	125
1270	10.6	124	9.7	132	10.7	121

### LUMEN ADJUSTMENT CALCULATIONS

#### Example 1 - Adjusted Lumen Output

Nominal Lumen Output selected = 1025 lms/ft (based on standard of 3500K/80CRI)  
Lumen Adjustment Factor = 0.801 (2700K/90CRI desired)

Adjusted Lumen Output = Nominal Lumen Output x Lumen Adjustment Factor  
Adjusted Lumen Output = 1025 lms/ft x 0.801 = 821 lms/ft

#### Example 2 - Custom Lumen Output based on Required Lumens Per Foot

Total light output (4ft) requirement of 2800 lms, desired CCT and CRI of 4000K/80CRI

Total required lumens per foot @ 4000K = 2800 lms / 4 ft = 700 lms/ft  
Lumen Adjustment Factor = 1.018 (Requirement based on 4000K / 80CRI)

Total required lumens per foot @ 3500K / 80CRI = 700 lms/ft ÷ 1.018 = 688 lms/ft

Estimated efficacy = 121 LPW (find nearest value using table above)

Estimated power consumption = 688 lms/ft ÷ 121 lm/W = 5.69 W/ft


### Custom Lumen Output

Total Light Output Range (lms/ft)

CCT	Lumen Adj Factors		Direct Output Range	
	80CRI	90CRI	80CRI	90CRI
2700K	N/A	0.792	N/A	297-1006
3000K	0.943	0.815	354-1198	306-1035
3500K	1.000	0.861	375-1270	323-1093
4000K	1.010	0.892	379-1283	335-1133
5000K	1.010	0.892	379-1283	335-1133

If your requirement is expressed in power consumption (W/ft) rather than light output, you can use the power to lumen output curves to convert power consumption to light output for specification. Efficacy for custom lumen outputs can be estimated using lumen output curves or with the use of our online custom lumen output tool.

Corner Transitions



Integrated Sensor Details and Placement

Sensor Type	Wireless	Sensor Integration	Sensor Mounting	Ordering Code
WaveLinx Pro	Yes	Integral to Fixture	Mounted in solid cover	WAA
WaveLinx Lite	Yes	Integral to Fixture	Mounted in solid cover	WAB
Enlighted	Yes	Integral to Fixture	Mounted in illuminated lens	LWIPD1
Stand-Alone SVPD1	No	Integral to Fixture	Mounted in solid cover	SVPD1

Optional standalone and wireless connected integrated sensors require use of the DD (0-10V) driver. WaveLinx and Enlighted sensors require additional system hardware (not provided) for full functionality.

Standard sensor layout is shown below. Please refer to sensor coverage pattern diagrams to ensure proper coverage for the application. Standard configurations are available in both individual fixtures and in continuous runs. Default spacing is based on the maximum fixture length of 12ft and can be changed to 8ft sensor spacing for additional coverage by selecting the 8ft max fixture length option when ordering.

For additional information integrated sensors and connected lighting, please visit [Cooper Lighting Solutions's Connected Lighting Website](#).

- ☐ Standard Sensor with Luminaire Control
- ☒ Auxiliary Sensor used for Sensor Coverage (wireless systems only)

INTEGRAL SENSOR

≤8ft Individual

☐

>8ft Individual

☐ ☒

Note: When 8ft max section length is used on individual fixtures > 8ft, sensor placement follows logic for continuous run.

Beginning of Run (BOR)

☐

Intermediate Section (INT)

☐

End of Run (EOR) > 4ft

☐ ☒


End of Run (EOR) ≤ 4ft

☐



## Define 5 Pendant LED with VividTune Tunable White

VividTune tunable white luminaires deliver high-quality light in a broad range of continuously variable color temperatures and intensities. Create a dynamic environment by adjusting the ambient light warmer or cooler to influence mood, support the task at hand, or create a dramatic ambience. The ability to control correlated color temperature and intensity separately using simple controls is the next evolution of LED lighting for the commercial, educational, healthcare and hospitality space. The unparalleled flexibility and number of available lighting environments enable users to find the right light with tunable white.




## Performance Data\*

Tunable White - Lumen Adjustment Factors				
CCT	3000K-5000K		2700K-6500K	
	80 CRI	90 CRI	80 CRI	90 CRI
2700K	-	-	0.868	0.741
3000K	0.894	0.736	0.893	0.771
3500K	0.946	0.804	0.924	0.809
4000K	0.993	0.868	0.944	0.835
4500K	1.002	0.883	0.961	0.857
5000K	1.002	0.883	0.974	0.874
6500K	-	-	0.988	0.897

Example of Approximate Lumen Calculation			
	Standard Catalog #	VividTune 80 CRI Catalog #	VividTune 90 CRI Catalog #
CCT Setting	S125DP-C1090D835-X-UDD-F-W	S125DP-V1090D83050-X-UW2A-F-W	S125DP-V1090D93050-X-UW2A-F-W
3000K	-	3898	3209
3500K	4360	4125	3505
4000K	-	4329	3784
4500K	-	4369	3850
5000K	-	4369	3850

## Controlling VividTune Tunable White

VividTune luminaires make tunable white more accessible by using simple and familiar controls. From wall dimmers to wireless controls, VividTune tunable white luminaires are compatible with industry standard 0-10V dimming controls. A single 0-10V dimming input is used to control intensity (brightness) while a second 0-10V dimming input is used to adjust CCT. For suggested control configurations, go to [www.cooperlightingsolutions.com](http://www.cooperlightingsolutions.com) for tunable white application guides.



## Example of Lumen Adjustment Calculation

S125DP-V1090D83050-X-UW2A-F-W  
at 80 CRI tuned to 3500K

Adjusted Lumen =  
published lm x adjusted lm factor

Adjusted Lumen = 4360 x 0.946

Adjusted Lumen = 4125 lm

\* Lumen adjustment factors are for reference and may be different for each product selected. Refer to IES files for actual performance data on each.

## BioUp Photometry

**Legend:** • Available  
- Unavailable

5in	DIRECT	
Nominal Output	BioUp Light Engine	B35 efficacy
lm/ft	W/ft	lm/W
375	-	-
610	5.9	103.4
850	8.6	98.8
1090	11.1	98.2
1270	15.0	84.7

0-10V						
Availability						
Lumens/ft		375	610	850	1090	1270
Fixture Length	2	-	-	•	•	•
	3	-	•	•	•	•
	4	-	•	•	•	•
	5	-	•	•	•	•
	6	-	•	•	•	•
	7	-	•	•	•	•
	8	-	•	•	•	•
	9	-	•	•	•	•
	10	-	•	•	•	•
	11	-	•	•	•	•
	12	-	•	•	•	•

DALI						
Availability						
Lumens/ft		375	610	850	1090	1270
Fixture Length	2	-	•	•	•	-
	3	-	•	•	•	-
	4	-	•	•	•	-
	5	-	•	•	•	-
	6	-	•	•	•	-
	7	-	•	•	•	-
	8	-	•	•	•	-
	9	-	•	•	•	-
	10	-	•	•	•	-
	11	-	•	•	•	-
	12	-	•	•	•	-



## Proven Research. Industry Recognized.

# BioUp

Melanopic Lighting



See better




Feel better



Function better



See [BioUp brochure](#) for more details



ANSI/IES RP-46-23


**RECOMMENDED PRACTICE:**  
SUPPORTING THE PHYSIOLOGICAL  
AND BEHAVIORAL EFFECTS  
OF LIGHTING IN INTERIOR  
DAYTIME ENVIRONMENTS  
AN AMERICAN NATIONAL STANDARD

ANSI/IES RP-46-23  
/ TM18 published  
March 2024 based  
on over 40 years of  
research.


"...circadian clock synchronization is paramount to the body's efficient and appropriate functioning." – TM18



BioUp solutions maximize WELL points for Circadian Lighting Design (L03):




**MDER, M-EDI and EML** are key metrics used to quantify non-visual performance of indoor lighting systems.




See [BioUp white paper](#) for more details

**MDER** - Melanopic Daylight Efficacy Ratio (MDER) measures the amount of light stimulating to the melanopsin receptors.

**Standard 4000K LED**  
MDER = .62



**BioUp 4000K LED**  
MDER = .82




## 30% boost Biological impact compared to traditional LED sources

CCT	LED MDER ~83 CRI	BioUp Static		BioUp Dynamic	
		MDER	CRI	MDER	CRI
2700K	0.44	—	—	0.43	95
3000K	0.49	—	—	0.54	94
3500K	0.56	0.71	90	0.71	90
4000K	0.64	0.84	87	0.82	87
5000K	0.77	0.98	84	0.98	84

BioUp enhances the LED spectrum with cyan light at 475nm increasing the biological impact of the light to enhance our circadian rhythm which regulates our sleep/wake cycle, daytime engagement, and mood – **all without distorting visual color impression.**

### Static (non-tunable)

Static BioUp is used when simple Melanopic Lighting is desired at all times.



3500K

or

4000K

or

5000K

Cyan light component always present

Dimming Control




no CCT control needed

Arrow in graph shows BioUp spectrum boost is at 475nm where non-visual biological response is enhanced.

### Dynamic - (Tunable)

Dynamic BioUp is used when Melanopic Lighting is desired to adjust during the day.



Warmer CCT Without Cyan content

Cooler Light With Cyan content

2700K – 5000K

CCT Control

Dimming Control



Control with Wavelinx, 2ch 0-10V, or DALI