

Project		Catalog #		Type	
Prepared by		Notes		Date	



Interactive Menu

- Order Information [page 2](#)
- Color Selections [page 3](#)
- Mounting [page 4](#)
- Photometric & UGR Data [page 4](#)

Top Product Features

- PrentaLux 300's are a series of decorative products that utilize Cooper Lighting's 3D Printing technology using an A-19 LED lamp base.
- Modern form available in 8 standard opaque colors and 4 standard translucent colors with additional On-Demand colors available with possible additional costs and lead times. Please consult factory.
- A19 Lamp based, E26 socket: Frosted lamp, Filament lamp, or no lamp (lamp is provided by others up to 50W), options.
- Voltage is 120V only.
- 3D printed mounting canopy available in disk or conical shape.
- Black or white power cord.
- BAA compliant. RoHS compliant.
- [Declare compliant](#)
- LBC Red List Free
- Finishes available on [Material Bank](#)
- 5 Year Warranty

PrentaLux

303

A-19 LED Lamp Based Luminaire Decorative

Typical Applications

- Hospitality • Office • Commercial • Education • Retail • Healthcare
- National Accounts • Residential • Multi-family

Certifications



Filament only.
See page 6



LIVING
BUILDING
CHALLENGE


Features




Awards



Dimensions



Scale



Order Information

SAMPLE CATALOG NUMBER: PRLX-303-FR-120-SLVR-SMGY-CB-BK

--	--	--	--	--	--

Domestic Preferences	Brand	Series	Source	Voltage	Shade Color
[Blank] = Standard BAA = Buy America Act	PRLX	303	NB = No Lamp Supplied (Lamp by others) FIL = A19, E26 LED Filament lamp, 2700K (60W incandescent equivalent) FR = A19, E26 LED Frosted lamp, 3000K (60W incandescent equivalent)	120 = 120V Voltage	Standard Transparent/Translucent Colors TRWH = Translucent White DIFF = Diffuse CLER = Clear SMGY = Smokey Gray Standard Opaque Colors: WHITE = White BLAK = Black GRAY = Gray ROSE = Rose CAPP = Cappuccino SAGE = Sage BRNZ = Bronze BRSS = Brass XXXX ² = On-Demand Color
Notes 1. Only product configurations with this designated prefix are built to be compliant with the Buy American Act of 1933 (BAA). Please refer to DOMESTIC PREFERENCES website for more information. Components shipped separately may be separately analyzed under domestic preference requirements.	Notes	Notes	Notes 1. A19 lamps up to 50W may be used in these fixtures (supplied by others). 2. Dimming is determined by lamp selected	Notes	Notes 1. See page 3 for color options. 2. On-Demand colors available with possible extended lead times and additional costs. Consult factory. See page 3 for additional color options.

Continue here to make complete selections

--	--	--

Top Finial Color	Canopy	Cord Color
TFIN ¹ = Top Finial Color Same as Outer Shade Color (Recommended) Standard Top Finial Colors: TFWHITE = White TFBLAK = Black TFGRAY = Gray TFROSE = Rose TFCAPP = Cappuccino TFSAGE = Sage TFBRNZ = Bronze TFBRSS = Brass XXXX ² = On-Demand Color	DW = Disk - White DB = Disk - Black DC = Disk canopy matches outer shade color (opaque color only) CW = Conical - White CB = Conical - Black CC = Conical canopy matches outer shade color (opaque color only)	BK = Black power cord and black socket WH = White power cord and white socket
Notes 1. Translucent White (TRWH) Outer Shade gets White (WHITE) Top Finial by default Diffuse (DIFF) Outer Shade gets White (WHITE) Top Finial by default Clear (CLER) Outer Shade gets White (WHITE) Top Finial by default Smokey Gray (SMGY) Outer Shade gets Black (BLAK) Top Finial by default 2. On-Demand colors available with possible extended lead times and additional costs. Consult factory. See page 3 for additional color options.	Notes	Notes

Product Specifications

Construction

- PrentaLux 300s series consist of a lamp / socket combination that uses an A-19, E26 Socket LED lamp base and a proprietary additive manufacturing process for the polycarbonate shade and components.
- 300 series shades utilize a proprietary, impact resistant polycarbonate for maximum durability
- The polycarbonate used for PrentaLux fixtures is bio-circular and thermally, mechanically and optically optimized for professional/commercial installations. Designed, engineered, and printed in the United States.

LED Lamp

- Available in Filament based LED lamp, Frosted based LED lamp, or no lamp (up to 50W supplied by others), options.
- Frosted LED lamp is 15W (equivalent to 60W incandescent lamp). 15,000 hour lamp life. 3000K @90 CRI. Output is 800 lumens. E26 base A19 lamp shape. Dimmable. Efficacy is 53.3 LPW.
- Filament LED lamp is (15W equivalent to 60W incandescent lamp). 15,000 hour lamp life. 2700K @90 CRI. Output is 800 lumens. E26 base A19 lamp shape. Dimmable. Efficacy is 53.3 LPW.
- Fixture is rated for lamps up to 50W (by others)
- Dimming is determined by the lamp selection

Optics

- Output determined per shade shape, color and transparency/translucency/opaqueness. See polar plots and UGR data on page 4.
- 300 series fixtures include an inner diffuser to create a consistent illumination with transparent or translucent outer shades.
- The 300 series pendants are designed for transparent and translucent outer shades. These options should be selected for maximum impact.

Electrical

- Standard 120V.

Mounting

- Mounting options include UL certified cord and option of 3D printed disk shape or conical shape mounting canopy.

Finish

- Shade available in 8 standard opaque colors and 4 standard transparent/translucent colors with additional On-Demand colors available. Additional costs and lead times may apply. Please consult factory.
- The 'Finial' recommendation is to match the outside shade color, with the following exceptions: When outer shade is transparent or translucent, an opaque finial color must be chosen. Black finial is default selection for Smokey Grey Outer Shade color and White finial is default selection for Clear Outer Shade color.
- Finishes are available for review on [Material Bank](#) under Cooper Lighting Solutions PrentaLux brand.

Lengths

- Fixture comes with 10ft cord. Lengths up to 25 ft possible. (Consult factory for length longer than 10ft as longer lead times apply).

Weight

- Product is light weight and much easier to install than traditional pendants.
- 303 fixture weighs approximately 2.3lbs

Environment

- Suited for 25° ambient. Dry location only.


Compliance

- All products are light weight and much easier to install than traditional pendants.
- Filament material is UL certified.
- Declare Compliant, LBC Red List Free, ISCC certified
- BAA compliant
- RoHS compliant
- Not to be installed in food prep areas and hazardous environments which may expose the product to pollutants such as oil, grease, or VOCs.
- IK02 impact rated. Not for installations in locations such as gymnasiums, arenas, sports complexes, multi-purpose rooms, and any other locations where the fixture potentially will be subject to impacts from external sources.


Sustainable Product Specifications

- PrentaLux 3D printed parts are produced with at least 55% mass balanced bio-circular materials.
- 70% of the 303 lighting fixture is made of 3D printed material.
- ISCC certified. Certification applies only to 3D printed material. See page 7.
- Declare compliant
- LBC Red List Free
- See pages 6-7 for additional sustainability details.

Mounting - Canopy Options



Canopy Colors



Standard Transparent/Translucent Shade Colors


Not available for Top Finial




CLER - Clear



DIFF - Diffuse White



TRWH - Translucent White



SMGY - Transparent Smokey Gray


Standard Opaque Shade & Top Finial Colors




WHITE - White



BLAK - Black



GRAY - Gray




ROSE - Rose



CAPP - Cappuccino



SAGE - Sage




BRNZ - Bronze



BRSS - Brass

On-Demand Transparent Shade Colors


These special color options may have extended lead times and/or additional costs. Please consult factory. Not available for Top Finial



TRBL - Transparent Blue




TRGR - Transparent Green



TROR - Transparent Orange



TRYE - Transparent Yellow



TRRE - Transparent Red

On-Demand Opaque Shade & Top Finial Colors

These special color options may have extended lead times and/or additional costs. Please consult factory.




ENGR - Enamel Green




MEGR - Metallic Green




MCHA - Matcha




STBL - Steel Blue




MEBL - Metallic Blue




MYBL - Misty Blue




DKGY - Dark Gray




SLVR - Silver



STBR - Stone Brown



MEPU - Metallic Purple



RGLD - Rose Gold



CITR - Citrona



CRWH - Cream White



BURG - Burgundy

Finial Color Recommendations




TFIN -
Top Finial Color Same
as Outer Shade Color





TFWHT - White
(if CLER Outer Shade Color
option chosen, White top
finial is recommended)



TFBLK - Black
(if SMGY Outer Shade
Color option chosen,
Black top finial is
recommended)



Photometric Data

PRENTALUX - 303					
303 - Frosted Lamp			303 - Filament Lamp		
Filename	303-FR-120-GDME-DC.ies		303-FIL-120-GDME-DC.ies		
Test No.	G3-2203-583-6		G3-2203-583-5		
Lumcat	303-FR-120-GDME-DC		303-FIL-120-GDME-DC		
Lumens	252.1 Lm		172.3 Lm		
Input Watts	7.37 W		7.52 W		
Efficacy	34.2 Lm/W		22.9 Lm/W		
CCT	3000K		2700K		
SC (0/90/45)	1.21 / 1.21 / 1.14		1.49 / 1.48 / 1.36		


UGR Data

Fixture Type	CCT	UGR [CIE 190:2010] ⁽¹⁾ (4H, 8H; Reflectance: 70%Ceiling, 50% Wall, 20% Ref. Plane		MAX LUMINANCE [45-90 DEG FROM NADIR] (2) (CD/M^2)	
		90 CRI		90 CRI	
		Frosted	Filament	Frosted	Filament
303	3000K (frosted) /2700K (filament)	5.20	4.10	648	531

Notes: (1) For other UGR data for room or reflective ceiling plans please see technical data on website. (2) For other CCT please see technical data on website.

(3) Averages taken over different colors. Tables available upon request.

PrentaLux is committed to making sustainable lighting a reality



Sustainability

PrentaLux is setting a new benchmark for sustainability in performance lighting. We are deeply committed to reducing CO2 emissions as a vital part of our efforts to combat climate change. Our ambition is to become truly circular in our 3D printing activities. PrentaLux products maximize sustainability by reducing carbon emissions, reducing components and assembly time through the innovative design and technology of 3D printing, reusing our misprints that reduce our carbon footprint, and by utilizing recycled plastics and repurposed waste from food processing and wood pulp industries as the feedstock for PrentaLux 3D printing filaments.



REDUCE

3D printing can save up to 76% lower carbon emissions on material supply and manufacturing. This data is based on a lifecycle comparison of a traditionally manufactured downlight and a 3D printed downlight.



REDUCE

Up to 28% lower carbon emissions in transport. PrentaLux products are manufactured in the US to improve lead times and lessen transportation costs, reducing carbon emissions compared to traditionally manufactured products *(based on a downlight comparison study)*



REUSE

The cardboard and paper packaging materials used to ship PrentaLux products, are themselves, 80% recycled paper at the very least.



RECYCLE


Our 3D printed parts are created with over 55% recycled or bio-circular materials.

Material Sustainability through Production and Supply Chain



Each of our 3D printing manufacturing plants have been audited by the ISCC (International Sustainability and Carbon Certification) organization to verify the implementation and use of environmentally, socially and economically sustainable production and materials.


** PrentaLux products will convert to printing our 3D parts with over 55% recycled or bio-circular materials (using an ISCC certified mass balance approach). Bio-circular materials are raw materials from ISCC Plus certified waste streams and residues including tall oils from the wood processing industry or used cooking oil from the food processing industry.*



CARBON NEUTRAL

PrentaLux products are produced in a carbon neutral manufacturing facility where over 99% of generated waste is diverted from landfills

70%
of 303 fixture is made
with 3D Printed material



55%

PrentaLux 3D printed parts are
produced with at least 55% mass
balanced bio-circular materials

Material Transparency



The ILFI (International Living Future Institute) has created a program where manufacturers can disclose the components or "ingredients" of a product. This disclosure has a rating system that shows transparency in the materials chosen in developing products, and whether there are any chemicals of concern, to help meet the requirements of leading green building standards that support human and environmental health.



LBC Red List Free

- Disclosed 100% at content inventory of 100ppm
- Suitable as a compliance pathway for LEED v4.1 Material Ingredients credit Option 1 Material Ingredient Reporting
- Suitable as a compliance pathway for WELL v2 Feature X07 Materials Transparency Parts 1 and 2

To see the full listing of Cooper Lighting products that participate in Declare, click [here](#).

Declare.

PrentaLux LED Lamp Base Luminares
Cooper Lighting Solutions

Final Assembly: Littlestown, Pennsylvania, USA
Life Expectancy: 10 Year(s)
End of Life Options: Recyclable (100%)

Ingredients:

Carbonic acid, polymer with 4,4'-[1,1'-methylenebis[4-oxo-1,4-dioxane-2,5-dione]]-2,2'-diyl; Polyacrylic acid; Poly[imino(1,6-dioxo-1,6-hexenediyl)imino-1,6-hexenediyl]; Zinc; copper; compound with lanthanum and nickel (4:1:1)

Living Building Challenge Criteria: Compliant

H3 Red List:

■ LBC Red List Free % Disclosed: 100% at 100ppm
□ LBC Red List Approved VOC Content: Not Applicable
□ Declared

H10 Interior Performance: Not Applicable
H14 Responsible Sourcing: Not Applicable

COO-0003

EXP 01 SEP 2024
Original Issue Date: 2023

MANUFACTURED BY COOPER LIGHTING SOLUTIONS
INTERNATIONAL LIVING FUTURE INSTITUTE™ [living-future.org/declare](#)