


Project		Catalog #		Type	
Prepared by		Notes		Date	



## Metalux

### 22FPX LED Panel

2' x 2' Configurable LED Edge Lit Panel  
Recessed in Insulated Ceilings or  
Suspended/Surface Mount

#### Typical Applications

- Commercial Office Spaces • Schools • Healthcare
- Retail Merchandising Areas

#### Interactive Menu

- Order Information [page 2](#)
- Photometric Data [page 4](#)
- Control Solutions [page 5](#)
- Product Warranty

#### Top Product Features

- Variety of controls and emergency battery pack options in all sizes
- Low profile perfect for renovation or new construction
- Contractor friendly, quick and easy install
- Available in 3000K, 3500K, 4000K, and 5000K CCT
- Standard and high efficacy options available
- Options to meet Trade Agreements Act requirements


#### Product Certification



#### Product Features



#### Dimensional and Mounting Details



Shown with either Sensor OR Integrated  
Emergency test switch.  
For units with both Emergency and Sensor  
there is one holder on each end.

[additional  
product diagrams](#)

## Order Information

SAMPLE ORDER NUMBER: **22FPX-32-L840-WLS**

Domestic Preferences	Rating	Width/Length	Series	LED Lumen Output	Voltage	Fuse Options	Emergency	CCT
Domestic Preferences <sup>(1)</sup>	Rating	Width/Length	Series	LED Lumen Output <sup>(3)</sup>	Voltage <sup>(5)</sup>	Fuse Options <sup>(7)</sup>	Emergency	CCT
[Blank]=Standard TAA=Trade Agreements Act	[Blank]=Standard ATW-SW4=Chicago Rated <sup>(2)</sup>	22=2' x 2'	FPX=Configurable Flat Panel	21=2100 25=2500 <sup>(4)</sup> 32=3200 42=4200	[Blank]=Universal Voltage 347V=347 Volt <sup>(6)</sup>	[Blank]=None GL=Single Element Fuse GM=Double Element Fuse	[Blank]=None EL7W=7-watt 120V-277V emergency battery pack <sup>(8)</sup> EL10W=10-watt 120V-277V emergency battery pack <sup>(8)</sup> EL14W=14-watt 120V-277V emergency battery pack <sup>(8)</sup> EL10WSD=10W emergency battery pack with self-diagnostic installed <sup>(8),(11)</sup> ETRD=Emergency Transfer Relay with dimming control <sup>(9),(10)</sup> WNPS=WaveLinX wireless UL924 Normal Power Sensing (NPS) capable device <sup>(19)</sup>	L830=3000K <sup>(12)</sup> L835=3500K L840=4000K L850=5000K
<b>Notes</b> (1) Only product configurations with this designated prefix are built to be compliant with the Trade Agreements Act of 1979 (TAA). Please refer to <a href="#">DOMESTIC.PREFERENCES</a> website for more information. Components shipped separately may be separately analyzed under domestic preference requirements. Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.	<b>Notes</b> (2) No sensor or installed FLEX options available with ATW-SW4 option.			<b>Notes</b> (3) Lumens are approximate. Use IES files for actual performance. (4) 2500 lumens only available in HE.	<b>Notes</b> (5) Products also available in non-US voltages and frequencies for international markets. (6) 347V with sensor and/or emergencies only available with HCD or SR.	<b>Notes</b> (7) Not available with the CD driver option.	<b>Notes</b> (8) Factory installed with integral test switch/indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES format photometry for luminaire under emergency operation available. Battery option increases total height by 1 inch. (9) Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others). ETRD option only requires one relay when used on a dimming fixture. 347 not available. (10) These options are only available with HCD and CD drivers. (11) EL10WSD not available with 347V. (19) Must be ordered with WLS or WPS sensor. WNPS cannot be ordered with emergency or relay options such as ETRD, GTR2, ELxxx or GTDU.	<b>Notes</b> (12) 3000K only available 21 and 32 lumen options.


Efficacy	Flex	Driver Type	Number of Drivers
Efficacy	Flex <sup>(14)</sup>	Driver Type <sup>(15)</sup>	Number of Drivers
[Blank]=Standard HE=High <sup>(13)</sup>	[Blank]=None A3/8-4/18GDIM=Flex pre-installed with 5 conductors including ground and dimming leads A3/8-5/18GDIM=Flex with 0-10V Dimming leads and Blue for alternate wiring. See below for details.	[Blank]=CD HCD=0-10V Driver (1%-100% Dimming) SLTD=DALI Driver (5%-100% Dimming) SLTHD=DALI Driver (1%-100% Dimming) SD=Step Dimming Driver (50% or 100% Dimming) LH=Lutron HiLume (LDE1 series) 1%-100% EcoSystem Driver with Soft-on Fade to Black dimming <sup>(7)</sup> SR=Sensor-ready Driver (1%-100% Dimming)	[Blank]=1 Driver
<b>Notes</b> (13) 2500 lumens only available in HE.	<b>Notes</b> (14) Multiple options available in online configurator. See additional notes on Flex below.  <b>Flexible Metal Conduit Options</b>  Flex options available for 0-10V dimming control, DALI dimming control, emergency and night light functions. 72-inch factory-installed and pre-wired to driver, fitted to luminaire housing access plate with 90° enclosed FMC connector. Not all options may be combined and installation ratings vary by type. A3/8-4/18GDIM series notes: Factory installed dimming option 3/8" flexible metal conduit with 2-#18 power and ground wires and 2-#18 UL-listed jacketed 0-10V +/- control wires. Meets UL 66, 83, 1479, 1569, 1581, 2556. NEC® 250.118, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, 72; Federal Specification A-A-59544 (formerly J-C-308); all applicable OSHA and HUD Requirements. UL Classified 1-, 2-, and 3-hour through penetration with applicable fire stop product (not included). May be surface mounted, fished and/or embedded in plaster. Cable tray and approved raceway rated, install per NEC®, Environmental Air-Handling Space Installation per NEC® 300.22(C).	<b>Notes</b> (15) Products also available in non-US voltages and frequencies for international markets.  Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (F) Consult Marketplace Options - Lutron system pages for additional details and compatibility. Compatible only with driver series shown, and may require two or more drivers. Requires field commissioning to operate or dim. Contact Lutron at <a href="#">www.lutron.com</a>	

Integrated Sensing Systems	Options	Packaging
Integrated Sensing Systems	Options	Packaging
[Blank]=No Sensor WLS (formerly WAB)=WaveLinX LITE Wireless Sensor, Occupancy w/ photocell, Independent & Networked <sup>(16),(B)</sup> WPS (formerly WAA)=WaveLinX PRO Wireless Sensor, Occupancy w/ photocell, Networked <sup>(17),(A)</sup> WLN=WaveLinX LITE Wireless Control Node, without sensor <sup>(16),(B)</sup> WPN=WaveLinX PRO Wireless Control Node, without sensor <sup>(17),(A)</sup>	[Blank]=None SUS=Suspension Mount <sup>(18)</sup>	[Blank]=Unit Pack PAL=Job Pack, out of carton
<b>Notes</b> (17) WPS sensor and WPN node to be used with CD or HCD driver. (16) WLS sensor and WLN node to be used with CD or HCD driver.  Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (A) Consult WaveLinX PRO system pages for additional details and compatibility. (B) Consult WaveLinX LITE system pages for additional details and compatibility.	<b>Notes</b> (18) Option is not required for suspension of the 2x2 but is recommended.	

Accessories/Ordering Information <sup>(20)</sup>


**Surface Mount Kit** – Surface box with sufficient clearance for all options

Catalog	UPC
FPXSURF22	080083867387
<b>Notes:</b> Surface mount kit is deep enough to fit all available options. Cannot be used with the FPSURF version.	



## Ceiling Retention

Catalog	UPC
FPEQ	080083802685
Required by some local codes Order one set for each fixture (Four clips per kit)	



## Load Data (CD most common driver)

Thd	14%
Power Factor	0.96
Weight	9.4 lbs.
Low Temp. Start	-20°C

## Suspension Kit

Catalog	UPC	Description
FPSUS24	080083258895	2 point Y-hanger suspension kit includes aircraft cable, carabiner, ceiling connection, SO cord, cord connectors and round 4" J-box cover plate
Mounting height from ceiling <b>Min.</b> = 7-1/4" [184mm] <b>Max.</b> = 27" [286mm]		

## Shipping Data

Size	Wt.	Pallet (30" x 56")
2' x 2'	12 lbs.	18

## Drywall Frame Kit

Catalog	UPC
DF-22W-U	662401232963

**Notes:** (20) Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

## Product Specifications

## Construction

- Narrow aluminum bezel is tightly held to a die-formed code gauge steel back plate with flush perimeter and internal gasket
- Seamless corners to maximize the light emitting surface with a refined finish

## Mounting

- Integral grid clips and separate suspension clips provided for installation flexibility when additional retention is required
- Junction box constructed of code gauge galvanized steel with an easy access hinged door
- Multiple trade size knockouts provided on the top and sides
- Stock luminaire is less than 2.5" for use in shallow plenum or low ceiling spaces
- Surface mounting kits available
- Suspension options available from factory
- Factory installed flexible cable with dimming leads options available

## Limited Warranty

- Five year limited warranty

## Integrated Controls

- Standard with 0-10V dimming driver (10% standard, 1% optional)
- Integrated WaveLinX options provide wireless individual fixture control and enable code compliance, increased energy savings, grouping of fixtures, and connection to WaveLinX control systems
- DALI 2.0, Lutron, and step-dimming available

## Electrical

- Standard and High Efficacy models available
- LED's available in 3000K, 3500K, 4000K, and 5000K with a minimum of 80 CRI
- Color accuracy  $\leq 3$ -Step MacAdam ellipse (SDCM)
- Projected lumen maintenance based on TM21 testing standards is L73 > 60,000 hours

## Optical Shielding

- Light guide with specialized features to optimize light extraction
- White frost lens with smooth pattern for uniform illumination
- Scratch and impact resistant


## Compliance

- Indoor luminaires are cULus listed for 25C ambient environments
- IC rated for direct insulation contact
- RoHS compliant
- Damp location listed
- IESNA LM-79 and LM-80 standards compliant
- Can be used for State of California Title 24 high efficacy luminaire
- Meets IP5X rating from the room side with no modification needed
- ATW-SW4 option is available for CCEA (Chicago Plenum) compliance
- Fixture is rated for NSF/ANSI standard 2 - Light fixture for Splash Zone and Non-Food Zone

## Emergency Options


- 120V-277V integral emergency battery pack comes in 7-watts, 10-watt, or 14-watts
- Self-diagnostic emergency battery available in 10 or 14-watts (NFPA 101® Life Safety Code®)
- Constant power to the LED system for controlled, predictable discharge
- Integrated test switch/indicator light visible from floor
- Min. 90-minute backup period for code compliance
- Integral emergency transfer relay available for generator equipped power systems
- WNPS enables Normal Power Sensing (NPS) functionality, allowing detection of normal power availability as part of a WaveLinX EM solution
- NPS must be ordered with WaveLinX LITE or PRO sensor to enable wireless sensing EM solution
- Order standard product with compatible emergency control device (ESP-P) when pairing NPS enabled luminaires in any space
- NPS luminaires meet UL924 requirements

## Photometric Data

[View IES files](#)



### 22FPX-25-L840-HE-WPS

Electronic Driver  
Linear LED 4000K  
Spacing criterion: (II) 1.25 x mounting height,  
(⊥) 1.24 x mounting height  
Lumens: 2539  
Input Watts: 19.8W  
Efficacy: 128.2 LPW  
Test Report: 22FPX-25-L840-HE-WPS.IES



### 22FPX-32-L840-WPS

Electronic Driver  
Linear LED 4000K  
Spacing criterion: (II) 1.25 x mounting height,  
(⊥) 1.24 x mounting height  
Lumens: 3543  
Input Watts: 30.4W  
Efficacy: 116.6 LPW  
Test Report: 22FPX-32-L840-WPS.IES



### 22FPX-42-L840-WPS

Electronic Driver  
Linear LED 4000K  
Spacing criterion: (II) 1.25 x mounting height,  
(⊥) 1.24 x mounting height  
Lumens: 4545  
Input Watts: 40.3W  
Efficacy: 112.8 LPW  
Test Report: 22FPX-42-L840-WPS.IES

## Energy and Performance Data by Catalog Number

Catalog	Delivered Nominal Lumens	Watts	Efficacy (lm/W)	Input Current (A)	
				120V	277V
22FPX-21-L840-HCD	2494	21.5	116.0	.18	.08
22FPX-25-L840-HE-HCD	2551	20.5	124.6	.17	.07
22FPX-32-L840-HCD	3560	31.2	114.1	.26	.11
22FPX-42-L840-HCD	4567	41.5	110.1	.35	.15
22FPX-32-L840-WPS	3543	30.4	116.2	.25	.11
22FPX-42-L840-WPS	4545	40.3	112.8	.34	.15

### Lumen Calculator

CCT Multiplier	80 CRI
3000K	0.94
3500K	1.00
4000K	1.00
5000K	1.03


### Example of Lumen Adjustment Calculation

22FPX-32-L830-HCD  
at 3000K

Lumen Adjustment Factor = 0.94

Total Light Output =  
3,560 lm x 0.94 = 3,360 lm  
Efficacy =  $\frac{3,360 \text{ lm}}{31.2 \text{ W}}$  = 107.7 lm/W

## Dimensional and Mounting Details



## Control Solutions

- WaveLinX LITE wireless
- WaveLinX PRO wireless
- WaveLinX CAT wired
- WaveLinX Wired



The FPX with WaveLinX offers no-hassle lighting control with multiple luminaire level control solutions.




**WaveLinX PRO** is a wireless lighting control solution, for connected spaces, that significantly reduces a building's energy consumption. From a single floor to an entire campus, WaveLinX PRO connects more than lighting assets; it shares aggregated sensor data with the WaveLinX CORE platform and other building systems, so building owners can improve operations, spaces environment, and tenants' experience. WaveLinX PRO offers a rich portfolio of wireless devices, WaveLinX PRO-enabled luminaires, and an intuitive WaveLinX mobile app for office, education, warehouse, and parking garage applications.




**WaveLinX LITE** is a cost effective, wireless digital lighting control solution, with out-of-the-box functionality, that saves energy and meets code. It's designed for applications that require occupancy-based, daylighting, or manual light control. Customize installations for office, education, warehouse and parking garages using the secure, simple mobile app.

### Integrated Sensor Coverage Pattern

TOP VIEW:




SIDE VIEW:




**Note:** Installation of integrated sensors within 3-ft (1m) of HVAC air vents is not recommended. The pattern shown is intended solely as a general guide and is not to scale.

With Integrated WaveLinX Sensor



With Integrated WaveLinX Node



Add a hidden WaveLinX sensor node (WPN, WLN) to your space lighting design!

**Allows to:**

- Keeps luminaire aesthetics
- Connect fixtures without the realstate to include sensor option such as downlights
- Connect sealed fixtures without a standard sensor option such as products for clinical space.

### Integrated Controls Options

Option	Out of the Box Functionality	Luminaire Level Lighting Control (LLC)	Automatic Dimming Photocell	Occupancy Sensing	CCT Control
WLS	X	X	X	X	
WLN		X			
WPS		X	X	X	X
WPN		X			X

**Note:** WaveLinX utilizes scenes to allow users to change an area's fixtures Correlated Color Temperature (CCT) and intensity using commissioned manual wireless wallstation scene control. To enable CCT adjustments through WaveLinX, include WPS or WPN devices in addition to VividTune or BioUp technologies for integrated fixture control.


The WNPS option is available with WLS or WPS sensors. Must be specified when ordered. Also note that WLS and WPS are also compatible with ESP-L-010-347 and ESP-P-010-347, respectively. Learn more about WaveLinX EM [here](#).

## Systems comparison chart

Cooper Lighting Solutions provides many lighting system solutions designed to satisfy code requirements and meet the unique needs of any project.



**Luminaire with standalone sensor**



**Standalone Spaces WaveLinX LITE**



**Standalone Spaces WaveLinX CAT**



**Networked Spaces WaveLinX PRO**



**Enterprise WaveLinX CORE**

	Luminaire with standalone sensor	Standalone Spaces WaveLinX LITE	Standalone Spaces WaveLinX CAT	Networked Spaces WaveLinX PRO	Enterprise WaveLinX CORE
<b>Occupancy</b>	Yes	Yes	Yes	Yes	Yes
<b>Daylighting</b>	Yes	Yes	Yes	Yes	Yes
<b>Wallstations</b>	–	Yes	Yes	Yes	Yes
<b>Gateways</b>	–	–	–	1 WAC	300 WACs
<b>Devices (MAX)</b>	–	40 per Area (1120 per space)	40 per Area	200 per WAC2	32,500 per CORE Enterprise
<b>Software</b>	–	WaveLinX LITE Mobile App	WaveLinX CAT Mobile App	WaveLinX Mobile App	CORE
<b>Areas</b>	–	28 per Space	Unlimited	50 per WAC2	up to 3,000
<b>Zones</b>	–	16 per Area	16 per Area	16 per Area	up to 9,000
<b>Scheduling</b>	–	–	–	Local	Global
<b>VividTune™</b>	–	–	–	Yes	Yes
<b>Plug-Load Control</b>	–	Yes	Yes	Yes	Yes
<b>Low-Voltage Power</b>	–	–	Yes	Yes	Yes
<b>Integration</b>	–	–	–	–	BACnet, API
<b>Dashboards</b>	–	–	–	–	Energy, Occupancy
<b>Configuration</b>	–	Installer	Installer	Technician	Technician / IT