

Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

FMNL 8" Flush Mount LED Downlight with Night Light

This Flush Mount features two lighting modes: double-toggle any standard switch or dimmer to change between bright downlighting or a warm glowing night light halo. Fixture mounts to 30 / 40 standard or pancake junction boxes or 5 7/8" recessed housings and comes with Paintable Matte White and Matte Black trim rings.

Typical Applications Residential - Multifamily - Hospitality
- Healthcare - Retail

Interactive Menu

- Order Information page 2
- Product Specifications page 3
- Energy Data page 4
- Photometric Data page 4
- Product Warranty

Product Certification



Can be used to comply with California Title 24 High Efficacy requirements.
Certified to California Appliance Efficiency Database under JAB.


Product Features



Top Product Features

- Round 8" Flush Mount LED Downlight with Night Light
- Installs in 30 / 40 junction boxes or 5 7/8" recessed housings
- **Two Lighting Modes:**
 - Downlight is 5-Color SeleCCTable™: 27/30/35/40/5000K (soft white to daylight)
 - Night Light is set to candlelight (2000K)
- Double-toggle wall switch/dimmer (ON/OFF/ON) to change light modes
- **Lumens (@3000K):** 980 (90+ CRI)
- **Dimming:** Flicker free dimming down to 10%
- Comes with 2 Trim Rings inside the box (Paintable Matte White and Matte Black)
- Damp Location Listed
- **Life:** 50,000 hrs of maintenance-free operation
- 5-year warranty

Dimensional and Mounting Details



Order Information

Surface mount downlight mount to junction boxes or 5" / 6" recessed housings (sold separately)

Catalog Number	Module	Lumens (@3000K)	CCT	CRI	Driver/Dimming	Accessory Trim included in Box	Packaging
FMNL809FS5	8-inch Flush Mount LED Downlight with Night Light	980 lm	5-Color Field-SeleCCTable™ CCT: 2700K/3000K/3500K/4000K/5000K	90 CRI	120V 60Hz, LE & TE phase cut 100–10% dimming	Paintable Matte White + Matte Black	Plastic-free Recyclable

Decorative Overlays (Included)



Paintable Matte White




Matte Black

Light Modes

Double-toggle wall switch/dimmer (ON/OFF/ON) to change light modes



Downlight



Night Light



Compatible Junction Boxes³



**Pancake
Steel Round ceiling Pan**
4" Diameter x 13/16"



**Octagon
Steel Light Fixture w/Fan Box**
4" x 4" x 2-1/8"



**Octagon
Steel Light Fixture w/Fan Box**
3-1/2" Diameter x 1-1/2" Deep



**Round
New Work Fixture Box (Plastic)**
4" Diameter x 2-3/18"



**Round
New Work Ceiling Box (Plastic)**
3-1/2" Diameter x 2-3/4"



**Round
Old Work Box (Plastic)**
4-1/4" Diameter flange (3-1/2" I.D.) x 2-5/8"



**Pancake
Steel Round ceiling Pan**
3" Diameter x 13/16"



**Round
New Work Fixture Box (Plastic) w/Bar Hanger**
4" x 2-3/18"



**TP316
For non-metallic cable**
4" x 4" x 2-1/8"



**TP317
For metal clad cable**
4" x 4" x 2-1/8"



**JB4FR2
4" NC JBox for Fire Rated Ceilings**
4" diameter x 5-1/2"
(102mm x 140mm)

³ This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.

Compatible Housings

HALO - 5" Housings⁴

HALO LED Housings	H550ICAT, H550RICAT
Standard Housings	H5ICAT, H5ICATNB, H5RICAT
Shallow Housings	H2550ICAT
Fire Rated Housings	H550FR2ICAT

4. This fixture is UL Certified for use with any 5" diameter recessed housing constructed of steel or aluminum with an internal volume that exceeds 107.9 in³ addition to those noted below and does not exceed the input rating of the housing.

HALO - 6" Housings⁵

HALO LED	H750ICAT, H750RICAT, H2750ICAT, H2750RICAT
Standard Housing	H7ICAT, H7ICATNB, H7RICAT, H7RICT, H7ICATNB
Shallow Housing	H27ICAT, H27RICAT, H2750ICAT
Fire Rated Housing	H750FR2ICAT

5. The fixture is UL Certified for use with any 6" diameter recessed luminaire constructed of steel or aluminum with an internal volume that exceeds 97.4 in³ addition to those noted below and does not exceed the input rating of the luminaire.

Specification Features

Fixture

- Stamped metal fixture frame, a twist-release acrylic lens, and interchangeable trim rings (paintable matte white and matte black included)
- 2 Light Modes: Downlight and Night Light
 - To change between light modes – double-toggle the wall switch/dimmer (ON/OFF/ON)
 - All fixtures will return to downlight mode after being OFF for >3 seconds
- Integral metal heat sink provides passive thermal cooling achieving L70 at 50,000 hrs in IC (insulation contact) and non-IC applications

LED Array

- Color Temperatures (CCT):
 - Night Light is set to 2000K
 - Downlight is 5-Color SeleCCTable™: 27/30/35/40/5000K
- Factory downlight mode default color temperature (CCT) is set to bright white (3000K)
- Color Quality: 90+ CRI (min)
- Backlit LED technology
- Expected Life: L70 at 50,000 hours projected in accordance with TM-21

Optical Assembly

- A collection of low-power LEDs beneath precision-engineered optics provide uniform lighting from behind a low-profile convex lens.
- Removable twist-release polycarbonate lens for easy installation

Driver & Dimming

- Integral 120V 60Hz constant current driver provides noise-free, high-efficiency operation
- Dimmable: Continuous, flicker-free phase cut (leading-edge/trailing-edge - LE/TE) dimming from 100% to 10% output with compatible dimmers
- See this fixture's Dimming Guide for compatible dimmers

Tip: For optimal dimming performance, consider dimmers with low-end trim adjustment; note that some dimmers require a neutral wire in the box

Wiring

- Wire nuts provided for mains connections in junction boxes.
- Included orange LED Quick Connect and E26 medium socket adapter provide mains connections in 5"/6" Traditional socket-based or LED-based recessed housings.
- Reference installation instructions for complete wiring and mounting steps

Electrical Junction Box Mounting

- Installs from below the ceiling into most standard and pancake 30 and 40 (3-½" and 4") round/octagonal junction boxes with included hardware
- May be used in compatible electrical junction boxes in direct contact with insulation, including spray foam insulation
- Installer must ensure compatibility of fit, wiring, and proper mounting in the electrical junction box. This includes all applicable national and local electrical and building codes. Refer to NEMA LSD 57-2013.
- Reference installation instructions for complete wiring and mounting steps

Recessed Housing Mounting

- The included wire nuts, orange LED Quick Connect, E26 medium socket adapter, and torsion springs provide easy mounting to recessed housings (non-California product only)

- Compatible with 5" and 6" new construction or remodel traditional socket-based or LED-based recessed housings
- Suitable for use in IC-rated housings in contact with air-permeable insulation. (Not for use in recessed housings in direct contact with spray foam insulation; refer to NEMA LSD 57-2013)
- Reference installation instructions for complete wiring and mounting steps

Compliance

- cULus certified for US and Canada
- Damp location listed
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant*
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Certified to State of California Title 20, State regulated LED Lamp; reference Modernized Appliance Efficiency Database System (MAEDBS) for State-regulated LED Lamp
- Can be used for State of California Title 24 high efficacy LED compliance under JA8*, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2019 JA8 High Efficacy Lighting

Warranty

- Five-year limited warranty, consult website for details.


www.cooperlighting.com/warranty

Energy Data

FMNL8 - 900 Lumen

Lumens (nominal) Main Light	900LM
Lumens (nominal) Night Light	90-120LM
Input Voltage(VAC)	120
Input Current(A)- Main Light	0.084A
Input Power(W)-Main Light	10W
Input Current(A)- Night Light	0.055A
Input Power(W)-Night Light	6.4W
Driver Efficiency(%)	79
Inrush(A)	<3A
THDi%	<20
PF	>0.9
T Ambient	-30~40
Sound Rating	≤22DB
Efficacy(LPW)	≥90

Photometric Data




FMNL809FS5-3000K

Spacing Criteria (0/90/45):
1.28/1.28/1.40
Beam Angle: 116°
Field Angle: 178°
Lumens: 980 lm
Input Watts: 10.2 W
Efficacy: 96 Lm/W
UGR: 27
Test Report: P1046633

Zonal Lumen	Lumens	% Lumens
0-30	235.2	24
0-40	387.1	39.5
0-60	694.3	70.9
0-90	936.7	95.6
90-180	43.0	4.4
0-180	980	100

TM-30-15	Rf = 92
	Rg = 104
CRI/CIE	Ra = 93
	R9 = 76



FMNL8 5CCT				
CCT	Watts	lumens	LPW	CRI
2700K	10.2	980	96.1	93
3000K	10.2	980	96.1	93
3500K	10.2	980	96.1	93
4000K	10.2	980	96.1	93
5000K	10.2	970	95.1	93
Night Light 2000K	6.7	90	13.4	93

FMNL809FS5-3000K

PRODUCT SPECIFICATIONS	
Lumens	980
Watts	10.2
Lumens Per Watt (Efficacy)	96.1
Color Accuracy (CRI)	93
Light Color (CCT)	3000K