


Project		Catalog #		Type	
Prepared by		Notes		Date	



HALO

HLC Tapered Surface Mount LED Disk Lights

HLC4FS1E-24P • HLC6FS1E-24P

Low-profile 4" and 6" tapered disk lights with 5-color selectability, wet-location rating, and smooth 10% dimming. Mounts directly to junction boxes for a flush, clean ceiling finish. Twist-release lens enables quick installation and CCT selection. Available in economical 24-packs for high-volume installs.

Typical Applications Residential • Multifamily • Hospitality

Interactive Menu

- Order Information [page 2](#)
- Product Specifications [page 3](#)
- Energy Data [page 4](#)
- Photometric Data [page 4](#)
- Product Warranty





Refer to ENERGY STAR® Certified Products List.
Can be used to comply with California Title 24 High Efficacy requirements.
Certified to California Appliance Efficiency Database under JAB.

Top Product Features

- 4" & 6" Surface Mount LED Disk Light (Round)
- Ultra-fast below-the-ceiling installation; no clips or plates needed
- Installs in many 3-1/2" & 4" (30/40) octagonal, or round standard & pancake junction boxes ([See compatibility list](#))
- **5-color Field-SeleCCTable:** (27/30/35/40/5000K); 90+ CRI
- **Brightness (@3000K):** 690 or 970 lumens
- **Dimming:** Dims to 10% (phase cut LE/TE) with compatible dimmers*; 120V input
- Mounting hardware included
- Integral gasket meets AIR-TITE and code compliance for additional energy savings
- Wet location-listied for shower or covered outdoor areas.
- ENERGY STAR® certified
- 50,000 hrs of maintenance-free operation
- 5-year warranty

* Consult the HLC Dimming Guide for dimmer compatibility.












Dimensional and Mounting Details



Order Information

Catalog Number	Module	Lumens (@3000K)	CRI/CCT	Driver	Finish	Packaging
HLC4FS1E-24P	4" LED Disk Light, Bulk 24 Pack	690 lm	90+ CRI, 5-color Field-SeleCCTable™ CCT: 2700/3000/3500/4000/5000K	10% Phase Cut LE/TE Dimming, 120V 60Hz	Matte White	24 pack, Plastic-free Recyclable
HLC6FS1E-24P	6" LED Disk Light, Bulk 24 Pack	970 lm	90+ CRI, 5-color Field-SeleCCTable™ CCT: 2700/3000/3500/4000/5000K	10% Phase Cut LE/TE Dimming, 120V 60Hz	Matte White	24 pack, Plastic-free Recyclable

Compatible Junction Boxes ⁽²⁾

 Octagon Steel Light Fixture w/Fan Box 4" x 4" x 2-1/8"	 Square Steel Deep Box 4" x 4" x 2-1/8"	 Round New Work Fixture Box (Plastic) 4" Diameter x 2-3/16"	 Round New Work Ceiling Box (Plastic) 3-1/2" Diameter x 2-3/4"	 Round Old Work Box (Plastic) 4-1/4" Diameter flange (3-1/2" I.D.) x 2-5/8"	
 4" round surface mount box 4" diameter x 1-1/2" (102mm x 38mm)	 TP316 For non-metallic cable 4" x 4" x 2-1/8"	 TP317 For metal clad cable 4" x 4" x 2-1/8"	 Round ceiling pan ⁽⁶⁾ 4" diameter x 13/16" (102mm x 21mm)	 Round New Work Fixture Box (Plastic) w/Bar Hanger 4" x 2-3/16"	 JB4FR2 - 4" New Construction Junction Box Housing (Suitable for use in Fire Rated Ceiling construction) 4" diameter x 5-1/2" (102mm x 140mm)

2. This is a representative list of compatible junction boxes only. Information contained in this literature about other manufacturers' products is from published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must determine that site conditions are suitable to allow proper installation of the mounting bracket in the box.

3. To ensure proper installation and airtight seal, pan/pancake boxes must be installed completely flush with ceiling material.

Product Specifications

Construction

- Stamped steel

Optics

- Twist-release polycarbonate lens
- Precision engineered optic provides uniform luminance from a low-profile convex lens
- Removable lens for easy install from below installation

LED

- Backlit LED technology
- 5CCT Field Selectable color temperature (2700K, 3000K, 3500K, 4000K, 5000K)
- 90 CRI is standard
- Color accuracy within 7 SDCM at the CCT endpoints, provide color accuracy and uniformity.
- Expected Life: L70 at 50,000 hours projected in accordance with TM-21

Driver

- Integral 120V 60Hz constant current driver provides virtually noise free operation.
- Continuous, flicker-free dimming from 100% to 10% with select leading or trailing edge 120V phase cut dimmers. See dimming guide.
- Dimming to 10% is best assured using dimmers with low end trim adjustment. Consult dimmer manufacturer for compatibility and conditions of use. (Note some dimmers require a neutral in the wallbox.)
- **TIPS:** For optimal dimming performance, consider dimmers with low-end trim adjustment and note that some dimmers require a neutral wire in the wallbox. (See the HLC Dimming Guide and then consult dimmer manufacturer for compatibility and conditions of use.)

Electrical Junction Box Mounting

- HLC fixtures may be used in compatible electrical junction boxes in direct contact with insulation including spray foam insulation
- Keyhole mounting slots allow for quick installation with provided screws
- Installs from below the ceiling
- Suitable for installation in most 3-1/2" and 4" octagon and round electrical junction boxes.
- Mounting holes at 2.76", 3.52" and 4.74" allow for mounting to most junction boxes.
- Compatible with compact (pancake) junction boxes (ensure pancake box is flush with the ceiling)
- The installer must ensure compatibility of fit, wiring and proper mounting in the electrical junction box. This includes all applicable national and local electrical and building coded NEMA LSD 57-2013
- Reference installation instructions for complete mounting steps

Gasket

- Closed-cell gasket achieves restrictive airflow requirements without additional caulking

Compliance

- ETL certified for US and Canada
- Wet Location listed
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements.
- Airtight per ASTM-E283 (no gasket necessary)
- EMI/RFI emissions per FCC 47CFR Part 15B
- Contains no mercury or lead and RoHS compliant ⁽¹⁾.
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11.
- Can be used for State of California Title 24 high efficacy luminaire compliance ⁽¹⁾
- Can be used for International Energy Conservation Code (IECC) and Washington State Energy Code high efficiency luminaire Compliance
- ENERGY STAR® Certified luminaire - consult ENERGY STAR® Certified Product List

Warranty

- Five year limited warranty, consult website for details. www.cooperlighting.com/warranty

1. T24 and RoHS are self-tested by Cooper Lighting Solutions. Not a third party certification.

Energy Data


HLC4FS1E	
Lumens	700
Input Voltage	120V
Input current FP	0.085A
Input Power	11 W
Efficiency	69
Inrush(A)	<1A
THDi	<50
PF	>0.9
T Ambient	-20~40°C
Sound Rating	≤22DB
Efficacy (LPW)	≥60

HLC6FS1E	
Lumens	900
Input Voltage	120V
Input current FP	0.129
Input Power	14 W
Efficiency	65
Inrush(A)	<1A
THDi	<50
PF	>0.9
T Ambient	-20~40°C
Sound Rating	≤22DB
Efficacy (LPW)	≥60

	CCT	Watts	lumens	LPW	CRI
HLC4FS1E	2700K	9.8	650	66.3	92
	3000K	9.8	690	70.4	92
	3500K	10.0	730	73	92
	4000K	9.9	750	75.8	92
	5000K	9.6	710	70	92

	CCT	Watts	lumens	LPW	CRI
HLC6FS1E	2700K	14.6	910	62.3	92
	3000K	14.7	970	66	92
	3500K	15.1	1050	69.5	92
	4000K	14.9	1060	71.1	92
	5000K	14.5	1010	69.7	92

Photometric Data




HLC4FS1E-24P-3000K

Spacing criterion:
 (0-180) 1.24 | (90-270) 1.25 | (Diagonal) 1.36
 Beam Angle: 113°
 Field Angle: 175°
 Lumens: 690
 Input Watts: 9.8 W
 Efficacy: 70.4 LPW
 UGR: 28
 Test Report: P1219800

Zonal Lumen	Lumens	% Lumens
0-30	175	26.5
0-40	285.9	43.3
0-60	505.5	76.6
0-90	674	102.1

TM-30-15	Rf = 92
	Rg = 99
CRI/CIE	Ra = 94.7
	R9 = 70

113°



HLC6FS1E-24P-3000K

Spacing criterion:
 (0-180) 1.24 | (90-270) 1.24 | (Diagonal) 1.36
 Beam Angle: 111°
 Field Angle: 171°
 Lumens: 970
 Input Watts: 14.7 W
 Efficacy: 66 LPW
 UGR: 26
 Test Report: P1219805

Zonal Lumen	Lumens	% Lumens
0-30	251	26.7
0-40	409.7	43.6
0-60	721.4	76.8
0-90	952	101.3

TM-30-15	Rf = 92
	Rg = 100
CRI/CIE	Ra = 94
	R9 = 69

111°