

Project		Catalog #		Type	
Prepared by		Notes		Date	



# HALO

## LT3 3" Recessed Canless LED Downlights

The LT Baffle Canless LED Downlights provide a modern, regressed downlight for bright, general area lighting. The 5-color selectability and flicker-free 10% dimming allow for easy lighting customization.

**Typical Applications** Residential

### Interactive Menu

- Order Information page 2
- Product Specifications page 2
- Energy Data page 3
- Photometric Data page 3
- Product Warranty

### Product Certification



Refer to ENERGY STAR® Certified Products List.  
Can be used to comply with California Title 24 High Efficacy requirements.  
Certified to California Appliance Efficiency Database under JAB.


### Product Features



### Top Product Features

- Round 3" Canless LED Downlight suitable for remodel and new construction installations (For new construction, use with canless mounting frames/plates)
- Installs in [2x4] framing and rated for IC (insulation contact) or non-IC applications (no housing required)
- **Lens & Trim:** Recessed baffle trim, flat diffuse lens
- **5-Color Field-SeleCCTable:** 2700K, 3000K, 3500K, 4000K, 5000K; 90+ CRI
- **Brightness:** 550 lumens (nominal)
- **Dimming:** Dims to 10% (phase cut LE/TE); 120V input
- Smooth Decorative Overlays in 2 finishes (sold separately)
- Meets AIR-TITE and code compliance for additional energy savings
- **Life:** 35,000 hrs of maintenance-free operation in damp or wet locations
- 5-year warranty

### Dimensional and Mounting Details



## Order Information

Catalog Number	Module	Lumens (@3000K)	CRI/CCT	Driver	Finish	Packaging
LTC305FS5B	3-inch LT Series Baffle Canless LED Downlight	560 lumens	90+ CRI, field selectable CCT: 2700K,3000K, 3500K, 4000K, 5000K	120V 60Hz, LE & TE phase cut 10% dimming	Matte White	Plastic-free & Fully Recyclable
LTC305FS5BMB	3-inch LT Series Baffle Canless LED Downlight	570 lumens	90+ CRI, field selectable CCT: 2700K,3000K, 3500K, 4000K, 5000K	120V 60Hz, LE & TE phase cut 10% dimming	Matte Black	Plastic-free & Fully Recyclable

### Optional Accessories - Decorative Smooth Splay Overlays (sold separately)

Catalog Number	Description
LT30MW	3-inch matte white decorative smooth splay overlay
LT30MB	3-inch matte black decorative smooth splay overlay



LT30MW  
Paintable Matte White,  
Smooth Splay



LT30MB  
Matte Black,  
Smooth Splay

### Optional Accessories - Extension Cable | SeleCCTable Driver/JBox (sold separately)

Catalog Number	Description
HLB06FSEC	6-ft.extension cable
HLB12FSEC	12-ft.extension cable
HLB20FSEC	20-ft.extension cable

### Accessories – New Construction Mounting Frames/Plates (order separately)

Ensure the proper placement and alignment of canless LED downlights in new construction applications. Mounting frames feature adjustable hanger bars, Got Nail™ captive pre-installed nails, and integrated thumb screws for holding canless junction boxes in place to meet code requirements during rough-in wiring.

Catalog Number	Description
SP346RS	3"/4"/6" Round/Square Smash Plate

## Specification Features

### Selectable System

- Use the 5-position color selector switch to choose between: 2700K, 3000K, 3500K, 4000K, and 5000K

### Module – Trim

- LED module consists of LED array, optical assembly, driver and self-flanged trim
- Baffle trim (Use a decorative overlay to convert from baffle to smooth splay - order separately)
- Injection molded plastic construction is impact resistant and non-corrosive
- Non-conductive construction meets most local code 'dead front' requirements

### LED Array

- A plurality of low power LEDs provide a uniform source with high efficiency and long life
- Available in 90 CRI minimum, R9 greater than 50 and color accuracy within 4 SDCM provide color accuracy and uniformity
- Factory default color temperature (CCT) is set to bright white (3000K)
- 5-color selectable CCT: 2700K, 3000K, 3500K, 4000K and 5000K

### Optical Assembly

- Optical assembly provides wide distribution useful for general and task lighting
- Diffuse injection molded lens with contoured profile provides uniformity and a familiar lamp like appearance

### Driver

- Integral 120V 60 Hz constant current driver provides noise free operation
- Dimmable: Continuous, flicker-free phase cut (leading-edge/trailing-edge - LE/TE) dimming from 100% to 10% output with compatible dimmers
- See this fixture's Dimming Guide for compatible dimmers

### Retention

- No additional housing or junction box required (Not for installation in recessed cans)
- The included remote driver / junction box may be used in direct contact with insulation
- Installer must cut hole and install fixture into aperture with the clips compressed
- When released, the spring clips will rest on the back side of the ceiling material holding the fixture in place
- For new construction applications, use HALO Canless Mounting Frames or Smash Plates prior to drywall installation

### Gasket

- Closed cell gaskets achieve restrictive airflow requirements without additional caulking

### Compliance

- UL Certified US and Canada Type IC suitable for direct contact with air permeable insulation
- Damp location listed. Not recommended for use in direct contact with spray foam insulation, reference NEMA LSD57-2013
- Airtight certified per ASTM-E283
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Contains no mercury or lead and RoHS compliant
- Photometric testing in accordance with IES LM-79-08
- Lumen maintenance projections in accordance with IES LM-80-08 and TM-21-11
- Can be used for State of California Title 24 high efficacy luminaire compliance. Complies with Title 24 JA8-2022-E.
- Can be used International Energy Conservation Code (IECC) high efficiency luminaire compliance.
- ENERGY STAR® listed, reference database for current listings

### Warranty


- Five year limited warranty, consult website for details. [www.cooperlighting.com/legal](http://www.cooperlighting.com/legal)

## Energy Data

### LT3 - 550 Lumens

Lumens (nominal)	550 Series
Input Voltage	120V
Input current	0.057A
Input Power	6.7W
Efficiency	78.16 (LPW)
Inrush(A)	1.09A@56usec
THD	15.10%
PF	0.966
T Ambient	-30° - +40°C
Sound Rating	18.7dB @1feet

## Photometric Data




### LTC305FS5B-3000K

Spacing Criteria (0/90/45):  
1.10/1.10/1.16  
Beam Angle: 83°  
Field Angle: 129°  
Lumens: 560  
Input Watts: 6.3 W  
Efficacy: 88.9 LPW  
UGR: 25.5  
Test Report: P879304

Zonal Lumen	Lumens	% Lumens
0-30	229.6	41
0-40	349.4	62.4
0-60	510.2	91.1
0-90	560	100
90-180	0	0
0-180	560	100

TM-30-15	Rf = 91
	Rg = 100
CRI/CIE	Ra = 94
	R9 = 60


CCT - Range of 2700K- 5000K



LT4 5CCT				
CCT	Watts	lumens	LPW	CRI
2700K	6.1	540	88.5	95
3000K	6.3	560	88.9	93
3500K	6.3	575	91.3	94
4000K	6.3	580	92.1	93
5000K	6.0	560	93.3	95

### LTC305FS5B-3000K

PRODUCT SPECIFICATIONS	
Lumens	560
Watts	6.3
Lumens Per Watt (Efficacy)	88.9
Color Accuracy (CRI)	93
Light Color (CCT) Correlated Color Temperature (CCT)	3000K




### LTC305FS5BMB-3000K

Spacing Criteria (0/90/45):  
 1.09 / 1.09 / 1.16  
 Beam Angle: 78.6°  
 Field Angle: 103.9°  
 Lumens: 570  
 Input Watts: 6.6 W  
 Efficacy: 86.4 LPW  
 UGR: 26.2  
 Test Report: P995470

Zonal Lumen	Lumens	% Lumens
0-30	233.1	40.9
0-40	359.8	63.1
0-60	537.7	94.3
0-90	570	100
90-180	0	0
0-180	570	100

TM-30-15	Rf = 91.6
	Rg = 102.1
CRI/CIE	Ra = 95.5
	R9 = 73.2



### LT4 5CCT

CCT	Watts	lumens	LPW	CRI
2700K	6.5	560	86.2	93
3000K	6.6	570	86.4	93
3500K	6.5	580	89.2	93
4000K	6.6	585	88.6	93
5000K	6.5	590	90.8	93

### LTC305FS5B-3000K

PRODUCT SPECIFICATIONS	
Lumens	570
Watts	6.6
Lumens Per Watt (Efficacy)	86.4
Color Accuracy (CRI)	93
Light Color (CCT) Correlated Color Temperature (CCT)	3000K