


Good

Better

Best

Click on products to learn more



		LHB	VHB	UHBS	ILED	Steeler	HBLED	OHB(L)	Benchmark	
APPLICABILITY ¹	Big Box Retail	★	★	★★	★★★	★★	★	★★★	★	
	Sports / Recreation	★★	★★	★★	★	★★★	★★	★★★	★★	
	Warehouses	★★★	★★★	★★	★★★	★★★	★★★	★★★		
	Manufacturing	★★	★★	★★	★	★★★	★★★	★★★	★★★	
	Cold Storage	★	★★★	★		★	★	★★★	★★	
	Large Indoor					★★	★★★	★★★	★★	
	Complex Environments		★	★★		★			★★★	
FEATURES / PERFORMANCE	Lumen Range	12,000 - 36,000	9,000 - 48,000	12,000 - 36,000	5,000 - 32,000	9,000 - 36,000	12,000 - 60,000	9,000 - 100,000	12,000 - 70,000	
	Selectable		Lumens	Lumens/CCT						
	Efficacy (Max)	140 lm/W	164 lm/W	165 lm/W	155 lm/W	152 lm/W	186 lm/W	205 lm/W	181 lm/W	
	CRI	80	70, 80, 90	80	80	80	70, 80	70, 80, 90	70, 80	
	Distribution	M	N, W	M	N, W	N, M, W	N, W	N, M, W	N, M, W	
	Sizes	13" x 2' & 4'	< 2'	13"/15" Dia	4', 8'	17" Dia	4'	Scalable	17", 25" Dia	
	Housing ²	CRS	CRS / Extruded	Diecast	CRS	CRS / Diecast	CRS	CRS	Diecast	
	Lensing	Acrylic	Polycarbonate	Polycarbonate	Optional	Polycarbonate	Optional	Acrylic	Acrylic	
	Uplight	None	None	None	Up to 5%	Up to 10%	None	None	None	
	Life (@ 60K hrs)	L84	L83	L91	L86	L88	L84	L96	L92	
	Ambient Range	-20C to 50C	-40C to 55C	-40C to 50C	-40C to 35C	-40C to 55C	-40C to 55C	-40C to 55C	-40C to 55C	-40C to 65C
	Emergency	Rapid Response	Remote	✓	Integrated	Remote	Integrated	Integrated	Remote	
	Ratings	Damp	Damp	IP65	Damp	IP65 Optics	Damp	Damp	IP66	
DLC	Premium	Standard, Premium	Premium	Premium	Premium	Premium	Premium	Premium		
INTEGRATED CONTROLS	Basic Occupancy	Rapid Response	✓		✓	✓	✓	✓	✓	
	Stand Alone Daylight / Occupancy		✓	✓	✓	✓	✓	✓	✓	
	WaveLinx		✓			✓	✓	✓	✓	
	Enlighted ³		✓			✓	✓	✓	✓	

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
 2. CRS=Cold-rolled Steel, Extruded=Extruded Aluminum, Diecast=Diecast Aluminum.
 3. Location data for asset tracking.