



Innovation you can rely on™



Roadway Lighting Redefined

A New Performance Standard in LED Roadway Lighting

With industry-leading, patented optics in a scalable package, the Navion™ LED roadway luminaire delivers state-of-the-art optical control, low maintenance costs, rugged construction and modern styling. Designed with DOT, municipal and utility customers in mind, the Navion luminaire's superior performance and configurability provide uniform, glare-free, energy-efficient light for highways, streets and other public spaces.

Long Life with Low Maintenance Costs

Superior illumination, low maintenance, long life and low cost of ownership are critical factors when lighting roads and public spaces. Ideal for retrofit and new construction applications, the Navion fixture can be tailored to meet your most important needs without compromising on specification features. The five housing configurations of the Navion luminaire allow scalability from 2,582 to 33,732 delivered lumens. The 4000K/70 CRI is standard, with 6000K/70 CRI and 3000K/70 CRI options available. LED components are IP66 rated and the fixture is wet location listed, with an IP66 housing option available.

Customer-Focused Design

Designed to meet the full range of outdoor lighting challenges in area, site and roadway applications, the Navion luminaire is available with a wide array of optics and specification performance features. A tool-less, removable power tray door and quick electrical disconnects make installation and maintenance easy. The 10kV common surge (line-to-ground) and differential surge (line-to-line) protection is standard. Four-bolt mounting with cast-in leveling steps ensures simple installation, while a super TGIC polyester powder-coat finish provides years of worry-free ownership.

Design Performance Features

Stepping Up to the Challenge

The Navion luminaire is designed to provide superior optical performance in a package that is easy to install and maintain. With HID equivalents from 70W HPS up to 750W Pulse Start MH, along with the industry-leading AccuLED Optics™ system from Cooper Lighting Solutions, the Navion fixture is designed to meet the toughest lighting challenges.

Construction

- Tool-less entry with hinged, removable power door for easy maintenance
- 3G vibration rated
- IP66-rated LED Light Squares
- Wet location-rated housing (IP66 housing optional)
- Extruded aluminum heat sink scaled to lumen package
- Rugged, die-cast aluminum housing

Electrical


- Operates in -40°C to 40°C ambient temperatures (optional 50°C high ambient configuration)
- 10kV common surge (line-to-ground) and differential surge (line-to-line) protector
- >L90, 60,000 hours at 40°C, compliant with IESNA TM-21
- LED driver is mounted directly to removable door for optimal heat sinking
- 120-277V 50/60Hz, 347V 60Hz or 480V 60Hz operation
- Quick disconnects for tool-less removal of power door

Controls

- Standard with 0-10V dimming driver(s)
- Optional occupancy sensor
- Optional wireless control and monitoring system

Finish


- Five-stage super TGIC paint resists extreme weather conditions while providing optimal color and gloss retention. It's available in standard grey or optional bronze, black, dark platinum, graphite metallic or white.



Warranty

- Five-year warranty

Extruded Aluminum Heat Sinks



Tool-less Entry

Scalable Lumen Package




Self-Cleaning Heat Sinks



Tool-less Entry

Stainless steel latches provide easy, tool-less access to electrical compartment, even with lineman's gloves.




Quick Disconnects

Connections between power door and housing are made with tool-less quick disconnects. Power door removes in seconds.



Bird Guard

Standard bird guard fits securely around 1-1/4" and 2" pipe (1-5/8" to 2-3/8" O.D.).



Four-Bolt Mounting


Sturdy four-bolt mounting brackets fit 1-1/4" to 2" pipe (1-5/8" to 2-3/8" O.D.). It's available with built-in level indicator for a secure, level installation.

Optional Features



NEMA Photocontrol Receptacle

Gasketed receptacle for mounting standard NEMA photocontrol (order separately).



Surge Protection

A 10kV common surge (line-to-ground) and differential surge (line-to-line) mode protection is standard.



Occupancy Sensor

The optional motion sensor reduces energy use for site lighting applications.



IP66 Rating

Housing is available with IP66 rating for dust and water.

Scalable Illumination with LED Light Squares

Energy Savings and Environmental Stewardship

The simplest and most effective way to reduce a lighting fixture's impact on the environment is to minimize its energy consumption. By incorporating Light Squares from Cooper Lighting Solutions, the Navion LED luminaire provides energy savings up to 75 percent compared to standard HID solutions.

Long Life

With a 60,000+ hour rated life (at greater than 90 percent lumen maintenance), the Navion LED luminaire operates up to six times longer than traditional metal halide fixtures.

Low Maintenance


With simple quick disconnects, the Light Squares are easily removed in the field for replacement or for the rotation of the optics.

Warm White Color

Lighting designers, architects and specifying engineers have long preferred light sources that provide a balanced spectral power distribution and warm white light. Many LED solutions standardize on a cool blue 5000-6000K correlated color temperature (CCT) to maximize lumen output. The Navion luminaire provides warm white light at a standard 4000K CCT with no sacrifice in lumen output.



NOTE: Compliant with IESNA TM-21



Optical Performance Redefined


Performance and Scalability

The Navion luminaire is designed around superior optical performance and scalability. With a choice of 15 lumen packages and 16 optical distributions, the optimal configuration can be used to maximize light levels while minimizing operating costs.

Power Consumption (Watts)

Number of Light Squares	Drive Current		
	530mA	700mA	1A
1	30	38	56
2	54	72	107
3	80	105	157
4	105	138	213
6	159	210	315

Efficacy (lm/W)



NOTE: Nominal efficacy at 4000K CCT



Superior Efficiency and Control

With efficiencies as high as 95 percent, the patented AccuLED Optics™ system is up to 30 percent more efficient than traditional HID optical systems. Available in 16 optional distributions, this system provides the flexibility and performance required for outdoor applications.




House Side Shield

For stringent light trespass requirements and the ultimate level of backlight control, a house side shield accessory is available for factory or field installation. Designed to seamlessly integrate with the SL2, SL3, SL4 and AFL distributions, the house side shield virtually eliminates backlight and also enhances visual comfort.



Optical Distributions

The Navion luminaire has a choice of seven asymmetric area, three asymmetric roadway, three symmetric and three specialized distributions.



Versatility and Simplicity



The Navion luminaire is designed to meet a wide range of outdoor lighting needs, from single-fixture applications to multi-lane highways. Utilities and municipalities will find it ideal for streets, rural roads, bridges, substations and small area security lighting applications. With multiple optical configurations and fixture sizes, the Navion luminaire allows lumen and energy output to be customized to fulfill the exact needs of the outdoor space — eliminating wasted energy and obtrusive spill light. The larger configurations excel in multi lane highway projects, while the smaller lumen packages work well in substation areas and along neighborhood streets.



Municipalities

For cities and towns, the Navion luminaire delivers superior optical performance in a durable, modern design, while providing up to 70 percent less energy usage compared to typical HID luminaires. With greater than 90 percent lumen maintenance at 60,000 hours (over 16 years at 10 hours daily use), the Navion fixture offers a long life and maximum savings in maintenance costs.

The Navion luminaire offers a choice of 10 optical packages to meet the exact needs of the outdoor area, and the fixture's size and construction are scaled to the specific lumen package. Designed to withstand harsh environments, the luminaire's rugged, die-cast aluminum construction and 2.5 mil powder-coat finish provide superior protection. The Navion luminaire is 3G vibration rated and comes standard with 10kV dual-mode surge protection.



Utilities

For utility applications, the Navion LED luminaire provides superior optical performance, reliability and low maintenance costs. With greater than 90 percent lumen maintenance at 60,000 hours (over 16 years at 10 hours daily use), the Navion luminaire's long life saves on maintenance costs — no expensive lamp replacement trips.

Available in 10 optical packages, the Navion luminaire's size and construction are scaled to the lumen package, offering choices to meet the exact needs of the application and keeping capital expenditures low. The superior LED optics eliminate uplight while delivering minimal glare. The sleek, modern design makes it an ideal solution for numerous lighting needs.

With standard 10kV dual-mode surge protection, a 3G vibration rating and testing performed at 40°C, versus the standard 25°C, utilities and their customers are guaranteed a reliable product. Fixture construction includes a durable, die-cast aluminum housing with a 2.5 mil powder coat finish to provide long-lasting protection.



Departments of Transportation

For local, state and federal Departments of Transportation, the Navion luminaire leads the field in optical performance, versatility and durability with uniform, warm white illumination, no uplight and minimal glare.

Available in five fixture sizes, each with a different lumen package for ultimate versatility, the Navion luminaire has a long rated life with greater than 90 percent lumen maintenance at 60,000 hours (over 16 years at 10 hours daily use).

The luminaire's rugged, quality construction includes a die-cast aluminum housing and a 2.5 mil power coat exterior finish to withstand harsh conditions. A unique tool-less entry design allows quick and easy installation and maintenance.

The Navion luminaire is suitable for -40°C to 40°C ambient environments and features 10kV dual-mode surge protection, a five-year warranty, IP66-rated LED panels and a 3G vibration rating.

Performance and Versatility

The Navion luminaire is built around LED technology and designed to accommodate ongoing improvements in LED chips and drivers, making it the ideal solution for both current and future lighting requirements.



Ease of Installation and Maintenance

The Navion luminaire's performance comes with years of low-cost, low-hassle ownership. With lumen maintenance and life expectancy far beyond traditional HID light sources, regular and time-consuming service visits are a thing of the past. The simple and spacious Navion fixture housing is designed to fit lineman's gloves and can be installed with simple tools. Key electrical components are mounted on the power door, so service is tool-less. The door is small enough to hold in one hand, making field replacement quick and easy.



Tool-less Access

Stainless steel latches provide easy, tool-less access to the electrical compartment, even with lineman's gloves.



Hinged, Removable Power Door

Driver and surge protector is mounted to door. Power door hangs securely and can be easily removed without the use of tools.



Occupancy Sensing

Accelerate Payback on your Investment

To further enhance energy savings, the Navion luminaire offers an optional occupancy sensor that is integral to each individual luminaire. When the area surrounding the luminaire is unoccupied, the sensor has the ability to reduce light levels and power consumption. In addition to financial benefits, all the control options for the Navion luminaire are designed to be simple and cost-effective ASHRAE and Title 24 compliant solutions.




Dimming Occupancy Sensor (DOS)

When the DOS option is selected, the occupancy sensor is connected to a dimming driver and the entire luminaire dims when there is no activity detected. When activity is detected, the luminaire returns to full light output. The sensor is factory preset to dim down to approximately 50 percent lumen output with a time delay of five minutes. To change these settings, a FSIR-100 accessory can be purchased. The FSIR-100 is a wireless configuration tool that allows the dimming level, time delay, sensitivity and other parameters to be changed. Consult a representative from Cooper Lighting Solutions for additional details.







LumaWatt Wireless Control and Monitoring System (DIMRF-LW and DIMRF-LN)

The LumaWatt system is best described as a peer-to-peer wireless network of luminaire-integral sensors that operate in accordance with programmable profiles. The end user can create and manage sensor profiles with browser-based management software and broadcast to the sensors as necessary via wireless gateways. Each sensor is capable of motion and photo sensing, metering power consumption and wireless communication. For additional details, refer to www.cooperlighting.com.

Dimming Occupancy Sensor (DOS)



LumaWatt (DIMRF-LW and DIMRF-LN)



Ordering Information


Sample Number: NVN-AE-01-E-U-T3A-10K-4-AP

Product Family	Light Engine	Number of LED Squares ¹	Driver	Voltage	Distribution	Surge Protection	
NVN=Navion	AE=1A Drive Current	01=1 02=2 03=3 04=4 06=6	E=Non-Dimming D=Dimming	U=Universal 120-277V 8=480V 9=347V	T2=Type II T2R=Type II Roadway T3=Type III T3R=Type III Roadway T4FT=Type IV Forward Throw T4W=Type IV Wide 5NQ=Type V Square Narrow 5MQ=Type V Square Medium	5WQ=Type V Square Wide SL2=Type II w/Spill Control SL3=Type III w/Spill Control SL4=Type IV w/Spill Control SLL=90° Spill Light Eliminator Left SLR=90° Spill Light Eliminator Right RW=Rectangular Wide Type I AFL=Automotive Frontline	10K=Cooper 10kV Surge Module (Standard) X=Driver Surge Protection Only ²
Options (Add as Suffix)							
2L=Two Circuits ³ 7030=70 CRI 3000K ⁴ 7060=70 CRI 6000K ⁴ 530=Drive Current Factory Set to 530mA ⁵ 700=Drive Current Factory Set to 700mA ⁵ 4=NEMA Twistlock Photocontrol Receptacle 4N5=NEMA 5-PIN Twistlock Photocontrol Receptacle 4N7=NEMA 7-PIN Twistlock Photocontrol Receptacle IP66=IP66 Rated HA=50°C High Ambient		U=UL Listed/CSA Certified L90=Optics Rotated 90° Left R90=Optics Rotated 90° Right MS/DIM-L08=Motion Sensor for Dimming Operation, Maximum 8' Mounting Height ⁶ MS/DIM-L20=Motion Sensor for Dimming Operation, 9' - 20' Mounting Height ⁶ MS/DIM-L40=Motion Sensor for Dimming Operation, 21' - 40' Mounting Height ⁶ MS/X-L08=Bi-Level Motion Sensor, Maximum 8' Mounting Height ⁷ MS/X-L20=Bi-Level Motion Sensor, 9' - 20' Mounting Height ⁷ MS/X-L40=Bi-Level Motion Sensor, 21' - 40' Mounting Height ⁷ K=Level Indicator			AI=Site Arm Included ⁸ LCF=Light Square Trim Plate Matches Housing Color HSS=Factory Installed House Side Shield ⁹		
Color				Accessories (Order Separately)			
AP=Grey (Standard) BZ=Bronze BK=Black DP=Dark Platinum GM=Graphite Metallic WH=White A=Raw Aluminum Finish				OA/RA1016=NEMA Photocontrol - Multi-Tap OA/RA1027=NEMA Photocontrol - 480V OA/RA1201=NEMA Photocontrol - 347V OA/RA1013=Photocontrol Shorting Cap OA/RA1014=NEMA Photocontrol - 120V OA1223=10kV Surge Module Replacement FSIR-100=Wireless Configuration Tool for Motion Sensor ¹⁰ LS/HSS=Field Installed House Side Shield ¹¹			


NOTES: 1 Standard 4000K CCT and minimum 70 CRI. 2 Consult factory for driver surge protection values. 3 Low-level output varies by number of light squares specified. Consult factory. Requires two or more light squares. No terminal block with 2L options. 4 Use dedicated IES files for 3000K and 6000K when performing layouts. These files are published on the Navion luminaire product page on the website. 5 1 Amp standard. Use dedicated IES files for 530mA and 700mA when performing layouts. These files are published on the Navion luminaire product page on the website. 6 Sensor mounted externally. Must specify dimming driver. Consult factory for more information. 7 Sensor mounted externally. Available in 2, 3, 4 or 6 Light Square configurations. Replace "X" with number of Light Squares in low output mode. For ON/OFF operation, replace "X" with "0". Maximum two Light Squares in low output mode. Not available with dimming driver. No terminal block with bi-level operation. 8 22" upsweep arm. Round pole adapter included. 9 Only for use with SL2, SL3, SL4 and AFL distributions. The Light Square trim plate is painted black when the HSS option is selected. 10 This tool enables adjustment of parameters including high and low modes, sensitivity, time delay, cutoff and more. Consult your Cooper Lighting Solutions representative for additional details. 11 One required for each Light Square.

Dimensions

1, 2 or 3 Light Squares




4 or 6 Light Squares



Dimensional Data

Number of Light Squares	"A" Length
1	21-1/2" (546mm)
2	27-5/8" (701mm)
3	33-5/8" (854mm)
4	27-5/8" (704mm)
6	33-5/8" (854mm)

Arm Drilling Type "M"




Lumen Multiplier

Ambient Temperature	Lumen Multiplier
0°C	1.02
10°C	1.01
25°C	1.00
40°C	0.99
50°C	0.97

Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 Hours)	Theoretical L70 (Hours)
25°C	> 94%	> 350,000
40°C	> 93%	> 250,000
50°C	> 90%	> 170,000

Optional Arm 22" Upsweep Arm



Additional Information

Compliances	Technical Data (Electronic Driver)	EPA (Effective Projected Area - Square Feet)			Shipping Data (Approximate Net Weight)
		Number of Light Squares	Without Arm	With Arm	
UL and cUL Wet Location Listed IP66 Light Squares 3G Vibration Rated ARRA Compliant ISO9001	+40°C (104°F) Ambient Temperature Rating -40°C (-40°F) Ambient Temperature Rating Optional 50°C (HA) Ambient Temperature Rating >0.9 Power Factor <20% Total Harmonic Distortion 120-277V/50 and 60 Hz 347/60 Hz, 480V/60 Hz	1 Square	0.8	1.2	1 Square 17 lbs. (7.7 kgs.)
		2 Squares	1.0	1.3	2 Squares 22 lbs. (10.0 kgs.)
		3 Squares	1.2	1.5	3 Squares 26 lbs. (11.8 kgs.)
		4 Squares	1.2	1.5	4 Squares 31 lbs. (14.1 kgs.)
		5 Squares	1.2	1.5	5 Squares 36 lbs. (16.3 kgs.)
		6 Squares	1.4	1.7	6 Squares 36 lbs. (16.3 kgs.)

NOTE: Specification and dimensions subject to change without notice.



IP66 Rated

Lighting Brands

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Brands

Greengate
Fifth Light

Connected Lighting Systems

HALO Home
WaveLinx

IoT Platforms

Trellix



Cooper Lighting Solutions

1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2021 Cooper Lighting Solutions
All Rights Reserved
Publication No. BR506111EN
February 2021

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.