


Project		Catalog #		Type	
Prepared by		Notes		Date	



## Portfolio

### LD4C | EU4C | 4LB - Full Spectrum

4" Round, New Construction Downlight  
Narrow, Medium, Wide Beam or Wall Wash  
98CRI, Full Spectrum

#### Typical Applications

Office • Education • Healthcare • Hospitality • Retail •  
Code-Compliance Areas • Sports Venues

#### Interactive Menu

- Order Information [page 2](#)
- Product Specifications [page 4](#)
- Dimensional & Mounting Details [page 5](#)
- Energy Data [page 6](#)
- Connected System [page 7](#)
- Product Warranty





### Top Product Features


- 250-6000 lumens
- Easy disconnect for LED engine replacement and installation
- Optional snap in driver for ease of replacement
- Standard 0-10V driver dims to 1%
- 5 color temperatures: 2700K, 3000K, 3500K, 4000K and 5000K CCT
- 98 CRI
- Options to meet Buy American and other domestic preference requirements

### Dimensional and Mounting Details

#### DOWNLIGHT



#### WALL WASH



[CLICK HERE](#)  
dimension information

## Single Line Order Information

SAMPLE ORDER NUMBER: **LD4C209830D010M1H**

Invoice will indicate separate fixture components (housing, trim, module) which will ship complete from a single CLS facility in separate cartons.

To receive separate components (housing, trim, module) shipment, click on the "Multi-Line Ordering Information Option" button to the right.

Multi-line Ordering  
Information Option

Housing	Lumen <sup>(1)</sup>	Color Control	CCT <sup>(20)</sup>
<b>LD4C</b> =LED Downlight 4" Nominal Aperture <b>LD4CCP</b> =LED Downlight 4" Nominal Aperture, Chicago Plenum  For BAA or TAA use <a href="#">Multi-line Ordering</a>	<b>02</b> =250 lumens <sup>(27)</sup> <b>05</b> =500 lumens <sup>(27)</sup> <b>08</b> =800 lumens <sup>(27)</sup> <b>10</b> =1000 Lumens <sup>(28)</sup> <b>15</b> =1500 Lumens <b>20</b> =2000 Lumens <b>25</b> =2500 lumens	<b>30</b> =3000 Lumens <sup>(10)</sup> <b>35</b> =3500 lumens <sup>(10)</sup> <b>40</b> =4000 Lumens <sup>(10)</sup> <b>45</b> =4500 Lumens <sup>(10)</sup> <b>50</b> =5000 Lumens <sup>(10)</sup> <b>60</b> =6000 Lumens <sup>(10)</sup>	<b>98</b> =Full spectrum (Thrive) used with 98 CRI light engine           <b>27</b> =2700K <b>30</b> =3000K <b>35</b> =3500K <b>40</b> =4000K <b>50</b> =5000K

Driver (Specify from Driver column.)		Information below for reference only.
		Remote driver & plug in driver
<b>D010</b> =0-10V Dimming, 1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1D010</b> =0-10V Dimming, 1% to 100%, 120V, 5000, 6000 lumens (2500 to 4500 lumens for remote driver) <b>2D010</b> =0-10V Dimming, 1% to 100%, 277V, 5000, 6000 lumens (2500 to 4500 lumens for remote driver) <b>3D010</b> =0-10V Dimming, 1% to 100%, 347V dedicated drivers, 800-3000; 500, 3500 and above use step down transformer (500 to 4500 lumens for remote driver)		Offered 250-4500
<b>D010TR</b> =0-10V (120-277V) or Phase-Cut (120V) dimming, 1-100%, 120V-277V, 250-3000 lumens (up to 2000 lumens for remote driver) <b>1D010TR</b> =0-10V or Phase-Cut Dimming, 1% to 100%, 120V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <b>2D010TR</b> =0-10V Dimming, 1% to 100%, 277V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <b>3D010TR</b> =0-10V Dimming, 1% to 100% 347V step down transformer, 250-6000 lumens (250 to 3000 lumens for remote driver)		Offered 250-3000
<b>DE010</b> =0-10V Dimming, 0.1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1DE010</b> =0-10V Dimming, 0.1% to 100%, 120V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>2DE010</b> =0-10V Dimming, 0.1% to 100%, 277V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>3DE010</b> =0-10V Dimming, 0.1% to 100%, 347V step down transformer, 500-6000 lumens (500 to 4500 lumens for remote driver)		Offered 500-4500
<b>DSL</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1DSL</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>2DSL</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 277V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>3DSL</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 347V step down transformer, 500-6000 lumens (500 to 4500 lumens for remote driver)		Offered 500-4500
<b>DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, 800-3000 lumens (up to 2000 lumens for remote driver) <sup>(14)</sup> <b>1DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(14)</sup> <b>2DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(14)</sup> <b>3DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 347V step down transformer, 800-6000 lumens (800 to 3000 lumens for remote driver) <sup>(14)</sup>		Offered 800-3000
<b>DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, RJ45 Connection, 800-3000 lumens (up to 2000 lumens for remote driver) <sup>(14)</sup> <b>1DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, RJ45 Connection, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(14)</sup> <b>2DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, RJ45 Connection, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(14)</sup> <b>3DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, RJ45 Connection, 347V step down transformer, 800-6000 lumens (800 to 3000 lumens for remote driver) <sup>(14)</sup>		Offered 800-3000
<b>DLE</b> =Lutron Ecosystem dimming 1% to 100%, 120V-277V, 800-2500 lumens (up to 2000 lumens for remote driver) <b>1DLE</b> =Lutron Ecosystem dimming 1% to 100%, 120V, 3000-5000 lumens (2500 lumens for remote driver) <b>2DLE</b> =Lutron Ecosystem dimming 1% to 100%, 277V, 3000-5000 lumens (2500 lumens for remote driver) <b>3DLE</b> =Lutron Ecosystem dimming 1% to 100%, 347V with step down transformer, 800-5000 lumens (800 to 2500 lumens for remote driver)		Offered 800-2500
<b>DLV</b> =Low voltage dimming driver (1-100%) for use with DLVP system, 800-2000 lumens <sup>(3)</sup>		Offered with remote driver only for 800-2000

Driver Options		Bar Hanger
<b>Blank</b> =Integral driver <b>RC100</b> =Remote 100ft <sup>(33)</sup> <b>RC75</b> =Remote 75ft <sup>(33)</sup> <b>RC50</b> =Remote 50ft <sup>(33)</sup> <b>RC25</b> =Remote 25ft <sup>(3)</sup>	<b>RC15</b> =Remote 15ft <sup>(3)</sup> <b>RC5</b> =Remote 5ft <sup>(3)</sup> <b>RC2</b> =Remote 2ft <sup>(3)</sup> <b>PD</b> =Plug in Driver <sup>(26)</sup>	<b>Blank</b> = Without hanger bars <b>B26</b> = C-channel Bar Hanger, 26" Long, Pair

Continued on next page.

## Single Line Order Information

Trim Distribution <sup>(5)</sup>	Trim Flange	Trim Finish	Options <sup>(3) (16) (31)</sup>
<b>N</b> =Narrow, Spun Aluminum <sup>(26) (30)</sup> <b>M</b> =50° Cutoff, Medium Beam Reflector, Spun Aluminum <b>MD</b> =45° Cutoff, Medium Beam Reflector, Spun Aluminum <b>W</b> =Wide, Spun Aluminum <b>S</b> =Shallow, Spun Aluminum <b>PS</b> =Non-Conductive Shallow (dead front), white <sup>(11) (12)</sup> <b>CS</b> =Cast Shallow, Die Cast Aluminum <b>BA</b> =Spun Aluminum Baffle <sup>(7)</sup> <b>Wall Wash</b> <b>SWN</b> =Single Wall Wash, Spun Aluminum <b>DWN</b> =Double Wall Wash, Spun Aluminum <b>CW</b> =Corner Wall Wash, Spun Aluminum <b>MDSW</b> =45° Cutoff, Single Wall Wash, Spun Aluminum <b>MDDW</b> = 45° Cutoff, Double Wall Wash, Spun Aluminum <b>LSWW</b> =Lensed Single wall wash, Spun Aluminum <b>LDWW</b> =Lensed Double wall wash, Spun Aluminum	<b>0</b> =White Polymer Trim Ring <b>1</b> =Self-flanged <sup>(13)</sup> <b>2</b> =White Painted Self-flanged <b>4</b> =Knife edge rimless use with die cast only <sup>(8) (23)</sup>	<b>LI</b> =Specular Clear <sup>(9)</sup> <b>H</b> =Semi-Specular Clear <sup>(9)</sup> <b>WMH</b> =Warm Haze <sup>(9)</sup> <b>WH</b> =Wheat <sup>(9)</sup> <b>GPH</b> =Graphite Haze <sup>(9)</sup> <b>B</b> =Specular Black <sup>(9)</sup> <b>MW</b> =Matte White (Antimicrobial) <b>MB</b> =Matte Black <sup>(8)</sup> <b>MMS</b> =Matte Metallic Silver <sup>(8)</sup>	<b>EMBOD</b> =Bodine® Emergency Module with Remote Test Switch <sup>(25)</sup> <b>EMBOD6ST</b> =Bodine® 6W Self Test Emergency Module with Remote Test Switch <b>EM7</b> =7W Emergency Module with Remote Test Switch <b>EM14</b> =14W Emergency Module with Remote Test Switch <b>EM14RSD</b> =14W Self Diagnostic Replaceable Emergency Battery Pack with Integral Test Switch <b>EMBOD7ST</b> =Bodine® Self Test Emergency Module <sup>(25)</sup> <b>IEMBOD</b> =Bodine® Emergency Module with Integral Test Switch <sup>(6) (25)</sup> <b>IEM7</b> =7W Emergency Module with Integral Test Switch <sup>(6)</sup> <b>IEM14</b> =14W Emergency Module with Integral Test Switch <sup>(6)</sup> <b>IEM14RSD</b> =14W Self Diagnostic Replaceable Emergency Battery Pack with Remote Test Switch <sup>(6)</sup> <b>IEMBOD6ST</b> =Bodine® 6W Self Test Emergency Module with Integral Test Switch <sup>(6) (25)</sup> <b>EMV7</b> =7W Low Voltage Emergency Module with Remote Test Switch <sup>(4)</sup> <b>EMV14</b> =14W Low Voltage Emergency Module with Remote Test Switch <sup>(4)</sup> <b>ETRD</b> =Emergency transfer device <sup>(32)</sup> <b>WPST</b> =Factory installed WaveLinX PRO Sensor Kit <sup>(15) (18)</sup> <b>WLST</b> =Factory installed WaveLinX LITE Sensor Kit <sup>(15) (17)</sup> <b>WPN</b> = WaveLinX PRO Wireless Node without sensor <sup>(21) (37)</sup> <b>WLN</b> = WaveLinX LITE Wireless Node without Sensor (not compatible with Tunable White) <sup>(36) (37)</sup>

Accessories (Sold separately) <sup>(22)</sup>

<b>TRM4P</b> =White metal trim ring <sup>(2)</sup> <b>LGSKT4IP66</b> =IP66 Gasket Kit <b>DT4RF</b> =4 inch frosted acrylic ring <sup>(20)</sup>  <b>PRR4</b> =Rimless Plaster Ring <sup>(2)</sup> <b>RKP4</b> =Knife Edge plaster Ring <sup>(24)</sup>	<b>RPM4MW</b> =Rimless Millwork Ring, Matte White <sup>(2)</sup> <b>RPM4MB</b> =Rimless Millwork Ring, Matte Black <sup>(2)</sup> <b>RKM4MW</b> =Knife Edge Millwork Ring, Matte White <sup>(24)</sup> <b>RKM4MB</b> =Knife Edge Millwork Ring, Matte Black <sup>(24)</sup>  <b>HSA4</b> =Slope Adapter for 4" Aperture Housings, Specify Slope <sup>(34)</sup>	<b>Connected Lighting Systems</b> <sup>(3) (15)</sup> <b>WPST</b> =Field installed WaveLinX PRO Sensor Kit <sup>(17)</sup> <b>WLST</b> =Field installed WaveLinX LITE Sensor Kit <sup>(18)</sup>  <b>Transformers</b> <b>H347</b> =H347 for 98CRI 4000 lumens and below	<b>Bar Hangers</b> <b>HB50</b> =C-channel Bar Hanger, 50" Long, Pair <b>RMB22</b> =Wood Joist Bar Hanger, 22" Long, Pair
---	--	--	--

## Notes:

- Nominal Lumens will vary depending on selected color, CRI, driver and reflector finish.
- Order trim with polymer trim ring (Consult specification sheet for color ordering information and options).
- Not available with Chicago Plenum.
- ULus listed only
- Beam angles are nominal with LI finish trims.
- Available with narrow (N), medium (M) and medium 45 degree (MD) Spun Aluminum trims. Required for use with all IEMBOD, IEM7, IEM14, IEMV7 and IEMV14 housings. Not offered with remote driver.
- Only available with Matte White and Matte Black Finishes.
- Available only on CS distributions.
- Not available on PS, CS or BA distributions.
- Product is marked spacing. [Reference table on page 4.](#)
- PS available in self-flanged MW finish only.
- Offered up to 2000 lumens
- Flange is the same finish as the reflector
- DMX fixtures default to full on upon loss of DMX signal.
- Refer to system specifications for additional information, features, and benefits. Order either factory installed option or accessory. Use with 0-10V driver.
- Non-IC

- WLST=WaveLinX LITE tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinX LITE system specifications)
- WPST=WaveLinX PRO wireless sensor kit for daylight dimming, PIR motion sensing, and optional RLTS - Real Time Location Services, use with 0-10V only.
- Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analysed under domestic preference requirements. Offered with spun aluminum narrow (N), medium (M), and wide (W) trims.
- WPN = WaveLinX PRO wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only.
- Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.
- Accessory (Requires knife edge accessory ring)
- Order die cast trim with flange type 4
- D010, D5LT, DE010 up to 4500 lumens with 98 CRI
- D010TR, DMX up to 3000 lumens with 98 CRI
- DLE, DL2 up to 2500 lumens with 98 CRI

- IC rated
- Tunable white IC rated with 1000 lumens
- Order with self flanged trim.
- Offered with DLVP up to 2000 lumens with 98 CRI.
- 120V-277V
- Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others)
- Not available with Lutron drivers
- Not recommended for use with Wall Wash
- Available with narrow (N), medium (M) and medium 45° (MD), Shallow (S). Required for use with all IEMBOD6ST, IEM7, IEM14, IEMV7 and IEMV14 housings. Not offered with remote driver.
- WLN = WaveLinX LITE wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.
- Not compatible with 347V or Chicago plenum.

## Product Specifications

### Lower Shielding Reflector

- Painted die-cast aluminum or spun aluminum lower reflector with lensed upper optical chamber provides superior lumen output with minimal source brightness
- Spun reflectors are available in all Portfolio anodized finishes
- Available with non-conductive polymer reflector up to 2000 lumens
- Plaster lathing ring, knife edge and millwork ring accessory for flush reflector transition
- Decorative frosted acrylic ring provides a light glow in the ceiling

### Wall Wash Reflector

- Open Wall Wash** - wall wash reflector with gradient kicker offered in single, double and corner wall wash provides even vertical illumination with minimal source brightness.
- Rotatable Lensed Wall Wash** - Rotatable Lensed wall wash reflector offered in single and double wall wash provides even vertical illumination with minimal source brightness.

### Trim Retention

- Two torsion springs hold reflector flange tightly to the finished ceiling surface

### Plaster Frame/Collar

- Die-cast aluminum 1 ½" deep collar
- Accommodates up to 2" ceiling thickness

### Universal Mounting Bracket

- Accepts 1/2" Electric Metallic Tube (EMT), C-channel and bar hangers
- Adjusts 5" vertically from above and below the ceiling

### Junction box

- Four 1/2" and two 3/4" trade size pry outs positioned to allow straight conduit runs
- Lever connectors for simple push in wiring
- Listed for eight #12 AWG (four in, four out) 90°C conductors and feed thru branch wiring

### Thermal

- Aluminum heat sink conducts heat away from the LED module for improved performance and longer life

### LED System

- Contains a plurality of high brightness white LED's combined with a high reflectance upper reflector and convex transitional lens producing even distribution without pixilation
- Auto resetting, thermally protected, LED's are turned off when safe operating temperatures are exceeded
- Quick disconnect allows for tool-less replacement of LED engine from below ceiling
- 98 CRI L70 55,000 hours
- Color variation within 2-step MacAdam ellipses
- Available in 2700K, 3000K, 3500K, 4000K and 5000K correlated color temperature (CCT)

- 98 CRI** With a full-spectrum approach using broad-blue chip technology and special phosphor blends, Thrive is able to closely match the spectrum of the sun across all color temperatures. Benefits of the natural spectrum of the sun using Thrive include superior accurate color rendering, reduced eye strain, and a higher sense of emotional well-being.

### Driver

- Standard 120-277V 0-10V dimming driver provides flicker free dimming from 100% to 1%
- Optional 120V leading edge/0-10V, <1% 0-10V, Fifth Light, DMX or Lutron® Ecosystem
- Driver can be serviced from above or through the aperture
- Distributed low voltage power system combines power, lighting, and controls with ease of installation.
- Optional Magnetically guided snap in driver for ease of maintenance.

### Emergency Option

- Provides 90 minutes of standby lighting, meeting most life safety codes for egress lighting
- Available with integral or remote charge indicator and test switch
- Available Self-Test with remote charge indicator and test switch
- Emergency transfer device (ETRD) senses the loss of power regardless of local control settings allowing emergency power to the fixture.
- UL 924 listed
- EM14RSD with simplified battery replacement and self diagnostics

### Connected Lighting System

Two WaveLinX connected solutions to choose from. Refer to WaveLinX system specifications and application guides for details.

#### WaveLinX PRO Tilemount Sensor Kit

- WaveLinX PRO WPST tilemount sensor kit offers daylight dimming, PIR motion sensing, scene and zone configuration, automatic commissioning; and optional RLTS - Real Time Location Services available.

#### WaveLinX PRO Wireless Node

- WaveLinX PRO WPN wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. **Note:** Not compatible with 347V or Chicago plenum.

#### WaveLinX LITE Tilemount Sensor Kit

- WaveLinX LITE WLST tilemount sensor kit offers daylight dimming and PIR motion sensing, scene and grouping configuration.

#### WaveLinX LITE Wireless Node

- WaveLinX LITE WLN wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with 0-10V driver only. **Note:** Not compatible with 347V or Chicago plenum.

#### WaveLinX Tilemount Sensor Kits Application

- The WPST and WLST tilemount sensor kits include a control module mounted on the luminaire junction box via 1/2" knock-out, and a tilemount sensor on 54-inch whip; for ceiling installation by direct-mount spring clips or via mounting bracket in octagon ceiling boxes.
- The WPST and WLST tilemount sensor kits may be ordered as factory installed on the luminaire, or ordered separately as a field installed accessory kit.
- Note: WaveLinX PRO devices are only compatible with the WaveLinX PRO system.**
- Note: WaveLinX LITE devices are only compatible with the WaveLinX LITE system.**

#### Code Compliance

- Thermally protected
- cULus Certified to UL 1598 / C22.2 No. 250.0 suitable for wet locations with downlight and lens wall wash; damp location with open wall wash with covered ceiling
- IP66 rated when used with IP66 gasket kit accessory
- Use IP66 gasket with non conductive reflector for steam room applications up to 2000 lumens and 40°C.
- Optional City of Chicago environmental air (CCEA) marking for plenum applications
- FCC CFR Title 47 Part 15 Class B at 120VAC and Class A at 277VAC
- Insulated ceiling (IC) rated up to 800 lumens (98 CRI & D2W); 1000 lumens (W2N). All others are non-IC rated (insulation must be kept 3" from top and sides of housing).
- Can be used for State of California Title 24 high efficacy LED compliance under JA8, reference Modernized Appliance Efficiency Database System (MAEDBS) for 2016 JA8 High Efficacy Lighting
- RoHS compliant
- Photometric testing completed in accordance with IES LM-79
- LED life testing completed in accordance with IES LM-80-08 and TM-21-11 standards
- See table on page 3 for marked spacing requirements

#### Warranty

- Five year warranty [www.cooperlighting.com/legal](http://www.cooperlighting.com/legal)



## Marked Spacing

4-inch Marked spacing for 98 CRI


Lumens	Center to Center of Adjacent Luminaire (inches)	Center Luminaire to Building Side Member (inches)	Minimum Overhead Height (inches)
3000-6000	36	18	8

## Dimensional and Mounting Details


DOWNLIGHT



WALL WASH




## Emergency Option




Trim with E option



Trim with EM6 option



Knife edge Trim



Rimless Trim

CATALOG #	Thrive		MAX HEIGHT			
	Flange DIAMETER or WIDTH [IN]	INSIDE DIAMETER [IN]	250-800 LUMENS	1000-2500 LUMENS	3000-4500 LUMENS	5000-9000 LUMENS
4LBN	5.67	4.24	5.6	5.6	5.6	8.1
4LBM	5.67	4.26	5.6	5.6	5.6	8.1
4LBW	5.67	4.27	5.6	5.6	5.6	7.7
4LBBA	5.67	4.28	5.6	5.6	5.6	8.1
4LBMD	5.67	4.26	5.8	5.9	6.4	8.9
4LBHY	5.67	4.34	5.6	5.6	5.6	8.1
4LBS	5.67	4.23	5.6	5.6	5.6	6.4
4LBPS	5.67	4.23	5.6	5.6	5.6	6.5
4LBCS	5.67	4.23	5.6	5.6	5.6	6.5
4LBSWN	5.67	4.27	5.6	5.6	5.6	7.7
4LBMDSW	5.67	4.26	5.8	5.9	6.4	8.9
4LBLSWW	5.67	4.27	5.6	5.6	5.6	7.7
4BLDWW	5.67	4.27	5.6	5.6	5.6	7.7

## Energy and Performance Data

## D010 DRIVER ENERGY DATA

Series	250 lumen		500 lumen		800 lumen		1000 lumen		1500 lumen		2000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.029	0.017	0.061	0.032	0.085	0.041	0.084	0.042	0.135	0.063	0.189	0.084
Input Power (W)	3.45	3.87	7.33	7.78	10.15	10.52	10.04	10.43	16.17	16.56	22.58	22.63
In-rush (A)	2.1	8.5	3.7	8.5	3.6	8.3	3.6	8.4	2.3	9.5	2.1	9.7
Inrush duration (μs)	250	131	190	136	220	135	226	136	230	125	243	132
THDi (%)	7.21	16.92	7.82	10.78	5.57	9.63	7.78	9.24	4.75	9.93	8.03	7.44
PF	≥ 0.98	≥ 0.9	≥ 0.99	≥ 0.93	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.94	≥ 0.99	≥ 0.96

Series	2500 lumen		3000 lumen		3500 lumen		4000 lumen		4500 lumen		5000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V	120V	277V
Input Current (A)	0.276	0.121	0.276	0.121	0.333	0.152	0.404	0.181	0.421	0.192	0.491	0.216
Input Power (W)	32.98	32.57	32	32.57	39.83	39.84	48.38	47.94	50.22	50.17	58.69	58.01
In-rush (A)	2.5	11.8	3.6	11.8	3.1	14.3	3.1	14.5	5.6	22.6	5.6	22.6
Inrush duration (μs)	215	111	220	111	200	94	197	95	215	120	213	135
THDi (%)	9.86	6.57	5.57	6.57	4.25	10.05	5.02	7.97	6.12	8.35	8.51	7.92
PF	≥ 0.99	≥ 0.97	≥ 0.99	≥ 0.99	≥ 0.99	≥ 0.94	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.95	≥ 0.99	≥ 0.96

Series	5500 lumen		6000 lumen	
Input Voltage 120-277VAC	120V	277V	120V	277V
Input Current (A)	0.526	0.231	0.542	0.256
Input Power (W)	62.97	61.97	64.88	65.7
In-rush (A)	5.1	23.1	6.2	27.5
Inrush duration (μs)	217	138	188	101
THDi (%)	9.42	7.16	4.33	11.86
PF	≥ 0.99	≥ 0.96	≥ 0.99	≥ 0.93

Minimum starting temperature -30°C (-22°F)\*  
(Nominal input 120-277VAC & 100% of rated output power)


Sound Rating: Class A standards

**Notes:**

Emergency Battery packs are rated for a minimum starting temperature of 0°C.

## COLOR METRICS - TM-30-15 &amp; CRI/CIE

## 98 CRI Color Metric Summary - 3500K\*



\* Color values are based on haze reflector, other finishes and field results may vary.

## Beam Angles

Trim	Beam Angle
4LBMH	MEDIUM BEAM 50° CUTOFF 65° BEAM (H)
4LBMLI	MEDIUM BEAM 50° CUTOFF 45° BEAM (LI)
4LBNH	NARROW 55° BEAM (H)
4LBNLI	NARROW 30° BEAM (LI)
4LBSh	SHALLOW 85° BEAM (H)
4LBShLI	SHALLOW 65° BEAM (LI)
4LBWH	WIDE 80° BEAM (H)

Trim	Beam Angle
4LBWLI	WIDE 80° BEAM (LI)
4LCShH	SINGLE WALL WASH (H)
4LCShLI	SINGLE WALL WASH (LI)
4LBWLI	LENSED WALL WASH (LI)
4LBWLI	LENSED WALL WASH (H)
4LBMDH	MEDIUM BEAM 45° CUTOFF 55° BEAM (H)
4LBMDLI	MEDIUM BEAM 45° CUTOFF 50° BEAM (LI)




The screenshot shows the WaveLinx Lite app interface. At the top, the status bar displays the time 12:55, signal strength, Wi-Fi, and battery level at 100%. The app title "WaveLinx Lite" is centered at the top. Below the title, there is a login section with two input fields: "Email" and "Password". To the right of the password field is a link that says "Forgot Password". Below these fields is a large, light gray button labeled "LOG IN". Underneath the login button, there is a registration section that says "By clicking on you agree to our Terms and Conditions" followed by a "Sign Up" button. At the bottom of the screen, the COOPER Learning Systems logo is displayed, featuring a red circular icon with a white 'C' and the text "COOPER Learning Systems".

**WaveLinx LITE devices only compatible with the WaveLinx LITE system.**

- Intuitive Android™ or Apple® iOS® app for basic system code compliant set up and configuration via Bluetooth
- Up to 28 unique areas per project site (WaveLinx LITE Bluetooth network)
- Up to 50 devices for an area, any one of 16 control zones, up to 6 occupancy sets, and custom lighting scenes
- Automatic occupancy or vacancy, sensor sensitivity, daylight dimming, etc. configurable through the app
- Refer to the WaveLinx system specifications for details



## WaveLinx LITE Bluetooth Enabled System




**WaveLinx PRO devices only compatible with the WaveLinx PRO system.**





- WaveLinx PRO Wireless functionality configures zones and customizes settings from one secure mobile app
- Automatic code commissioning that meets the strictest codes
- Fixtures and sensors integrate with Wireless Area Controller, Wall Stations, and Control Devices
- Stand-Alone Offices or Entire Building Network Installations



## WaveLinx mobile app settings



## WaveLinx CORE Building Management Integration



## Connected Solutions



### WaveLinX LITE Wireless Node - WLN


**WaveLinX LITE devices only compatible with the WaveLinX LITE system.**

- Intuitive Android™ or Apple® iOS® app for basic system code compliant set up and configuration via Bluetooth
- Up to 28 unique areas per project site (WaveLinX LITE Bluetooth network)
- Up to 50 devices for an area, any one of 16 control zones, up to 6 occupancy sets, and custom lighting scenes
- Refer to the WaveLinX system specifications for details
- **Not available with BioUp or Tunable White**

#### WaveLinX mobile app settings



#### WaveLinX LITE Wireless Node (WLN) Wiring Diagram



#### WaveLinX LITE Bluetooth Enabled System




### WaveLinX PRO Wireless Node - WPN

**WaveLinX PRO devices only compatible with the WaveLinX PRO system.**


- WaveLinX Wireless functionality configures zones and customizes settings from one secure mobile app
- Automatic code commissioning that meets the strictest codes
- Fixtures and sensors integrate with WaveLinX Area Controller, Wall Stations, and Control Devices
- Stand-Alone Offices or Entire Building Network Installations




#### WaveLinX mobile app settings



#### WaveLinX PRO Wireless Node (WPN) Wiring Diagram



#### WaveLinX CORE Building Management Integration





## Multi-line Order Information

SAMPLE ORDER NUMBER: **LD4C10D010TRIEM14**

Invoice will indicate separate fixture components (housing, trim, module) and may ship from multiple CLS facilities in separate cartons.

Single line Ordering  
Information Option

Domestic Preferences <sup>(1)</sup>	Housing	Lumens <sup>(2)</sup>				Color Control
<b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act	<b>LD4C</b> =LED Downlight 4-inch Nominal Aperture <b>LD4CCP</b> =LED Downlight 4-inch Nominal Aperture, Chicago Plenum	<b>02</b> =250 lumens <b>05</b> =500 lumens <b>08</b> =800 lumens <b>10</b> =1000 lumens	<b>15</b> =1500 lumens <b>20</b> =2000 lumens <b>25</b> =2500 lumens	<b>30</b> =3000 lumens <sup>(3)</sup> <b>35</b> =3500 lumens <sup>(3)</sup> <b>40</b> =4000 lumens <sup>(3)</sup>	<b>45</b> =4500 lumens <sup>(3)</sup> <b>50</b> =5000 lumens <sup>(3)</sup> <b>60</b> =6000 lumens <sup>(3)</sup>	<b>FS</b> =Full spectrum (Thrive) used with 98 CRI light engine

Driver						Information below for reference only.
						Remote driver & plug in driver
<b>D010</b> =0-10V Dimming, 1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1D010</b> =0-10V Dimming, 1% to 100%, 120V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>2D010</b> =0-10V Dimming, 1% to 100%, 277V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>3D010</b> =0-10V Dimming, 1% to 100%, 347V dedicated drivers, 800-3000 lumens & 250, 500, 3500 and above use step down transformer (250 to 4500 lumens for remote driver) <b>1 driver:</b> 250-4500 lumens; <b>2 drivers:</b> 5000-6000 lumens						250-4500
<b>D010TR</b> =0-10V (120-277V) or Phase-Cut (120V) dimming, 1-100%, 250-3000 lumens (up to 2000 lumens for remote driver) <b>1D010TR</b> =0-10V or Phase-Cut Dimming, 1% to 100%, 120V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <b>2D010TR</b> =0-10V Dimming, 1% to 100%, 277V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <b>3D010TR</b> =0-10V Dimming, 1% to 100% 347V step down transformer, 250-6000 lumens (250 to 3000 lumens for remote driver) <b>1 driver:</b> 250-3000 lumens; <b>2 drivers:</b> 3500-6000 lumens						250-3000
<b>DE010</b> =0-10V Dimming, 0.1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1DE010</b> =0-10V Dimming, 0.1% to 100%, 120V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>2DE010</b> =0-10V Dimming, 0.1% to 100%, 277V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>3DE010</b> =0-10V Dimming, 0.1% to 100%, 347V step down transformer, 500-6000 lumens (500 to 4500 lumens for remote driver) <b>1 driver:</b> 500-4500 lumens; <b>2 drivers:</b> 5000-6000 lumens						500-4500
<b>D5LT</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V-277V, 500-4500 lumens (up to 2000 lumens for remote driver) <b>1D5LT</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>2D5LT</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 277V, 5000-6000 lumens (2500 to 4500 lumens for remote driver) <b>3D5LT</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 347V step down transformer, 500-6000 lumens (500 to 4500 lumens for remote driver) <b>1 driver:</b> 500-4500 lumens; <b>2 drivers:</b> 5000-6000 lumens						500-4500
<b>DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, 800-3000 lumens (up to 2000 lumens for remote driver) <sup>(5)</sup> <b>1DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(5)</sup> <b>2DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(5)</sup> <b>3DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 347V step down transformer, 800-6000 lumens (800 to 3000 lumens for remote driver) <sup>(5)</sup> <b>1 driver:</b> 800-3000 lumens; <b>2 drivers:</b> 3500-6000 lumens						800-3000
<b>DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, RJ45 Connection, 800-3000 lumens (up to 2000 lumens for remote driver) <sup>(5)</sup> <b>1DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, RJ45 Connection, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(5)</sup> <b>2DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, RJ45 Connection, 3500-6000 lumens (2500 to 3000 lumens for remote driver) <sup>(5)</sup> <b>3DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 347V step down transformer, RJ45 Connection, 800-6000 lumens (800 to 3000 lumens for remote driver) <sup>(5)</sup> <b>1 driver:</b> 800-3000 lumens; <b>2 drivers:</b> 3500-6000 lumens						800-3000
<b>DLE</b> =Lutron Ecosystem dimming 1% to 100%, 120V-277V, 800-2500 lumens (up to 2000 lumens for remote driver) <b>1DLE</b> =Lutron Ecosystem dimming 1% to 100%, 120V, 3000-5000 lumens (2500 lumens for remote driver) <b>2DLE</b> =Lutron Ecosystem dimming 1% to 100%, 277V, 3000-5000 lumens (2500 lumens for remote driver) <b>3DLE</b> =Lutron Ecosystem dimming 1% to 100%, 347V with step down transformer, 800-5000 lumens (800 to 2500 lumens for remote driver) <b>1 driver:</b> 800-2500 lumens; <b>2 drivers:</b> 3000-5000 lumens						800-2500
<b>DLV</b> =Low voltage dimming driver (1-100%) for use with DLVP system, 800-2000 lumens <sup>(4)</sup>						800-2000 (Not offered with plug in driver)

Driver Options	Options <sup>(6)</sup> (29) (30)	
<b>Blank</b> =Integral driver <b>R</b> =Remote driver (order remote driver separately) <sup>(6)</sup> <b>PD</b> =Plug in Driver <sup>(6)</sup>	<b>EMBOD</b> =Bodine® 7W Emergency Module with Remote Test Switch <sup>(10)</sup> <b>EMBOD6ST</b> =Bodine® 6W Self Test Emergency Module with Remote Test Switch <b>EM7</b> =7W Emergency Module with Remote Test Switch <b>EM14</b> =14W Emergency Module with Remote Test Switch <b>EM14RSD</b> =14W Self Diagnostic Replaceable Emergency Battery Pack with Integral Test Switch <b>EMBOD7ST</b> =Bodine® 7W Self Test Emergency Module <sup>(10)</sup> <b>IEMBOD</b> =Bodine® Emergency Module with Integral Test Switch <sup>(10)</sup> (22) <b>IEM7</b> =7W Emergency Module with Integral Test Switch <sup>(22)</sup> <b>IEM14</b> =14W Emergency Module with Integral Test Switch <sup>(22)</sup>	<b>IEM14RSD</b> =14W Self Diagnostic Replaceable Emergency Battery Pack with Remote Test Switch <sup>(22)</sup> <b>IEMBOD6ST</b> =Bodine® 6W Self Test Emergency Module with Integral Test Switch <sup>(4)</sup> <b>EMV7</b> =7W Low Voltage Emergency Module with Remote Test Switch <sup>(7)</sup> <b>EMV14</b> =14W Low Voltage Emergency Module with Remote Test Switch <sup>(7)</sup> <b>ETRD</b> =Emergency transfer device <sup>(31)</sup> <b>WPST</b> =Factory installed Wavelinx (includes control module, sensor, cable, tilemount and ceiling mount sensor) <sup>(11)</sup> (13) <b>WLST</b> =Factory installed Wavelinx LITE Sensor Kit <sup>(11)</sup> (12) <b>WPN</b> =Wavelinx PRO Wireless Node without sensor <sup>(15)</sup> (37) <b>WLN</b> =Wavelinx LITE Wireless Node without Sensor (not compatible with Tuneable White) <sup>(36)</sup> (37)

Continued on next page.

## Multi-line Order Information (continued)

SAMPLE ORDER NUMBER: EU4C10209035

Domestic Preferences <sup>(1)</sup>	Power Module	Lumen Levels <sup>(2)</sup>	Color
<b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act	<b>EU4C</b> =4-inch Universal LED Module	<b>One 98 CRI THRIVE LED for use with one driver</b> <b>0208IC</b> =250, 500 and 800 lumens 98 CRI, IC rated (For use with all drivers, min 500 lumens with DE010 and D5LT, min 800 lumens with DLVP, Lutron and DMX) <b>1025</b> =1000, 1500, 2000 and 2500 lumens, 98 CRI (For use with D010, D010TR, DE010, DMX and Lutron 1000-2500 lumens. DLVP 1000-2000 lumens) <b>3045</b> =3000, 3500, 4000 and 4500 lumens, 98 CRI (For use with D010, D5LT and DE010 3000-4500 lumens, D010TR and DMX 3000 lumens) <sup>(3)</sup>  <b>Two 98 CRI THRIVE LED for use with two drivers</b> <b>30452</b> =3000, 3500, 4000 and 4500 lumens, 98 CRI (For use with Lutron 3000-4500 lumens, D010TR and DMX 3500-4500 lumens) <sup>(3)</sup> <b>5060</b> =5000 and 6000 lumens, 98 CRI (For use with D010, DE010 and D5LT 5000-9000 lumens, D010TR and DMX 5000-6000 lumens, Lutron 5000 lumens) <sup>(3)</sup>	<b>98 CRI</b> <b>9827</b> =2700K <b>9830</b> =3000K <b>9835</b> =3500K <b>9840</b> =4000K <b>9850</b> =5000K

SAMPLE ORDER NUMBER: 4LB2MH

Domestic Preferences <sup>(1)</sup>	Trim	Reflector	Flange	Finish	Options	
<b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act	<b>4LB</b> =4" LED	<b>N</b> =Narrow, Spun Aluminum <sup>(8) (23)</sup> <b>M</b> =50° Cutoff, Medium Beam Reflector, Spun Aluminum <b>MD</b> =45° Cutoff, Medium Beam Reflector, Spun Aluminum <b>W</b> =Wide, Spun Aluminum <b>S</b> =Shallow, Spun Aluminum <b>PS</b> =Non-Conductive Shallow (dead front), white <sup>(16) (17)</sup> <b>CS</b> =Cast Shallow, Die Cast Aluminum <b>BA</b> =Spun Aluminum Baffle <sup>(24)</sup>	<b>Wall Wash</b> <b>SWN</b> =Single wall wash, spun aluminum <b>DWN</b> =Double wall wash, spun aluminum <b>CW</b> =Corner wall wash, spun aluminum <b>MDSW</b> =45° Cutoff, Single Wall Wash, Spun Aluminum <b>MDDW</b> = 45° Cutoff, Double Wall Wash, Spun Aluminum <b>LSWW</b> =Lensed single wall wash, spun aluminum <b>LDWW</b> =Lensed double wall wash, spun aluminum	<b>0</b> =White polymer trim ring <b>1</b> =Self flanged <sup>(18)</sup> <b>2</b> =White painted self flanged <b>4</b> =Knife edge rimless use with die cast only <sup>(19)</sup>	<b>LI</b> =Specular Clear <sup>(20)</sup> <b>H</b> =Semi-Specular Clear <sup>(20)</sup> <b>WMH</b> =Warm Haze <sup>(20)</sup> <b>WH</b> =Wheat <sup>(20)</sup> <b>GPH</b> =Graphite Haze <sup>(20)</sup> <b>B</b> =Specular Black <sup>(20)</sup> <b>MW</b> =Matte White <b>MB</b> =Matte Black <sup>(21)</sup> <b>MMS</b> =Matte Metallic Silver <sup>(21)</sup>	<b>E</b> =Integral Emergency Test Switch Hole <sup>(22)</sup> For use with IEM <b>EM6</b> =Integral Emergency Test Switch Hole <sup>(26)</sup> For use with IEMBOD6ST: • Available with narrow (N), medium (M) and medium 45° (MD)

REQUIRED if Remote Driver (R) is specified

SAMPLE ORDER NUMBER: RC10010D010TREM7

Domestic Preferences <sup>(1)</sup>	Remote Drivers <sup>(6)</sup>	Lumens <sup>(2) (14)</sup>	Color Control
<b>[Blank]</b> =Standard <b>BAA</b> =Buy American Act <b>TAA</b> =Trade Agreements Act	<b>RC100</b> =Remote 100ft <b>RC75</b> =Remote 75ft <b>RC50</b> =Remote 50ft <b>RC25</b> =Remote 25ft	<b>02</b> =250 lumens <b>05</b> =500 lumens <b>08</b> =800 lumens <b>10</b> =1000 lumens <b>15</b> =1500 lumens <b>20</b> =2000 lumens <b>25</b> =2500 lumens <b>30</b> =3000 lumens <b>35</b> =3500 lumens <b>40</b> =4000 lumens <b>45</b> =4500 lumens	<b>FS</b> =Full spectrum (Thrive) used with 98 CRI light engine up to 6,000 lumens

Driver	Specify from Driver column. Information below for reference only.
	<b>98 CRI</b>
<b>D010</b> =0-10V Dimming, <1% to 100%, 120V-277V, 500-2000 lumens <b>1D010</b> = 0-10V Dimming, <1% to 100%, 120V, 2500-4500 lumens <b>2D010</b> = 0-10V Dimming, <1% to 100%, 277V, 2500-4500 lumens <b>3D010</b> = 0-10V Dimming, <1% to 100%, 347V dedicated driver 800-3000 lumens, with step down transformer for 98 CRI 250, 500 and 3500-4500 lumens	250-4,500
<b>D010TR</b> =0-10V (120-277V) or Phase-Cut (120V) dimming, 1-100%, 250-2000 lumens <b>1D010TR</b> = 0-10V or Phase-Cut Dimming, 120V, 1-100%, 2500-3000 lumens <b>2D010TR</b> = 0-10V Dimming, 277V, 1-100%, 2500-3000 lumens <b>3D010TR</b> = 0-10V Dimming, 347V with step down transformer, 1-100%, 250-3000 lumens	250-3,000
<b>DE010</b> =0-10V Dimming, 0.1% to 100%, 120V-277V, 500-2000 lumens <b>1DE010</b> = 0-10V Dimming, 0.1% to 100%, 120V, 2500-4500 lumens <b>2DE010</b> = 0-10V Dimming, 0.1% to 100%, 277V, 2500-4500 lumens <b>3DE010</b> = 0-10V Dimming, 0.1% to 100%, 347V with step down transformer, 500-4500 lumens	500-4,500
<b>D5LT</b> =Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V-277V, 500-2000 lumens <b>1D5LT</b> = Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 120V, 2500-4500 lumens <b>2D5LT</b> = Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 277V, 2500-4500 lumens <b>3D5LT</b> = Fifth Light® (DALI T6) Logarithmic Dimming, 0.1% to 100%, 347V with step down transformer, 500-4500 lumens	500-4,500
<b>DMX</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, 800-2000 lumens <sup>(5)</sup> <b>1DMX</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, 2500-3000 lumens <sup>(5)</sup> <b>2DMX</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, 2500-3000 lumens <sup>(5)</sup> <b>3DMX</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 347V with step down transformer, 800-3000 lumens <sup>(5)</sup>	800-3,000

Multi-line Order Information (continued)

<b>DMXC5</b> =DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V-277V, RJ45 connection, 800-2000 lumens <sup>(5)</sup> <b>1DMXC5</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 120V, RJ45 connection, 2500-3000 lumens <sup>(5)</sup> <b>2DMXC5</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 277V, RJ45 connection, 2500-3000 lumens <sup>(5)</sup> <b>3DMXC5</b> = DMX/RDM Logarithmic Dimming, 0.1% to 100%, 347V with step down transformer, RJ45 connection, 800-3000 lumens <sup>(5)</sup>	800-3,000
<b>DLE</b> =Lutron Ecosystem dimming 1% to 100%, 120V-277V, 25' Max remote length, 800-2000 lumens <b>1DLE</b> = Lutron Ecosystem dimming 1% to 100%, 120V, 25' Max remote length, 2500 lumens <b>2DLE</b> = Lutron Ecosystem dimming 1% to 100%, 277V, 25' Max remote length, 2500 lumens <b>3DLE</b> = Lutron Ecosystem dimming 1% to 100%, 347V with step down transformer, 25' Max remote length, 800-2500 lumens	800-2,500
<b>DLV</b> =Low voltage dimming driver (1-100%) for use with DLVP system, 800-2000 lumens <sup>(6)</sup>	800-2,000

Options <sup>(6)</sup> <sup>(30)</sup>	Controls
<b>EMBOD</b> =Bodine® Emergency Module with Remote Test Switch <sup>(10)</sup> <b>EMBOD6ST</b> =Bodine® 6W Self Test Emergency Module with Remote Test Switch <b>EM7</b> =7W Emergency Module with Remote Test Switch <b>EM14</b> =14W Emergency Module with Remote Test Switch	<b>WPST</b> =Factory installed Wavelinx (includes control module, sensor, cable, tilemount and ceiling mount sensor) <sup>(11)</sup> <sup>(13)</sup> <b>WLST</b> =Factory installed WaveLinX LITE Sensor Kit <sup>(11)</sup> <sup>(12)</sup> <b>WPN</b> = WaveLinX PRO Wireless Node without sensor <sup>(15)</sup> <sup>(37)</sup> <b>WLN</b> = WaveLinX LITE Wireless Node without Sensor <sup>(36)</sup> <sup>(37)</sup>

Accessories (Order separately) <sup>(25)</sup>			
<b>TRM4P</b> =White metal trim ring <sup>(26)</sup> <b>LGSKT4IP66</b> =IP66 Gasket Kit <b>DT4RF</b> =4 inch frosted acrylic ring <sup>(28)</sup>  <b>PRR4</b> =Rimless Plaster Ring <sup>(26)</sup> <b>RKP4</b> =Knife Edge plaster Ring <sup>(27)</sup>	<b>RPM4MW</b> =Rimless Millwork Ring, Matte White <sup>(26)</sup> <b>RPM4MB</b> =Rimless Millwork Ring, Matte Black <sup>(26)</sup> <b>RKM4MW</b> =Knife Edge Millwork Ring, Matte White <sup>(27)</sup> <b>RKM4MB</b> =Knife Edge Millwork Ring, Matte Black <sup>(27)</sup>  <b>HSA4</b> =Slope Adapter for 4" Aperture Housings, Specify Slope <sup>(34)</sup>	<b>Connected Lighting Systems</b> <sup>(6)</sup> <sup>(11)</sup> <b>WPST</b> =Field installed WaveLinX sensor Kit <sup>(13)</sup> <b>WLST</b> =Field installed WaveLinX LITE Sensor Kit <sup>(12)</sup>  <b>Transformers</b> <b>H347</b> =H347 for 98CRI 4000 lumens and below	<b>Bar Hangers</b> <b>BAA-HB26</b> =C-channel Bar Hanger, 26" Long, Pair <sup>(1)</sup> <b>TAA-HB26</b> =C-channel Bar Hanger, 26" Long, Pair <sup>(1)</sup> <b>HB26</b> =C-channel Bar Hanger, 26" Long, Pair <b>HB50</b> =C-channel Bar Hanger, 50" Long, Pair <b>RMB22</b> =Wood Joist Bar Hanger, 22" Long, Pair

- Notes:**

**1.** Only product configurations with these designated prefixes are built to be compliant with the Buy American Act of 1933 (BAA) or Trade Agreements Act of 1979 (TAA), respectively. Please refer to [DOMESTIC PREFERENCES](#) website for more information. Components shipped separately may be separately analysed under domestic preference requirements. Offered with spun aluminum narrow (N), medium (M) and wide (W) trims.

**2.** Nominal Lumens will vary depending on selected color, CRI, driver and reflector finish. Reference IES files.

**3.** Product is marked spacing. [Reference table on page 4 for the spacing details.](#)

**4.** Available with narrow (N), medium (M) and medium 45° (MD), Shallow (S). Required for use with all IEMBOD6ST, IEM7, IEM14, IEMV7 and IEMV14 housings. Not offered with remote driver.

**5.** DMX fixtures default to full on upon loss of DMX signal.

**6.** Not available with Chicago Plenum.

**7.** ULus listed only

**8.** - D010, D5LT, DE010 up to 4500 lumens with 98 CRI  
- D010TR, DMX up to 3000 lumens with 98 CRI  
- DLE, DL2 up to 2500 lumens with 98 CRI

**11.** Refer to system specifications for additional information, features, and benefits. Order either factory installed option or accessory. Use with 0-10V driver.
- 12.** WLST=WaveLinX LITE tilemount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinX LITE system specifications)

**13.** WPST=WaveLinX PRO wireless sensor kit for daylight dimming, PIR motion sensing, and optional RLTS - Real Time Location Services, use with 0-10V only.

**15.** WPN = WaveLinX PRO wireless node provides luminaire-level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.

**16.** PS available in self-flanged MW finish only

**17.** Offered up to 2000 lumens

**18.** Flange is the same finish as the reflector

**19.** Requires knife edge ring accessory.

**20.** Anodized or spun reflectors

**21.** Die cast only

**22.** Available with narrow (N), medium (M) and medium 45 degree (MD) Spun Aluminum trims. Required for use with all IEMBOD, IEM7, IEM14, IEMV7 and IEMV14 housings. Not offered with remote driver.

**23.** Offered with DLVP up to 2000 lumens with 98 CRI.

**24.** Black or white paint.
- 25.** Accessories sold separately will be separately analyzed under domestic preference requirements. Consult factory for further information.

**26.** Order trim with polymer trim ring (Consult specification sheet for color ordering information and options).

**27.** Order die cast trim with flange type 4

**28.** Order with self flanged trim.

**29.** If using remote driver order battery and controls with the remote driver.

**30.** 120V-277V

**31.** Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others)

**32.** IC rated for 800 lumens

**33.** IC rated for 1000 lumens

**34.** Not recommended for use with Wall Wash

**36.** WLN = WaveLinX LITE wireless node provides luminaire level control with scene and zone configuration without an integrated sensor; Connects wirelessly with daylight dimming sensor and PIR motion sensor if desired. Use with D010 or DE010 drivers only.

**37.** Not compatible with 347V or Chicago plenum.

**38.** Required for use with IEMBOD6ST. Not offered with remote driver.