

|             |  |           |  |      |  |
|-------------|--|-----------|--|------|--|
| Project     |  | Catalog # |  | Type |  |
| Prepared by |  | Notes     |  | Date |  |



## WaveLinux Pro

### Relay Switchpack with 0-10V

Relay switchpack with 0-10V control

#### Typical Applications

Office • Education • Healthcare • Hospitality • Retail  
Industrial • Manufacturing

#### Interactive Menu

- Order Information page 2
- Additional Resources page 3
- Wiring Diagrams page 4
- Connected Systems page 5
- Product Warranty

#### Product Certification



- Meets latest ASHRAE Standard 90.1 requirements
- Meets latest IECC requirements
- Meets latest CEC Title 24 requirements
- Manufactured in an ISO 9001 certified factory


#### Product Features



#### Top Product Features

- Output control loads up to 20amps or 1.5 HP and 0-10V dimming control
- Plenum rated design with easy junction box mounting
- Universal voltage input (120V-277V)
- Fails safe to 100% if communications are lost
- Energy calculations available through Trellix

#### Dimensional Details



## Order Information

The WaveLinX Pro Dimming Switchpack is an accessory to the WaveLinX Pro connected lighting (WCL) system and requires a Wireless Area Controller (WAC) for full functionality.

The wireless relay is used to control plug loads or luminaires that do not include the wireless integrated sensor.

### Catalog Number

| Catalog Number | Description                          |
|----------------|--------------------------------------|
| WSP-MV-010     | Wireless Relay Switchpack with 0-10V |

## Required Accessories

All WaveLinX Pro connected lighting (WCL) system accessories require at least one WaveLinX Pro Wireless Area Controller (WAC) for communications. Ensure the bill of material includes one of the following components.

### Catalog Number

| Catalog Number | Description                           |
|----------------|---------------------------------------|
| WAC-POE        | Wireless Area Controller, POE powered |

## Optional Accessories

For connection to 120VAC outlets.

### Catalog Number

| Catalog Number | Description            |
|----------------|------------------------|
| WPOE-120       | 120VAC to PoE Injector |

## Product Specifications

### Key Features

- Output control for the following
  - 0-10V continuous dimmable luminaires
  - LED loads up to 20A
  - Receptacle loads up to 20A
  - Motor loads to 1.5 HP
- Plenum rated design with easy junction box mounting
- Device identification LED
- Universal voltage input (120V-277V)
- Designed with safety in mind, at loss of communications with Wireless Area Controller, the wireless relay switchpack will turn ON and set dimmer to 70% light level
- Energy calculations available through Trellix

### Mechanical

**Size:** 1.7"H x 2.6"W x 6.1"L (43mm x 66mm x 155mm)

### Environment:

- Operating temperature:** 32°F to 104°F (0°C to 40°C)
- Storage temperature:** 32°F to 158°F (0°C to 70°C)
- Relative humidity operating:** 10% to 90% RH (non-condensing)
- For indoor use only

**Mounting:** Mounts to the side of a 4" (102mm) square box via ½" (13mm) knockout

**Color:** Matte White

**Housing:** Medium impact injection molded housing. ABS resin with 5VA flame rating. Plenum rated for external junction box mounting with Teflon coated leads.

### Electrical

#### Power:

- 120-277VAC (+/- 10%) 50/60Hz
- 5mA (120V) / 10mA (277V)

#### Output Information:

- 20amp 120/277VAC General Purpose
- 16amp 120/277VAC electronic ballast (LED load)
- Single class 2 0-10V dimming output (IEC 60929 Annex E) sinks up to 120mA per (40 µA max per circuit leakage to line)
- 0-10V output supports up to 60 ballasts/drivers that draw a standard 2mA each

### Wireless Specifications

**Radio:** 2.4GHz

**Standard:** IEEE 802.15.4

**Transmitter Power:** + 7dBm

**Range:** 150ft (46m) LOS

50ft (15m) through standard walls when mounted outside junction box

**# of Walls:** 2 interior walls standard construction

### System Performance

**Maximum number of Devices:** 150 per Wireless Area Controller (best practice 100 devices)

### Standards/Ratings


- cULus Listed - Energy Management Equipment (UL916)
- Manufactured in an ISO 9001 certified factory
- Meets latest ASHRAE Standard 90.1 requirements
- Meets latest IECC requirements
- Meets latest CEC Title 24 requirements

### Warranty

Five year warranty standard

## System Architecture



This diagram shows the main components of the WaveLinx Pro connected lighting (WCL) system. The WCL system communicates using wireless mesh technology based on the 802.15.4 standard. A POE LAN connection for each Wireless Area Controller (WAC) is required for power and data access to the building wireless network. System setup is achieved through a simple mobile application via wireless communication to the system.



## Overview

The WaveLinx Pro Relay switchpack with 0-10V (WSP-MV-010) control is an integral part of the WaveLinx Pro connected lighting (WCL) system and offers 120-277VAC 20amp zero crossing relay control and continuous 0-10V dimming control of LED and non LED loads. The relay switchpack with 0-10V control also supports 20amp plug load control. The WSP-MV-010 is powered by the 120-277VAC circuit it is controlling and provides simple 1/2" knockout mounting. The relay switchpack with 0-10V control operates on a wireless mesh network based on IEEE 802.15.4 standards.

## Mounting



## Connected Systems

- Trellix

## Better Data. Better Decisions.

Trellix combined with our WaveLinX Pro connected lighting system is a distributed network of LED lighting fixtures with integrated sensing and beacon technology that captures real-time data; making your facility smarter so you can make smarter decisions.

Trellix provides an open IoT platform and infrastructure that connects intelligent sensors leveraging the real-estate of the physical light fixture to solve higher complexity problems in a commercial building to deliver actionable insights through the aggregation of valuable data.

