

DESCRIPTION

A series of understated, balanced lampholders that come in a variety of lamp types.

APPLICATION

Ideal for accent and display lighting applications. This 150W PAR38 lampholder is perfect for those applications where performance is required from a discreet source.

Catalog #	Type
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Flexible Track

Die Cast housing. Attaches electrically and mechanically anywhere along track.

B ... Electrical Quick Lock Adapter - Power Trac

Die Cast housing. Attaches electrically and mechanically anywhere along track.

C ... Electrical Quick Lock Adapter - Architectural Track

Polycarbonate housing with integral fuse and on-off switch. Attaches electrically and mechanically anywhere along track.

D ... Lockable Aiming


Lampholder tilt can be locked in place easily with the use of a 1.5mm allen wrench.

E ... Lampholder Body

Die Cast Aluminum body with threaded screw-on bezel for positive engagement.

Labels

UL/c-UL Listed for use with Halo Architectural Linear and Flexible Track, Halo Power-Trac, and Lazer Track.



LF10538
LA10538
L10538

Stasis
150W PAR38 Accent

Flexible Track
Architectural Track
Power-Trac

LF
L=7.6" [193mm]
W=6.4" [162mm]
Max Extension=8.9"
[226mm]

L
L=7.6" [193mm]
W=6.4" [162mm]
Max Extension=9.4"
[238mm]


LA
L=7.6" [193mm]
W=6.4" [162mm]
Max Extension=8.4"
[213mm]

	1	05	38		
Track	Lamp Type	Series	Lamp	Finish	Accessories
LF=Flexible Track L=Halo Track LA=Halo Architectural Track Systems	1=Incandescent	05=Stasis	38=PAR38	AH=Aluminum Haze P=White (L and LA only) MB=Black (L and LA only)	LM10538=PAR38 Media Holder

• Product is only available in 120 volts.

Media Holder

LM10538=PAR38 Media Holder



Media Holder

L200 Color Filters

L211=Medium Pink Color Filter

L212=Warm Red Color Filter


L214=Ultraviolet Filter

L220=Daylight Blue Color Filter

L221=Medium Blue Color Filter

L231=Medium Amber Color Filter

L241=Medium Green Color Filter



L200 Series Color Filters

L200 Series Optical Lenses

L210=Linear Spread Lens

L210 lens fans out light beam 55° - 27 1/2° each side of center

L215=Radial Spread Lens



L215 lens spreads light beam 30° in all directions - 15° on all sides of center

L250=Linear Spread Lens

L250 lens spreads light beam in one direction

L265=Prismatic Spread Lens


L265 Spreads light beam in all directions



L200 Lenses

L275 Cube Cell Louver

4 3/4" OD (121mm). Black finish 1/2" cells for directing light and eliminating glare.



L275 Cube Louver