

DESCRIPTION

A series of lampholders employing simple geometric shapes that create bold statements in any application. Toolless lockable tilt and rotation with graduations for precise, repeatable aiming. Three media capable, these 250W PAR38 lampholders are comfortable in applications from Gallery to Specialty Retail. Threaded screw-on bezel provides positive engagement, and removable beveled spacer creates an attractive look when multiple media are not required. Ideal for accent and display lighting applications.

Catalog #	Type
Project	
Comments	Date
Prepared by	

SPECIFICATION FEATURES

A ... Electrical Quick Lock Adapter - Flexible Track

Die Cast housing. Attaches electrically and mechanically anywhere along track.

B ... Electrical Quick Lock Adapter - Power Trac

Die cast housing. Attaches electrically and mechanically anywhere along track.

C ... Electrical Quick Lock Adapter - Architectural Track

Polycarbonate housing with integral fuse and on-off switch. Attaches electrically and mechanically anywhere along track.

D ... Yoke

Aluminum die cast yoke allows lampholder to rotate 330° and provides 0° to 90° vertical pivot for maximum aiming adjustability.

E ... Lockable Aiming

Lampholder tilt and rotation can be locked in place easily without the use of tools.

F ... Lampholder Body

Machined, Extruded and Die Cast Aluminum cylinders.

G ... Graduated Dials

Graduated dials for precise aiming of fixture.

Labels


UL/c-UL Listed for use with Halo Architectural Linear and Flexible Track, Halo Power-Trac, Lazer.



LF10638
LA10638
L10638

Synchro
250W PAR38 Accent

Flexible Track
Architectural Track
Power-Trac



LF
L=7.56" [192mm]
W=5" [127mm]
Max Extension =
16.75" [425.45mm]


L
L=7.56" [192mm]
W=5" [127mm]
Max Extension =
17.00" [431.80mm]

LA
L=7.56" [192mm]
W=5" [127mm]
Max Extension =
16.80" [426.72mm]

	1	06	38	
Track	Lamp Type	Series	Lamp	Finish
LF=Flexible Track	1=Incandescent	06=Synchro	38=PAR38	AH=Aluminum Haze
L=Halo Power-Trac				P=White (L and LA only)
LA=Halo Architectural Track				MB=Black (L and LA only)

L200 Color Filters

- L211=Medium Pink Color Filter
- L212=Warm Red Color Filter
- L214=Ultraviolet Filter
- L220=Daylight Blue Color Filter
- L221=Medium Blue Color Filter
- L231=Medium Amber Color Filter
- L241=Medium Green Color Filter



L200 Series Color Filters

L200 Series Optical Lenses

L210=Linear Spread Lens

L210 lens fans out light beam 55° - 27 1/2° each side of center

L215=Radial Spread Lens


L215 lens spreads light beam 30° in all directions - 15° on all sides of center

L250=Linear Spread Lens

L250 lens spreads light beam in one direction

L265=Prismatic Spread Lens


L265 Spreads light beam in all directions



L200 Lenses

L275 Cube Cell Louver

4 3/4" OD (121mm). Black finish 1/2" cells for directing light and eliminating glare.



L275 Cube Louver

Remove beveled spacer when 2 or 3 media are used.