

HL3 Remodel 225 mA 0-10V Dimming

D010 250mA/1000 Lumens

Dimmer Make	Dimmer Series	Dimmer Model #	Types of Dimmer	Minimum Lamps or Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit) at 120V	Maximum Recommended Luminaires (per circuit) at 277V	Max Dimming percentage (%)	Min Dimming percentage (%)	Low End Start Time
Eaton	Slide Dimmer	SF10P	0-10v	1	96	135	100	1	<1S
Eaton	Decorator Dimmer	DF10P	0-10v	1	96	135	100	1	<1S
Leviton	Illumatech	IP710-DL	0-10v	1	57	57	100	1	<1S
Lutron	NTFTV	NOVA T	0-10v	1	61	61	100	1	<1S
Lutron	DIVA	DVTV	0-10v	1	57	57	100	1	<1S
Cooper Lighting Solutions	iLumin	SC277-06	0-10v	1	154	196	100	1	<1S
Cooper Lighting Solutions	Greengate	CK4A	0-10v	1	192	196	100	1	<1S

HL3 Remodel 300 mA 0-10V Dimming

D010 250mA/1000 Lumens

Dimmer Make	Dimmer Series	Dimmer Model #	Types of Dimmer	Minimum Lamps or Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit) at 120V	Maximum Recommended Luminaires (per circuit) at 277V	Max Dimming percentage (%)	Min Dimming percentage (%)	Low End Start Time
Eaton	Slide Dimmer	SF10P	0-10v	1	76	106	100	1	<1S
Eaton	Decorator Dimmer	DF10P	0-10v	1	76	106	100	1	<1S
Leviton	Illumatech	IP710-DL	0-10v	1	76	96	100	1	<1S
Lutron	NTFTV	NOVA T	0-10v	1	121	56	100	1	<1S
Lutron	DIVA	DVTV	0-10v	1	121	56	100	1	<1S
Cooper Lighting Solutions	iLumin	SC277-06	0-10v	1	121	188	100	1	<1S
Cooper Lighting Solutions	Greengate	CK4A	0-10v	1	151	185	100	1	<1S

HL3 Remodel 475 mA 0-10V Dimming

D010 250mA/1000 Lumens

Dimmer Make	Dimmer Series	Dimmer Model #	Types of Dimmer	Minimum Lamps or Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit) at 120V	Maximum Recommended Luminaires (per circuit) at 277V	Max Dimming percentage (%)	Min Dimming percentage (%)	Low End Start Time
Eaton	Slide Dimmer	SF10P	0-10v	1	47	66	100	1	<1S
Eaton	Decorator Dimmer	DF10P	0-10v	1	47	66	100	1	<1S
Leviton	Illumatech	IP710-DL	0-10v	1	47	60	100	1	<1S
Lutron	NTFTV	NOVA T	0-10v	1	75	168	100	1	<1S
Lutron	DIVA	DVTV	0-10v	1	75	168	100	1	<1S
Cooper Lighting Solutions	iLumin	SC277-06	0-10v	1	75	168	100	1	<1S
Cooper Lighting Solutions	Greengate	CK4A	0-10v	1	94	192	100	1	<1S

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	Standard 150 W LED+	AYCL-153P	1	15	9%	98%	<1S
Lutron	Standard 150 W LED+	CTCL-153P	1	15	9%	98%	<1S
Lutron	Standard 150 W LED+	DVCL-153P	1	15	9%	98%	<1S
Lutron	Standard 150 W LED+	SCL-153P	1	15	9%	98%	<1S
Lutron	Standard 150 W LED+	TGCL-153P	1	15	9%	98%	<1S
Lutron	Maestro	MACL-153M	1	15	9%	93%	<1S
Lutron	Sunnata	STCL-153P	1	15	9%	93%	<1S
Lutron	RadioRA 2	RRD-10ND	1	15	8%	91%	<1S
Lutron	HomeWorks QS	HQRD-10ND	1	14	8%	91%	<1S
Lutron	RadioRA 2	RRD-6NA	1	15	12%	100%	<1S
Lutron	HomeWorks QS	HQRD-6NA	1	15	12%	100%	<1S
Lutron	HomeWorks	HxD-6ND	1	9	8%	91%	<1S
Lutron	Stanza	SZ-6ND	1	5	8%	91%	<1S
Lutron	Power Modules	PPHM-PA with Grafik Eye QS Main Unit	1	36	10%	97%	<1S
Lutron	Power Modules	PPHM-WBX with 3-wire fluorescent control	1	36	10%	97%	<1S
Lutron	Panel Module	HW/LP-RPM-4U-120 (Forward Phase)	1	26	10%	98%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Reverse Phase)	1	36	10%	97%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Forward Phase)	1	15	10%	98%	<1S
Lutron	Grafik QS/Wallbox Power Module	"Grafik Eye QS Main Unit Family/ LQRJ-WPM-6P"	1	26	10%	98%	<1S
Lutron	Grafik T	Keypad RRT-GHxB/HQRT-GHxB	1	15	8%	91%	<1S
Lutron	Panel Module	GP (Harrier) Card	1	26	10%	98%	<1S
Lutron	Maestro Sensor	MSCL-OP153M(T2)	1	15	9%	93%	<1S
Lutron	Maestro Sensor	MSCL-VP153M(T2)	1	15	9%	93%	<1S
Lutron	Grafik Eye 3000/HomeWorks	Grafik Eye 3000 Family/HWI-WPM-6D-120	1	26	10%	98%	<1S
Lutron	RadioRA 2	RRD-6CL (R3)	1	15	8%	91%	<1S
Lutron	HomeWorks QS	HQRD-6CL (H2)	1	15	8%	91%	<1S
Lutron	HomeWorks QS	HQRA-6CL (H2)	1	15	8%	91%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (without neutral)	1	25	12%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (without neutral)	1	25	12%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (without neutral)	1	25	12%	100%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (with neutral)	1	25	12%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (with neutral)	1	25	12%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (with neutral)	1	25	12%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Forward Phase)	1	3	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Reverse Phase)	1	5	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Forward Phase)	1	3	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Forward Phase)	1	3	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Forward Phase)	1	3	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Forward Phase)	1	3	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Reverse Phase)	1	2	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Reverse Phase)	1	2	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Reverse Phase)	1	2	10%	99%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Reverse Phase)	1	2	10%	99%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Reverse Phase)	1	26	10%	99%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Reverse Phase)	1	26	10%	99%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Reverse Phase)	1	26	10%	99%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Reverse Phase)	1	26	10%	99%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Forward Phase)	1	8	10%	99%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Forward Phase)	1	8	10%	99%	<1S

HL3 Remodel 225 mA Triac Dimming

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Forward Phase)	1	11	10%	99%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Forward Phase)	1	11	10%	99%	<1S
Lutron	Grafik T	GT-5NEM	1	25	12%	100%	<1S
Lutron	Grafik T	GTJ-5NEM	1	25	12%	100%	<1S
Lutron	HomeWorks	HXD-5NE	1	9	12%	100%	<1S
Lutron	Skylark Contour Slide to Off	CTCL-150/LECL-150	1	15	9%	98%	<1S
Lutron	Dalia	RCL-153PNL	1	15	9%	98%	<1S
Lutron	Caseta Wireless Phase Selectable	PD-5NE	1	25	12%	100%	<1S
Lutron	Vive	MRF2S-6ELV	1	15	12%	100%	<1S
Lutron	Vive	MRF2S-6CL	1	15	8%	91%	<1S
Lutron	Maestro	MACL-LFQ	1	7	9%	93%	<1S
Lutron	Caseta Wireless	PD-6WCL (SD12)	1	15	8%	91%	<1S

HL3 Remodel 225 mA Triac Dimming

For Reference Only

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Leviton	Decora	6673	1	48	1%	97%	<1s
Leviton	SureSlide	6674	1	12	0%	100%	N.A. ¹
Leviton	SureSlide	6631-2	1	48	0%	100%	N.A. ¹
Leviton	Illumatech	IPL06	1	12	1%	98%	<1s
Leviton	Vizia	VPI06	1	48	1%	99%	<1s
Leviton	Decora	6161	1	40	1%	99%	<1s
Leviton	SureSlide	6633-P	1	48	0%	100%	N.A. ¹
Lutron	Toggler	TG-600P	1	48	0%	94%	N.A. ¹
Eaton	RF Smart	RF9540-N	1	24	1%	100%	<1s
Lutron	Toggler	TGCL-153P	1	12	7%	93%	<1s
Lutron	Lumea	LG600P	1	48	0%	98%	N.A. ¹
EWD	Universal	TUL06P-C2	1	24	1%	95%	<1s
EWD	Universal	SUL06P	1	24	1%	94%	<1s
Lutron	Skylark	SCL-153P-WH	1	12	1%	94%	<1s
Lutron	Diva	DV603P	1	48	0%	97%	N.A. ¹
Lutron	Diva	DVCL-153P	1	12	1%	94%	<1s
Lutron	Maestro	MACL-153-M	1	12	1%	87%	<1s
Leviton	Vizia	VPE06	1	48	1%	99%	<1s
Leviton	Legrand	H703PTU	1	24	1%	99%	<1s
Leviton	Vizia	VZE04	1	32	1%	99%	<1s
Lutron	Maestro	MAELV600	1	48	1%	99%	<1s
Lutron	Diva	DVELV303P	1	24	0%	96%	N.A. ¹
Lutron	Skylark	SELV300P	1	24	0%	98%	N.A. ¹
EWD	Smart	AAL06	1	24	0%	96%	N.A. ¹
Lightolier	Sunrise	ZP260QEW	1	20	1%	99%	<1s
Eaton	Aspire	9530AW	1	48	0%	100%	N.A. ¹
Eaton	Devine	DE06P	1	48	0%	85%	N.A. ¹
Eaton	React	RI061	1	48	0%	100%	N.A. ¹
Eaton	Devine	TAL06P	1	24	1%	100%	<1s
Eaton	Toggle	DAL06P	1	24	1%	100%	<1s
Eaton	Skye	SAL06P	1	24	1%	100%	<1s
Eaton	Skye	SLC03P	1	24	1%	100%	<1s
Eaton	Devine	DLC03P	1	24	1%	100%	<1s
Eaton	Toggle	TI061	1	48	0%	82%	N.A. ¹
Lutron	LCP128	LP-RPM-4U-120	1	35	0%	100%	N.A. ¹
Lutron	LCP128	LP-RPM-4A-120	1	22	0%	100%	N.A. ¹
Ecospec	LDCM	LDCM-PL-120-277-010V-GR	1	36	0%	100%	N.A. ¹
Lutron	Ariadni	AY-600P	1	48	0%	100%	N.A. ¹
Lutron	Contour	CT-103P	1	80	0%	97%	N.A. ¹
Lutron	Contour	CT-600P	1	48	0%	98%	N.A. ¹
Lutron	Rotary	D-600P	1	48	0%	94%	N.A. ¹
Lutron	Diva	DV-600P	1	48	0%	97%	N.A. ¹
Lutron	Glyder	GL-600P	1	48	0%	98%	N.A. ¹
Lutron	Lumia	LG-600PH	1	48	0%	98%	N.A. ¹
Lutron	Maestro	MA-600	1	48	0%	99%	N.A. ¹
Lutron	Nova	N-600	1	48	0%	100%	N.A. ¹
Lutron	Skylark	S-600P	1	48	0%	98%	N.A. ¹
Lutron	Centurion	C-600P	1	48	0%	100%	N.A. ¹
Lutron	Ariadni	AYLV-600P	1	36	1%	100%	<1s
Lutron	Glyder	GLV-600	1	36	0%	100%	N.A. ¹
Lutron	Diva	DVLV-600P	1	36	0%	97%	N.A. ¹
Lutron	Lumina	LG-103P	1	80	0%	98%	N.A. ¹
Lutron	Skylark	SLV-600P	1	36	0%	99%	N.A. ¹
EWD	Universal	DUL06P-C7	1	24	1%	95%	<1s
Lutron	Nova	NTLV-600	1	24	0%	100%	N.A. ¹
Lutron	Nova	NT-600	1	36	0%	100%	N.A. ¹

1. Dim to off.

HL3 Remodel 300 mA Triac Dimming

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	Standard 150 W LED+	AYCL-153P	1	11	9%	97%	<1S
Lutron	Standard 150 W LED+	CTCL-153P	1	11	9%	97%	<1S
Lutron	Standard 150 W LED+	DVCL-153P	1	11	9%	97%	<1S
Lutron	Standard 150 W LED+	SCL-153P	1	11	9%	97%	<1S
Lutron	Standard 150 W LED+	TGCL-153P	1	11	9%	97%	<1S
Lutron	Maestro	MACL-153M	1	11	10%	91%	<1S
Lutron	Sunnata	STCL-153P	1	11	10%	91%	<1S
Lutron	RadioRA 2	RRD-10ND	1	11	8%	91%	<1S
Lutron	HomeWorks QS	HQRD-10ND	1	11	8%	91%	<1S
Lutron	RadioRA 2	RRD-6NA	1	11	10%	98%	<1S
Lutron	HomeWorks QS	HQRD-6NA	1	11	10%	98%	<1S
Lutron	HomeWorks	HxD-6ND	1	7	8%	91%	<1S
Lutron	Stanza	SZ-6ND	1	4	8%	91%	<1S
Lutron	Power Modules	PHPM-PA with Grafik Eye QS Main Unit	1	44	9%	100%	<1S
Lutron	Power Modules	PHPM-WBX with 3-wire fluorescent control	1	44	9%	100%	<1S
Lutron	Panel Module	HW/LP-RPM-4U-120 (Forward Phase)	1	20	15%	91%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Reverse Phase)	1	44	9%	100%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Forward Phase)	1	14	15%	91%	<1S
Lutron	Grafik QS/Wallbox Power Module	"Grafik Eye QS Main Unit Family/ LQRJ-WPM-6P"	1	20	15%	91%	<1S
Lutron	Grafik T	Keypad RRT-GHxB/HQRT-GHxB	1	11	8%	91%	<1S
Lutron	Panel Module	GP (Harrier) Card	1	20	15%	91%	<1S
Lutron	Maestro Sensor	MSCL-OP153M(T2)	1	11	10%	91%	<1S
Lutron	Maestro Sensor	MSCL-VP153M(T2)	1	11	10%	91%	<1S
Lutron	Grafik Eye 3000/HomeWorks	Grafik Eye 3000 Family/HWI-WPM-6D-120	1	20	15%	91%	<1S
Lutron	RadioRA 2	RRD-6CL (R3)	1	11	8%	91%	<1S
Lutron	HomeWorks QS	HQRD-6CL (H2)	1	11	8%	91%	<1S
Lutron	HomeWorks QS	HQRA-6CL (H2)	1	11	8%	91%	<1S
Lutron	RadioRA 2	RRD-HN6BRL (with neutral)	1	7	8%	91%	<1S
Lutron	HomeWorks QS	HQRD-HN6BRL (with neutral)	1	7	8%	91%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (without neutral)	1	19	10%	98%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (without neutral)	1	19	10%	98%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (with neutral)	1	19	10%	98%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (with neutral)	1	19	10%	98%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (with neutral)	1	19	10%	98%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Forward Phase)	1	2	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Reverse Phase)	1	6	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Forward Phase)	1	3	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Forward Phase)	1	3	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Forward Phase)	1	3	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Forward Phase)	1	3	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Reverse Phase)	1	5	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Reverse Phase)	1	5	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Reverse Phase)	1	5	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Reverse Phase)	1	5	10%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Reverse Phase)	1	31	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Reverse Phase)	1	31	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Reverse Phase)	1	31	10%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Reverse Phase)	1	31	10%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Forward Phase)	1	7	9%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Forward Phase)	1	7	9%	100%	<1S

HL3 Remodel 300 mA Triac Dimming

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Forward Phase)	1	10	9%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Forward Phase)	1	10	9%	100%	<1S
Lutron	Grafik T	GT-5NEM	1	19	10%	98%	<1S
Lutron	Grafik T	GTJ-5NEM	1	19	10%	98%	<1S
Lutron	HomeWorks	HXD-5NE	1	7	10%	98%	<1S
Lutron	Skylark Contour Slide to Off	CTCL-150/LECL-150	1	11	9%	97%	<1S
Lutron	Dalia	RCL-153PNL	1	11	9%	97%	<1S
Lutron	Caseta Wireless Phase Selectable	PD-5NE	1	19	10%	98%	<1S
Lutron	Vive	MRF2S-6ELV	1	11	10%	98%	<1S
Lutron	Vive	MRF2S-6CL	1	11	8%	91%	<1S
Lutron	Maestro	MACL-LFQ	1	5	10%	91%	<1S
Lutron	Caseta Wireless	PD-6WCL (SD12)	1	11	8%	91%	<1S

HL3 Remodel 300 mA Triac Dimming

For Reference Only

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Leviton	SureSlide	6674	1	9	11%	97%	<1s
Leviton	SureSlide	6631-2	1	38	1%	100%	<1s
Leviton	Illumatech	IPL06	1	9	1%	97%	<1s
Leviton	Vizia	VPI06	1	38	1%	97%	<1s
Leviton	Decora	6161	1	32	1%	97%	<1s
Leviton	SureSlide	6633-P	1	38	0%	99%	N.A. ¹
Eaton	RF Smart	RF9540-N	1	19	1%	98%	<1s
Lutron	Toggler	TGCL-153P	1	9	6%	91%	<1s
EWD	Universal	TUL06P-C2	1	19	1%	93%	<1s ²
EWD	Universal	SUL06P	1	19	1%	91%	<1s ²
Lutron	Skylark	SCL-153P-WH	1	9	1%	93%	<1s ²
Lutron	Diva	DVCL-153P	1	9	1%	93%	<1s
Lutron	Maestro	MACL-153-M	1	9	1%	87%	<1s
Leviton	Vizia	VPE06	1	38	1%	100%	<1s
Leviton	Vizia	VZE04	1	25	1%	100%	<1s
Lutron	Maestro	MAELV600	1	38	1%	100%	<1s
Lutron	Diva	DVELV303P	1	19	1%	95%	<1s
Lutron	Skylark	SELV300P	1	19	1%	97%	<1s
EWD	Smart	AAL06	1	19	1%	96%	<1s
Lightolier	Sunrise	ZP260QEW	1	16	1%	94%	<1s
Eaton	Aspire	9530AW	1	38	1%	100%	<1s
Eaton	React	RI061	1	38	0%	100%	N.A. ¹
Eaton	Toggle	DAL06P	1	19	1%	100%	<1s
Eaton	Skye	SAL06P	1	19	1%	100%	<1s
Eaton	Skye	SLC03P	1	19	1%	100%	<1s
Eaton	Devine	DLC03P	1	19	1%	100%	<1s
Lutron	LCP128	LP-RPM-4U-120	1	35	0%	100%	N.A. ¹
Lutron	LCP128	LP-RPM-4A-120	1	22	0%	99%	N.A. ¹
Ecospec	LDCM	LDCM-PL-120-277-010V-GR	1	28	0%	100%	N.A. ¹
Lutron	Ariadni	AY-600P	1	38	1%	98%	<1s
Lutron	Contour	CT-600P	1	38	0%	96%	N.A. ¹
Lutron	Rotary	D-600P	1	38	0%	92%	N.A. ¹
Lutron	Glyder	GL-600P	1	38	0%	96%	N.A. ^{1, 2}
Lutron	Lumia	LG-600PH	1	38	0%	96%	N.A. ^{1, 2}
Lutron	Maestro	MA-600	1	38	0%	94%	N.A. ¹
Lutron	Nova	N-600	1	38	0%	100%	N.A. ¹
Lutron	Centurion	C-600P	1	38	1%	100%	<1s
Lutron	Ariadni	AYLV-600P	1	28	1%	100%	<1s
Lutron	Glyder	GLV-600	1	28	0%	100%	N.A. ¹
Lutron	Diva	DVLV-600P	1	28	1%	95%	<1s
Lutron	Lumina	LG-103P	1	64	1%	96%	<1s
Lutron	Skylark	SLV-600P	1	28	0%	97%	N.A. ^{1, 2}
EWD	Universal	DUL06P-C7	1	19	1%	93%	<1s ²
Lutron	Nova	NTLV-600	1	19	1%	100%	<1s ²
Lutron	Nova	NT-600	1	28	0%	100%	N.A. ^{1, 2}

1. Dim to off.

2. Shimmer at lowest dim setting

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	RadioRA 2	RRD-6NA	1	10	10%	100%	<1S
Lutron	HomeWorks QS	HQRD-6NA	1	10	10%	100%	<1S
Lutron	HomeWorks	HxD-6ND	1	5	10%	98%	<1S
Lutron	Stanza	SZ-6ND	1	3	10%	98%	<1S
Lutron	Power Modules	PHPM-PA with Grafik Eye QS Main Unit	1	28	10%	100%	<1S
Lutron	Power Modules	PHPM-WBX with 3-wire fluorescent control	1	28	10%	100%	<1S
Lutron	Panel Module	HW/LP-RPM-4U-120 (Forward Phase)	1	14	10%	92%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Reverse Phase)	1	28	10%	100%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Forward Phase)	1	13	10%	100%	<1S
Lutron	Grafik QS/Wallbox Power Module	"Grafik Eye QS Main Unit Family/ LQRJ-WPM-6P"	1	14	10%	92%	<1S
Lutron	Grafik T	Keypad RRT-GHxB/HQRT-GHxB	1	10	10%	98%	<1S
Lutron	Panel Module	GP (Harrier) Card	1	14	10%	92%	<1S
Lutron	Grafik Eye 3000/HomeWorks	Grafik Eye 3000 Family/HWI-WPM-6D-120	1	14	10%	92%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (without neutral)	1	16	10%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (without neutral)	1	16	10%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (without neutral)	1	16	10%	100%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (with neutral)	1	16	10%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (with neutral)	1	16	10%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (with neutral)	1	16	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Forward Phase)	1	2	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Reverse Phase)	1	5	14%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Forward Phase)	1	1	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Forward Phase)	1	1	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Forward Phase)	1	1	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Forward Phase)	1	1	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Reverse Phase)	1	4	14%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Reverse Phase)	1	4	14%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Reverse Phase)	1	4	14%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Reverse Phase)	1	4	14%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Reverse Phase)	1	20	14%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Reverse Phase)	1	20	14%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Reverse Phase)	1	20	14%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Reverse Phase)	1	20	14%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Forward Phase)	1	6	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Forward Phase)	1	6	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Forward Phase)	1	9	10%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Forward Phase)	1	9	10%	100%	<1S
Lutron	Grafik T	GT-5NEM	1	16	10%	100%	<1S
Lutron	Grafik T	GTJ-5NEM	1	16	10%	100%	<1S
Lutron	HomeWorks	HXD-5NE	1	10	10%	100%	<1S
Lutron	Caseta Wireless Phase Selectable	PD-5NE	1	16	10%	100%	<1S
Lutron	Vive	MRF2S-6ELV	1	10	10%	100%	<1S

HL3 Remodel 350 mA Triac Dimming

For Reference Only

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Leviton	Decora	6673	1	32	6%	93%	<1s
Leviton	SureSlide	6674	1	8	12%	100%	<1s
Leviton	SureSlide	6631-2	1	32	0%	100%	N.A. ¹
Leviton	Illuminatech	IPL06	1	8	1%	99%	<1s
Leviton	Vizia	VPI06	1	32	1%	100%	<1s
Leviton	Decora	6161	1	26	5%	99%	<1s
Leviton	SureSlide	6633-P	1	32	0%	100%	N.A. ¹
Lutron	Toggler	TG-600P	1	32	1%	93%	<1s
Eaton	RF Smart	RF9540-N	1	16	1%	98%	<1s
Lutron	Toggler	TGCL-153P	1	8	1%	94%	<1s
Lutron	Lumea	LG600P	1	32	0%	98%	N.A. ¹
EWD	Universal	TUL06P-C2	1	16	1%	96%	<1s
EWD	Universal	SUL06P	1	16	1%	95%	<1s
Lutron	Skylark	SCL-153P-WH	1	8	1%	96%	<1s
Lutron	Diva	DV603P	1	32	1%	97%	<1s
Lutron	Diva	DVCL-153P	1	8	1%	95%	<1s
Lutron	Maestro	MACL-153-M	1	8	1%	89%	<1s
Leviton	Vizia	VPE06	1	32	1%	100%	<1s
Leviton	Legrand	H703PTU	1	16	10%	100%	<1s
Leviton	Vizia	VZE04	1	21	3%	100%	<1s
Lutron	Maestro	MAELV600	1	32	3%	100%	<1s
Lutron	Diva	DVELV303P	1	16	1%	98%	<1s
Lutron	Skylark	SELV300P	1	16	1%	99%	<1s
EWD	Smart	AAL06	1	16	1%	97%	<1s
Lightolier	Sunrise	ZP260QEW	1	13	1%	98%	<1s
Eaton	Aspire	9530AW	1	32	1%	100%	<1s
Eaton	Devine	DE06P	1	32	1%	85%	<1s
Eaton	React	RI061	1	32	0%	100%	N.A. ¹
Eaton	Devine	TAL06P	1	16	1%	99%	<1s
Eaton	Toggle	DAL06P	1	16	1%	99%	<1s
Eaton	Skye	SAL06P	1	16	1%	99%	<1s
Eaton	Skye	SLC03P	1	16	1%	99%	<1s
Eaton	Devine	DLC03P	1	16	1%	99%	<1s
Eaton	Toggle	TI061	1	32	1%	82%	<1s
Lutron	LCP128	LP-RPM-4U-120	1	35	0%	100%	N.A. ¹
Lutron	LCP128	LP-RPM-4A-120	1	22	0%	100%	N.A. ¹
Ecospec	LDCM	LDCM-PL-120-277-010V-GR	1	24	0%	100%	N.A. ¹
Lutron	Ariadni	AY-600P	1	32	1%	100%	<1s
Lutron	Contour	CT-103P	1	53	1%	98%	<1s
Lutron	Contour	CT-600P	1	32	0%	98%	N.A. ¹
Lutron	Rotary	D-600P	1	32	0%	94%	N.A. ¹
Lutron	Diva	DV-600P	1	32	0%	97%	N.A. ¹
Lutron	Glyder	GL-600P	1	32	0%	98%	N.A. ¹
Lutron	Lumia	LG-600PH	1	32	0%	97%	N.A. ¹
Lutron	Nova	N-600	1	32	0%	100%	N.A. ¹
Lutron	Skylark	S-600P	1	32	0%	97%	N.A. ¹
Lutron	Centurion	C-600P	1	32	0%	100%	N.A. ¹
Lutron	Ariadni	AYLV-600P	1	24	4%	100%	<1s
Lutron	Glyder	GLV-600	1	24	1%	100%	<1s
Lutron	Diva	DVLV-600P	1	24	1%	97%	<1s
Lutron	Lumina	LG-103P	1	53	3%	98%	<1s
Lutron	Skylark	SLV-600P	1	24	1%	99%	<1s
EWD	Universal	DUL06P-C7	1	16	1%	95%	<1s
Lutron	Nova	NTLV-600	1	16	1%	100%	<1s
Lutron	Nova	NT-600	1	24	1%	100%	<1s

1. Dim to off.

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	Diva	C-L Gen 1.0	1	7	13%	93%	<1S
Lutron	Skylark Contour	C-L Gen 1.0	1	7	13%	93%	<1S
Lutron	Ariadni	C-L Gen 1.0	1	7	13%	93%	<1S
Lutron	Toggler	C-L Gen 1.0	1	7	13%	93%	<1S
Lutron	Standard 150 W LED+	AYCL-153P	1	7	10%	97%	<1S
Lutron	Standard 150 W LED+	CTCL-153P	1	7	10%	97%	<1S
Lutron	Standard 150 W LED+	DVCL-153P	1	7	10%	97%	<1S
Lutron	Standard 150 W LED+	SCL-153P	1	7	10%	97%	<1S
Lutron	Standard 150 W LED+	TGCL-153P	1	7	10%	97%	<1S
Lutron	Maestro	MACL-153M	1	7	15%	93%	<1S
Lutron	Sunnata	STCL-153P	1	7	15%	93%	<1S
Lutron	RadioRA 2	RRD-10ND	1	7	10%	92%	<1S
Lutron	HomeWorks QS	HQRD-10ND	1	7	10%	92%	<1S
Lutron	RadioRA 2	RRD-6NA	1	7	9%	100%	<1S
Lutron	HomeWorks QS	HQRD-6NA	1	7	9%	100%	<1S
Lutron	HomeWorks	HxD-6ND	1	4	10%	92%	<1S
Lutron	Stanza	SZ-6ND	1	2	10%	92%	<1S
Lutron	Power Modules	PHPM-PA with Grafik Eye QS Main Unit	1	25	10%	99%	<1S
Lutron	Power Modules	PHPM-WBX with 3-wire fluorescent control	1	25	10%	99%	<1S
Lutron	Panel Module	HW/LP-RPM-4U-120 (Forward Phase)	1	13	10%	96%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Reverse Phase)	1	25	10%	99%	<1S
Lutron	Panel Module	HW/LP-RPM-4A-120 (Forward Phase)	1	10	10%	96%	<1S
Lutron	Grafik QS/Wallbox Power Module	"Grafik Eye QS Main Unit Family/ LQRJ-WPM-6P"	1	13	10%	96%	<1S
Lutron	Grafik T	Keypad RRT-GHxB/HQRT-GHxB	1	7	10%	92%	<1S
Lutron	Panel Module	GP (Harrier) Card	1	13	10%	96%	<1S
Lutron	Maestro Sensor	MSCL-OP153M(T2)	1	7	15%	93%	<1S
Lutron	Maestro Sensor	MSCL-VP153M(T2)	1	7	15%	93%	<1S
Lutron	Grafik Eye 3000/HomeWorks	Grafik Eye 3000 Family/HWI-WPM-6D-120	1	13	10%	96%	<1S
Lutron	RadioRA 2	RRD-6CL (R3)	1	7	10%	92%	<1S
Lutron	HomeWorks QS	HQRD-6CL (H2)	1	7	10%	92%	<1S
Lutron	HomeWorks QS	HQRA-6CL (H2)	1	7	10%	92%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (without neutral)	1	12	9%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (without neutral)	1	12	9%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (without neutral)	1	12	9%	100%	<1S
Lutron	RadioRA 2	RRD-PRO (RP) (with neutral)	1	12	9%	100%	<1S
Lutron	Maestro C-L Pro	MA-PRO (RP) (with neutral)	1	12	9%	100%	<1S
Lutron	HomeWork QS	HQRx-PRO (RP) (with neutral)	1	12	9%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Forward Phase)	1	1	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-120-D (Reverse Phase)	1	4	12%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Forward Phase)	1	2	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Forward Phase)	1	2	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Forward Phase)	1	2	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Forward Phase)	1	2	10%	100%	<1S
Lutron	HomeWorks QS/myRoom	LQSE-4A1-D (Reverse Phase)	1	4	12%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-4A1-D (Reverse Phase)	1	4	12%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-3A1 (Reverse Phase)	1	4	12%	100%	<1S
Lutron	HomeWorks QS/myRoom	MQSE-2A1-D (Reverse Phase)	1	4	12%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Reverse Phase)	1	18	12%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Reverse Phase)	1	18	12%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Reverse Phase)	1	18	12%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Reverse Phase)	1	18	12%	100%	<1S

HL3 Remodel 475 mA Triac Dimming

Compatible Dimmers

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Lutron	HomeWorks	LQSE-4A5-120-D (Zones 2-4 Forward Phase)	1	5	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zones 2-4 Forward Phase)	1	5	10%	100%	<1S
Lutron	Energi Savr Node (Phase adaptive)	QSN-4A5-S (Zone 1 Forward Phase)	1	7	10%	100%	<1S
Lutron	HomeWorks	LQSE-4A5-120-D (Zone 1 Forward Phase)	1	7	10%	100%	<1S
Lutron	Grafik T	GT-5NEM	1	12	9%	100%	<1S
Lutron	Grafik T	GTJ-5NEM	1	12	9%	100%	<1S
Lutron	HomeWorks	HXD-5NE	1	7	9%	100%	<1S
Lutron	Diva/Skylark Contour	DVRP-253P	1	12	10%	100%	<1S
Lutron	Diva/Skylark Contour	CTRP-253P	1	12	10%	100%	<1S
Lutron	Nova T	NTRP-250	1	12	10%	100%	<1S
Lutron	Skylark Contour Slide to Off	CTCL-150/LECL-150	1	7	10%	97%	<1S
Lutron	Dalia	RCL-153PNL	1	7	10%	97%	<1S
Lutron	Caseta Wireless Phase Selectable	PD-5NE	1	12	9%	100%	<1S
Lutron	Vive	MRF2S-6ELV	1	7	9%	100%	<1S
Lutron	Vive	MRF2S-6CL	1	7	10%	92%	<1S
Lutron	Maestro	MACL-LFQ	1	3	15%	93%	<1S
Lutron	Caseta Wireless	PD-6WCL (SD12)	1	7	10%	92%	<1S

For Reference Only

Dimmer Make	Dimmer Series	Dimmer Model #	Minimum Luminaires (per circuit)	Maximum Recommended Luminaires (per circuit)	Min Dimming percentage (%)	Max Dimming percentage (%)	Low End Start Time
Leviton	Decora	6673	1	23	1%	94%	<1s
Leviton	SureSlide	6631-2	1	23	1%	100%	<1s
Leviton	Illumatech	IPL06	1	5	1%	100%	<1s
Leviton	Vizia	VPI06	1	23	1%	100%	<1s
Leviton	Decora	6161	1	19	6%	99%	<1s
Leviton	SureSlide	6633-P	1	23	0%	100%	N.A. ¹
Lutron	Toggler	TG-600P	1	23	1%	99%	<1s
Eaton	RF Smart	RF9540-N	1	11	1%	99%	<1s
Lutron	Toggler	TGCL-153P	1	5	1%	92%	<1s
Lutron	Lumea	LG600P	1	23	0%	97%	N.A. ¹
EWD	Universal	TUL06P-C2	1	11	1%	95%	<1s
EWD	Universal	SUL06P	1	11	1%	94%	<1s
Lutron	Skylark	SCL-153P-WH	1	5	1%	94%	<1s
Lutron	Diva	DV603P	1	23	0%	97%	N.A. ¹
Lutron	Diva	DVCL-153P	1	5	1%	94%	<1s
Lutron	Maestro	MACL-153-M	1	5	1%	88%	<1s
Leviton	Vizia	VPE06	1	23	1%	99%	<1s
Leviton	Legrand	H703PTU	1	11	6%	99%	<1s
Leviton	Vizia	VZE04	1	15	1%	98%	<1s
Leviton	Acenti	ATX10	1	39	0%	98%	N.A. ¹
Lutron	Maestro	MAELV600	1	23	2%	97%	<1s
Lutron	Diva	DVELV303P	1	11	1%	91%	<1s
Lutron	Skylark	SELV300P	1	11	1%	94%	<1s
EWD	Smart	AAL06	1	11	1%	95%	<1s
Lightolier	Sunrise	ZP260QEW	1	10	1%	93%	<1s
Eaton	Aspire	9530AW	1	23	1%	99%	<1s
Eaton	Devine	DE06P	1	23	1%	85%	<1s
Eaton	React	RI061	1	23	0%	99%	N.A. ¹
Eaton	Devine	TAL06P	1	11	1%	99%	<1s
Eaton	Toggle	DAL06P	1	11	1%	99%	<1s
Eaton	Skye	SAL06P	1	11	1%	99%	<1s
Eaton	Skye	SLC03P	1	11	1%	99%	<1s
Eaton	Devine	DLC03P	1	11	1%	99%	<1s
Eaton	Toggle	TI061	1	23	1%	83%	<1s
Lutron	LCP128	LP-RPM-4U-120	1	35	0%	99%	N.A. ¹
Lutron	LCP128	LP-RPM-4A-120	1	22	0%	99%	N.A. ¹
Ecospec	LDCM	LDCM-PL-120-277-010V-GR	1	17	1%	100%	<1s
Lutron	Ariadni	AY-600P	1	23	3%	100%	<1s
Lutron	Contour	CT-103P	1	39	1%	97%	<1s
Lutron	Contour	CT-600P	1	23	1%	97%	<1s
Lutron	Rotary	D-600P	1	23	0%	94%	N.A. ¹
Lutron	Diva	DV-600P	1	23	0%	97%	N.A. ¹
Lutron	Glyder	GL-600P	1	23	1%	97%	<1s
Lutron	Lumia	LG-600PH	1	23	0%	97%	N.A. ¹
Lutron	Nova	N-600	1	23	0%	98%	N.A. ¹
Lutron	Skylark	S-600P	1	23	0%	97%	N.A. ¹
Lutron	Centurion	C-600P	1	23	0%	100%	N.A. ¹
Lutron	Ariadni	AYLV-600P	1	17	7%	100%	>1s
Lutron	Glyder	GLV-600	1	17	1%	100%	<1s
Lutron	Diva	DVLV-600P	1	17	1%	96%	<1s
Lutron	Lumina	LG-103P	1	39	2%	97%	<1s
Lutron	Skylark	SLV-600P	1	17	1%	99%	<1s
EWD	Universal	DUL06P-C7	1	11	1%	98%	<1s
Lutron	Nova	NTLV-600	1	11	1%	99%	<1s
Lutron	Nova	NT-600	1	17	1%	99%	<1s

1. Dim to off.

Dimmer Notes:

- 1) Start time is measured at the lowest dimmer setting.
- 2) Some LED dimmers have a "rapid start" design used to provide a momentary power boost to LED and CFL lamps during start-up. When a LED luminaire is on a dimmer with "rapid start" the boost may cause a momentary flash of the LED lighting. This "flash" is generated by the dimmer, and may be more noticeable when the dimmer is at a low setting. A solution is available with Cooper Lighting Solutions dimmers which provide adjustment capability of the "rapid start": Devine (DAL06P), Accell (AAL06P), and Trace (TAL06P). Refer to product specifications online at www.cooperlighting.com for more details.

Dimming Guide Disclaimer:

- 1) Leviton® is a registered trademark of Leviton Manufacturing Co. Inc.; Lutron® is a registered trademark of Lutron Electronics Co. Inc.; Lightolier® is a registered trademark of Philips Lighting; Hubbell® is a registered trademark of Hubbell Incorporated; Legrand® and Pass & Seymour® are registered trademarks of Legrand®. These companies and their tradenames, trademarks or brands, where noted, are associated with their respective company and are not associated with Cooper Lighting Solutions.
- 2) Testing conducted by Cooper Lighting Solutions is not a substitute for and does not imply certification by an independent laboratory or any other standards certification. Refer to the manufacturer specifications for more detailed information on product certifications and standards.
- 3) This is a representative list of typical dimmers as tested by Cooper Lighting Solutions business for performance with the designated LED luminaires only. Test data contained in this literature is based upon dimmers obtained in the marketplace. Information about these other manufacturers products is obtained from packaging and published information made available by the manufacturer and is deemed to be reliable, but has not been verified. Dimmer performance and perceived limitations of the dimmers are based on factors outside of Cooper Lighting Solutions' control. The specifications of these dimming controls and their conditions of use may change without notice to Cooper Lighting Solutions or any other user. Cooper Lighting Solutions makes no specific recommendation on product selection and there are no warranties of performance or compatibility implied. Installer must ensure proper local and national electrical codes are followed; and that the dimmer application and condition of use is per dimmer manufacturer instructions and guidelines.