

DESCRIPTION

The EPIC Collection delivers custom luminaire flexibility with high quality, yet availability expectations of standard specification grade product. The EPIC Collection can be dressed to suit any application. Recognizing evolving environmental and legislative trends, the EPIC Collection delivers world class LED optical and performance solutions to the decorative luminaire marketplace.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Construction

TOP: Cast aluminum top housing attaches to cast aluminum mounting arm hub with four stainless steel fasteners. One-piece silicone gasket between mounting hub and top casting seals out moisture and contaminants. (See the mounting accessories section for a full selection of mounting arms. (Only these arms are compatible with the Epic luminaire). **MIDSECTION:** Continuous silicone gaskets seal lens to top casting and shade. The mid section features cast aluminum construction and stainless steel assembly. **SHADES:** Heavy gauge precision spun aluminum shades offer superior surface finish and consistency in form. **DOORFRAME:** Die-cast aluminum 1/8" thick door and doorframe seal to underside of shade with a thick wall continuous silicone gasket. Mounting hub ships attached to mounting arm.

Optics

Choice of twelve patented, high-efficiency AccuLED Optic™ technology manufactured from

injection-molded acrylic. Optics are precisely designed to shape the optics, maximizing efficiency and application spacing. AccuLED Optic technology, creates consistent distributions with the scalability to meet customized application requirements. Offered Standard in 4000K (+/- 275K) CCT and nominal 70 CRI. Optional 3000K CCT and 5000K CC. For the ultimate level of spill light control, an optional house-side shield accessory can be field or factory installed. The house-side shield is designed to seamlessly integrate with the SL2, SL3 or SL4 optics.

Electrical

LED drivers mount to die-cast aluminum back housing for optimal heat sinking, operation efficacy, and prolonged life. Standard drivers feature electronic universal voltage (120-277V 50/60Hz), 347V 60Hz or 480V 60Hz operation, greater than 0.9 power factor, less than 20% harmonic distortion, and is suitable for operation in -40°C to 40°C ambient environments. All fixtures are shipped standard

with 10kV/10kA common – and differential – mode surge protection. LightBARs feature and IP66 enclosure rating and maintain greater than 95% lumen maintenance at 60,000 hours per IESNA TM-21. Occupancy sensor and dimming options available.

Finish

Housing is finished in five-stage super TGIC polyester powder coat paint, 2.5 mil nominal thickness for superior protection against fade and wear. LightBAR™ cover plates are standard white and may be specified to match finish of luminaire housing. Standard colors include black, bronze, grey, white, dark platinum and graphite metallic. RAL and custom color matches available. Consult Outdoor Architectural Colors brochure for a complete selection.

Warranty

Five-year warranty.



CEM/MEM EPIC MEDIUM LED

1 - 4 LightBARs
Solid State LED

DECORATIVE AREA LUMINAIRE



CERTIFICATION DATA

UL/cUL Listed
IP66 LightBARs
LM79 / LM80 Compliant
2G Vibration Tested
ISO 9001

ENERGY DATA

Electronic LED Driver
>0.9 Power Factor
<20% Total Harmonic Distortion
120-277V 50/60Hz, 347V/60Hz,
480V/60Hz
-40°C Minimum Temperature
40°C Ambient Temperature Rating

EPA


Effective Projected Area: (Sq. Ft.) 0.94

SHIPPING DATA


Approximate Net Weight:
45 lbs. [20 kgs.]

DIMENSIONS

CEM Classical




MEM Classical



See configurations for more detailed information.

CONFIGURATIONS



POWER AND LUMENS BY BAR COUNT (21 LED LIGHTBARS)

Number of LightBARs		E01	E02	E03	E04
Drive Current		350mA Drive Current			
Power (Watts)		25W	52W	75W	97W
Current @ 120V (A)		0.22	0.44	0.63	0.82
Current @ 277V (A)		0.10	0.20	0.28	0.36
Power (Watts)		31W	58W	82W	99W
Current @ 347V (A)		0.11	0.19	0.28	0.29
Current @ 480V (A)		0.09	0.15	0.20	0.21
T2	Lumens	2,948	5,896	8,844	11,792
	BUG Rating	B1-U0-G1	B2-U0-G2	B3-U0-G3	B3-U0-G3
T3	Lumens	2,936	5,873	8,809	11,745
	BUG Rating	B1-U0-G1	B2-U0-G2	B3-U0-G3	B3-U0-G3
T4	Lumens	2,876	5,752	8,627	11,503
	BUG Rating	B1-U0-G1	B1-U0-G2	B1-U0-G2	B2-U0-G3
5MQ	Lumens	3,054	6,108	9,161	12,215
	BUG Rating	B2-U0-G1	B3-U0-G1	B3-U0-G2	B4-U0-G2
5WQ	Lumens	2,987	5,975	8,962	11,949
	BUG Rating	B2-U0-G1	B3-U0-G1	B3-U0-G2	B4-U0-G2
5XQ	Lumens	2,982	5,963	8,945	11,926
	BUG Rating	B2-U0-G1	B3-U0-G2	B3-U0-G3	B4-U0-G3
SL2	Lumens	2,878	5,756	8,634	11,512
	BUG Rating	B1-U0-G1	B1-U0-G2	B2-U0-G2	B2-U0-G2
SL3	Lumens	2,894	5,788	8,682	11,576
	BUG Rating	B1-U0-G1	B1-U0-G2	B2-U0-G2	B2-U0-G2
SL4	Lumens	2,823	5,647	8,470	11,294
	BUG Rating	B1-U0-G1	B1-U0-G2	B2-U0-G2	B2-U0-G2
RW	Lumens	2,957	5,915	8,872	11,829
	BUG Rating	B2-U0-G2	B3-U0-G3	B3-U0-G3	B3-U0-G3
SLL/SLR	Lumens	2,616	5,231	7,847	10,462
	BUG Rating	B1-U0-G2	B1-U0-G2	B1-U0-G3	B2-U0-G3


POWER AND LUMENS BY BAR COUNT (7 LED LIGHTBARS)

Number of LightBARs		F01	F02	F03	F04
Drive Current		1A Drive Current			
Power (Watts)		26W	55W	78W	102W
Current @ 120V (A)		0.22	0.46	0.66	0.86
Current @ 277V (A)		0.10	0.21	0.29	0.37
Power (Watts)		32W	60W	85W	105W
Current @ 347V (A)		0.11	0.19	0.28	0.30
Current @ 480V (A)		0.09	0.15	0.21	0.22
T2	Lumens	2,434	4,867	7,301	9,735
	BUG Rating	B1-U0-G1	B2-U0-G2	B2-U0-G2	B3-U0-G3
T3	Lumens	2,424	4,848	7,272	9,696
	BUG Rating	B1-U0-G1	B2-U0-G2	B2-U0-G2	B3-U0-G3
T4	Lumens	2,374	4,748	7,122	9,496
	BUG Rating	B1-U0-G1	B1-U0-G2	B1-U0-G2	B2-U0-G2
5MQ	Lumens	2,521	5,042	7,563	10,084
	BUG Rating	B2-U0-G1	B3-U0-G1	B3-U0-G1	B3-U0-G2
5WQ	Lumens	2,466	4,932	7,398	9,864
	BUG Rating	B2-U0-G1	B3-U0-G1	B3-U0-G2	B4-U0-G2
5XQ	Lumens	2,461	4,923	7,384	9,845
	BUG Rating	B2-U0-G1	B3-U0-G2	B3-U0-G2	B4-U0-G3
SL2	Lumens	2,376	4,752	7,127	9,503
	BUG Rating	B1-U0-G1	B1-U0-G1	B2-U0-G2	B2-U0-G2
SL3	Lumens	2,389	4,778	7,167	9,556
	BUG Rating	B1-U0-G1	B1-U0-G1	B1-U0-G2	B2-U0-G2
SL4	Lumens	2,331	4,662	6,993	9,323
	BUG Rating	B1-U0-G1	B1-U0-G2	B1-U0-G2	B2-U0-G2
RW	Lumens	2,441	4,883	7,324	9,765
	BUG Rating	B1-U0-G1	B2-U0-G2	B3-U0-G3	B3-U0-G3
SLL/SLR	Lumens	2,159	4,318	6,478	8,637
	BUG Rating	B1-U0-G1	B1-U0-G2	B1-U0-G3	B1-U0-G3

LUMEN MAINTENANCE

Ambient Temperature	25,000 Hours*	50,000 Hours*	60,000 Hours*	100,000 Hours	Theoretical L70 (Hours)
25°C	> 99%	> 97%	> 96%	> 93%	> 450,000
40°C	> 98%	> 97%	> 96%	> 92%	> 425,000
50°C	> 97%	> 96%	> 95%	> 91%	> 400,000

* Per IESNA TM-21 data.



LUMEN MULTIPLIER

Ambient Temperature	Lumen Multiplier
10°C	1.02
15°C	1.01
25°C	1.00
40°C	0.99
50°C	0.96

ORDERING INFORMATION

Sample Number: CEM-E04-LED-E-U-T2-4-FL-BK


Product Family ^{1,2}	Number of LightBARs ^{3,4}	Lamp Type	Driver ⁵	Voltage	Distribution	Mid Section Type	Shade Type	Color ⁷
CEM=Classical Epic Medium MEM=Modern Epic Medium	E01=(1) 21 LED LightBAR E02=(2) 21 LED LightBARs E03=(3) 21 LED LightBARs E04=(4) 21 LED LightBARs F01=(1) 7 LED LightBAR F02=(2) 7 LED LightBARs F03=(3) 7 LED LightBARs F04=(4) 7 LED LightBARs	LED=Solid State Light Emitting Diodes	E=Non-Dimming D=Dimming (0-10V)	U=Universal (120-277V) 8=480V ⁶ 9=347V	T2=Type II T3=Type III T4=Type IV SL2=Type II w/Spill Control SL3=Type III w/Spill Control SL4=Type IV w/Spill Control 5MQ=Type V Square Medium 5WQ=Type V Square Wide 5XQ=Type V Square Extra Wide RW=Rectangular Wide SLL=90° Spill Light Eliminator Left SLR=90° Spill Light Eliminator Right	X=Solid 4=Solid Rings	SN=Straight Narrow SW=Straight Wide BL=Bell FL=Flute	AP=Grey BZ=Bronze BK=Black DP=Dark Platinum GM=Graphite Metallic WH=White
Options (Add as Suffix)		Accessories (Order Separately) ¹⁴						
2L=Two Circuits ⁸ 7030=70 CRI / 3000K CCT ⁹ 7050=70 CRI / 5000K CCT ⁹ 7060=70 CRI / 5700K CCT ⁹ 8030=80 CRI / 3000K CCT ⁹ LCF=LightBAR Cover Plate Matches Housing Finish MS-LXX=Motion Sensor for ON/OFF Operation ¹⁰ MS/X-LXX=Motion Sensor for Bi-Level Switching ¹¹ PM48=Pendant Mount 48" Length or Specify Pendant Length Inches (XX) ¹² HSS=Factory Installed House Side Shield ¹³		OA/RA1016 =NEMA Twistlock Photocontrol - Multi-Tap LB/HSS-21 =Field Installed House Side Shield for "E" LightBARs ^{13, 19} LB/HSS-07 =Field Installed House Side Shield for "F" LightBARs ^{13, 19} Mounting Accessories (Order Separately) Classical SA6154-XX =Bishop Single Pole Mount Arm SA6155-XX =Bishop Single Pole Mount Arm with Cross Rod SA6156-XX =Bishop Twin Pole Mount Arm SA6157-XX =Bishop Twin Pole Mount Arm with Cross Rods SA6158-XX =Traditional Single Pole Mount Arm SA6159-XX =Traditional Single Pole Mount Arm with Rounded Upper Bar SA6160-XX =Traditional Single Pole Mount Arm with Rounded Lower Bar ¹⁵ SA6161-XX =Traditional Single Pole Mount Arm with 45° Upper Bar SA6162-XX =Traditional Single Pole Mount Arm with 45° Lower Bar ¹⁵ SA6163-XX =Traditional Single Pole Mount Arm with 45° Upper Strap SA6165-XX =Traditional Twin Pole Mount Arm SA6166-XX =Traditional Twin Pole Mount Arm with Rounded Upper Bars SA6167-XX =Traditional Twin Pole Mount Arm with Rounded Lower Bars ¹⁵ SA6168-XX =Traditional Twin Pole Mount Arm with 45° Upper Bars SA6169-XX =Traditional Twin Pole Mount Arm with 45° Lower Bars ¹⁵ SA6170-XX =Traditional Twin Pole Mount Arm with 45° Upper Straps SA6171-XX =Mast Arm Adapter Modern SA6105-XX =Bishop Single Pole Mount Arm SA6106-XX =Bishop Single Pole Mount Arm with Cross Rod SA6107-XX =Bishop Twin Pole Mount Arm SA6108-XX =Bishop Twin Pole Mount Arm with Cross Rods SA6109-XX =Traditional Single Pole Mount Arm SA6110-XX =Traditional Single Pole Mount Arm with Rounded Upper Bar SA6111-XX =Traditional Single Pole Mount Arm with Rounded Lower Bar ¹⁵ SA6112-XX =Traditional Single Pole Mount Arm with 45° Upper Bar SA6113-XX =Traditional Single Pole Mount Arm with 45° Lower Bar ¹⁵ SA6114-XX =Traditional Single Pole Mount Arm with 45° Upper Strap SA6116-XX =Traditional Twin Pole Mount Arm SA6117-XX =Traditional Twin Pole Mount Arm with Rounded Upper Bars SA6118-XX =Traditional Twin Pole Mount Arm with Rounded Lower Bars ¹⁵ SA6119-XX =Traditional Twin Pole Mount Arm with 45° Upper Bars SA6120-XX =Traditional Twin Pole Mount Arm with 45° Lower Bars ¹⁵ SA6121-XX =Traditional Twin Pole Mount Arm with 45° Upper Straps SA6122-XX =Mast Arm Adapter						
		Accessory Options (Add as Suffix to Accessories) ¹⁶ M =Modern Finial ¹⁷ A =Architectural Finial ¹⁷ N =Nostalgic Finial ¹⁷ 4 =NEMA Twistlock Photocontrol Receptacle ¹⁸						

NOTES:


- Customer is responsible for engineering analysis to confirm pole and fixture compatibility for all applications. Refer to our white paper WP513001EN for additional support information.
- Arm not included. Order separately. See mounting accessories.
- Standard 4000K CCT and greater than 70 RL.
- 21 LED LightBAR powered by 350mA and 7 LED LightBAR powered by 1A.
- Consult factory for driver surge protection values.
- Only for use with 480V Wye systems. Per NEC, not for use with ungrounded systems, impedance grounded systems or corner grounded systems (commonly known as Three Phase Three Wire Delta, Three Phase High Leg Delta and Three Phase Corner Grounded Delta systems).
- Custom and RAL color matching available upon request. Consult your lighting representative at Eaton for more information.
- Low-level output varies by bar count. Consult factory. Requires quantity of two or more LightBARs.
- Consult customer service for lead times and multiplier.
- Sensor mounted to the luminaire. Available in E01-E04 and F01-F04 configurations. Replace XX with mounting height in feet for proper lens selection, (e.g., MS-L25). Consult factory for additional information.
- Sensor mounted to the luminaire. Available in E02-E04 and F02-F04 configurations. Replace X with number of LightBARs operating in low output mode and replace XX with mounting height in feet for proper lens selection, (e.g., MS/3-L25). Maximum four bars in low output mode. Consult factory for additional information.
- Pendant mount option "PM48" must be used with Streetworks pendant mount kit only. Includes 48" long pendant pipe, swivel hanger and canopy cover. Other pendant lengths can be specified in inches (XX). Minimum pendant length is 9'-1/2". For lengths above 48", consult your lighting representative at Eaton for more information.
- Only for use with SL2, SL3 and SL4 distributions.
- Replace XX with color suffix.
- Requires use of 4" O.D. round straight pole.
- Add as suffix to mounting accessory. Example: SA6105-BK-R.
- Only available with traditional arms.
- Not available with finials, pendant mount "PM48" or bishop wall mounts.
- One required for each LightBAR.

MOUNTING ACCESSORIES


Pole mount arms are designed to fit both medium CEM/MEM housings. (Only these arms are compatible with the Epic luminaire). Arms feature a precision welded cast aluminum mounting hub for attachment of fixture head to arm with four stainless steel fasteners. Wall mount arms compliment pole mount luminaires and attractively transition fixture scale in lower mounting height pedestrian environments. Wall mount arms are designed to fit both medium CEM/MEM housings. Arms feature a precision welded cast aluminum mounting hub for attachment of fixture head to arm with four stainless steel fasteners.

**BISHOP SINGLE POLE MOUNT ARM**


SA6105 (Modern), SA6154 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 24 lbs. E.P.A: 0.92

**BISHOP SINGLE POLE MOUNT ARM WITH CROSS ROD**


SA6106 (Modern), SA6155 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 25 lbs. E.P.A: 0.98

**BISHOP TWIN POLE MOUNT ARM**


SA6107 (Modern), SA6156 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 37 lbs. E.P.A: 1.43

**BISHOP TWIN POLE MOUNT ARM WITH CROSS RODS**


SA6108 (Modern), SA6157 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 39 lbs. E.P.A: 1.55

**TRADITIONAL SINGLE POLE MOUNT ARM**


SA6109 (Modern), SA6158 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 20 lbs. E.P.A: 0.86

**TRADITIONAL SINGLE POLE MOUNT ARM WITH ROUNDED UPPER BAR**


SA6110 (Modern), SA6159 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 28 lbs. E.P.A: 1.4

**TRADITIONAL SINGLE POLE MOUNT ARM WITH ROUNDED LOWER BAR**


SA6111 (Modern), SA6160 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 25 lbs. E.P.A: 1.16

**TRADITIONAL SINGLE POLE MOUNT ARM WITH 45° UPPER BAR**


SA6112 (Modern), SA6161 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 28 lbs. E.P.A: 1.38

**TRADITIONAL SINGLE POLE MOUNT ARM WITH 45° LOWER BAR**

SA6113 (Modern), SA6162 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 24 lbs. E.P.A: 1.17


**TRADITIONAL SINGLE POLE MOUNT ARM WITH 45° UPPER STRAP**

SA6114 (Modern), SA6163 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 24 lbs. E.P.A: 1.17


**TRADITIONAL TWIN POLE MOUNT ARM**

SA6116 (Modern), SA6165 (Classical)
Slipfits over 4" round straight pole, or 4" O.D. by 6" tall round tenon.
Weight: 30 lbs. E.P.A: 1.44


MOUNTING ACCESSORIES


**TRADITIONAL TWIN POLE
MOUNT ARM WITH ROUNDED
UPPER BARS**


SA6117 (Modern), SA6166 (Classical)
Slipfits over 4" round straight pole,
or 4" O.D. by 6" tall round tenon.
Weight: 43 lbs. E.P.A: 2.28


**TRADITIONAL TWIN POLE
MOUNT ARM WITH ROUNDED
LOWER BARS**


SA6118 (Modern), SA6167 (Classical)
Slipfits over 4" round straight pole,
or 4" O.D. by 6" tall round tenon.
Weight: 40 lbs. E.P.A: 2.04


**TRADITIONAL TWIN POLE
MOUNT ARM WITH 45° UPPER BARS**


SA6119 (Modern), SA6168 (Classical)
Slipfits over 4" round straight pole,
or 4" O.D. by 6" tall round tenon.
Weight: 43 lbs. E.P.A: 2.24


**TRADITIONAL TWIN POLE
MOUNT ARM WITH 45° LOWER BARS**


SA6120 (Modern), SA6169 (Classical)
Slipfits over 4" round straight pole,
or 4" O.D. by 6" tall round tenon.
Weight: 40 lbs. E.P.A: 2.0


**TRADITIONAL TWIN POLE
MOUNT ARM WITH 45° UPPER STRAPS**


SA6121 (Modern), SA6170 (Classical)
Slipfits over 4" round straight pole,
or 4" O.D. by 6" tall round tenon.
Weight: 37 lbs. E.P.A: 1.81


MAST ARM ADAPTER


SA6122 (Modern), SA6171 (Classical)
Secures fixture to nominal 2" pipe
(2-3/8" horizontal O.D.)
Weight: 4 lbs.


NEMA TWISTLOCK PHOTOCONTROL (R)


Order separately (Not compatible with
finials or wall mount bishop arms)

Wall Mount Accessories

BISHOP WALL MOUNT ARM


SA6101 (Modern), SA6150 (Classical)
Mounts to wall with four stainless
steel lag bolts (provided by other).
Weight: 16 lbs.


**BISHOP WALL MOUNT ARM
WITH CROSS ROD**

SA6102 (Modern), SA6151 (Classical)
Mounts to wall with four stainless
steel lag bolts (provided by other).
Weight: 17 lbs.


TRADITIONAL WALL MOUNT ARM

SA6103 (Modern), SA6152 (Classical)
Mounts to wall with four stainless
steel lag bolts (provided by other).
Weight: 17 lbs.


**TRADITIONAL WALL MOUNT ARM
WITH 45° STRAP**

SA6104 (Modern), SA6153 (Classical)
Mounts to wall with four stainless
steel lag bolts (provided by other).
Weight: 18 lbs.