

## E26 6" Trim Series

### DESCRIPTION

Gimbal with 25° tilt (max.) and self-flange in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.


Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- 25° Tilt (max.), 360° rotation
- Adjustable gimbal for PAR38 lamps
- Torsion spring retention
- Socket supporting gimbal
- Self-flanged trim ring sized to hide gaps caused by construction tolerances.

Housings		Max Lamp Compatibility
H7ICT	H7RICT	
H7ICAT	H7RICAT	45W PAR38
E7ICAT	E7RICAT	
<hr/>		
H7ICTNB		
H7ICATNB		45W PAR38L
E7ICATNB		
<hr/>		
H7T	E7TAT	
H7TCP		90W PAR38
H7RT	E7RTAT	
<hr/>		
H7TNB	E7TATNB	90W PAR38

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.



### Dimensions:

A: 4-1/2" [113mm]  
 H: 1-1/8" [29mm]  
 OD: 7-3/4" [197mm]

### ORDERING INFORMATION

SAMPLE NUMBER: 6170WH

Trim	Finish
6170= 6" Gimbal with 25° tilt (max.), Self-flange	<b>WH</b> =White <b>BK</b> =Black <b>SN</b> =Satin Nickel <b>TBZ</b> =Tuscan Bronze

### HALO HOUSING COMPATIBILITY


Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
6170	Adjustable	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•	—	—	—	—		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
•	•	•	•	•	•	•	•	—	
		H27RT	E27TAT	E27RTAT					
—	—	—							

For use in select other's housings, refer to U.L. classification list at [www.cooperlighting.com](http://www.cooperlighting.com)

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.




**6170WH**  
White Gimbal



**6170BK**  
Black Gimbal



**6170SN**  
Satin Nickel Gimbal



**6170TBZ**  
Tuscan Bronze Gimbal

## 6170

6-Inch Gimbal  
 25° Tilt (max.),  
 Self-flange



For use in Halo listed housings.



Select trims are classified for use in others housings.  
 See [www.cooperlighting.com](http://www.cooperlighting.com)