


Project		Catalog #		Type	
Prepared by		Notes		Date	



# Metalux

## 14RLN

1' x 4' Recessed LED  
Specification Grade  
Rectilinear Shielding

### Typical Applications

- Commercial Office Spaces • Schools • Hospitals
- Retail Merchandising Areas

### Interactive Menu

- Order Information [page 2](#)
- Photometric Data [page 3](#)
- Control Systems [page 4](#)
- VividTune™ Color Tuning Solutions [page 5](#)
- Product Warranty

### Top Product Features

- Luminous center panel with gently elevated luminous side panels for a visually pleasing appearance
- Efficacy up to 139 lm/W, uniform illumination for a pleasant ambient environment
- 3000K, 3500K, and 4000K at 80 or 90 CRI
- White tuning solutions available, either 3000K - 5000K or 2700K - 6500K
- LED driver access from below the ceiling


### Product Certification




### Product Features



### Dimensional and Mounting Details



### Ceiling Compatibility



## Order Information

SAMPLE ORDER NUMBER: **14RLN-LD5-35-UNV-L835-CD1-U**

Rating	Series	Lamp Type	Lumen Output	Shielding	Voltage	Emergency	CCT
<b>[Blank]</b> =Standard <b>ATW</b> =Chicago <b>SW4</b> =Chicago Rated	<b>14RLN</b> =1x4 RLN Series	<b>LD5</b> =LED 5.0	<b>23</b> =2300 Lumen <sup>(2)</sup> <b>26</b> =2600 Lumen <b>31</b> =3100 Lumen <b>35</b> =3500 Lumen <b>40</b> =4000 Lumen	<b>Blank</b> =Standard Lens <b>RDP</b> =Rectilinear with Round Pattern Insert	<b>347V</b> =347 Volt <sup>(4)</sup> <b>UNV</b> =Universal Voltage 120-277 <b>48V</b> =48 Volt Low-voltage (Class 2) <b>120V</b> =120 Volt <sup>(12)</sup> <b>277V</b> =277 Volt <sup>(12)</sup>	<b>EL7W</b> =7-watt, 120V-277V emergency battery pack installed <sup>(5)</sup> <b>EL14W</b> =14-watt 120V-277V emergency battery pack installed <sup>(5)</sup> <b>EL7VW</b> =7-watt, DLVP-compatible low voltage emergency battery pack installed <sup>(6)</sup> <b>ELV14W</b> =14-watt DLVP-compatible low voltage emergency battery pack installed <sup>(6)</sup> <b>GTR2</b> =Bodine Generator Transfer Relay <sup>(6),(12)</sup> <b>ETRD</b> =Iota Emergency Transfer Relay with dimming control <sup>(6)</sup>	<b>L830</b> =3000K <b>L835</b> =3500K <b>L840</b> =4000K <b>L930</b> =3000K <b>L935</b> =3500K <b>L940</b> =4000K <b>L83050</b> =80CRI 3000K-5000K White Tuning <sup>(7)</sup> <b>L93050</b> =90CRI 3000K-5000K White Tuning <sup>(7)</sup> <b>L82765</b> =80CRI 2700K-6500K White Tuning <sup>(7)</sup> <b>L92765</b> =90CRI 2700K-6500K White Tuning <sup>(7)</sup>
	<b>Notes</b> (1) DesignLights Consortium® Qualified and classified for both DLC Standard and DLC Premium, refer to www.designlights.org for details.		<b>Notes</b> (2) Not compatible with WN driver.		<b>Notes</b> (3) Products also available in non-US voltages and frequencies for international markets. (4) 347V versions are not available with emergency options. (12) Must specify voltage as 120V or 277V when ordering GTR2 option.	<b>Notes</b> (5) With integral test switch/ indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES-format photometry for luminaire under emergency operation available. (6) Used to bypass local control during outage. Must be used in conjunction with UL 1008 device (provided by others). GTR2 option includes 2 relays on fixtures with dimming drivers. ETRD option only requires one relay when used on a dimming fixture. (12) Must specify voltage as 120V or 277V when ordering GTR2 option. (C) Consult DLVP system pages for additional details and compatibility.	<b>Notes</b> (7) White tuning provides correlated color temperatures (CCT) between 3000K (warm) to 5000K (cool) or 2700K (warm) to 6500K (cool). Must be used in conjunction with WZA driver only. Must be used with two (2) 10V dimming control channels, 1 color, 1 intensity.

Factory Wiring	Driver Type	Number of Drivers	Integrated Sensing Systems	Packaging	Accessories
<b>A3/8-4/18GDIM</b> =3/8" Flex with 0-10V Dimming Leads. Multiple other configurations available. See below for details. <b>A3/8-5/18GDIM</b> =Flex with 0-10V Dimming leads and Blue for alternate wiring. See below for details.	<b>CD</b> =0-10V Dimming Driver (1%-100% Dimming) <b>WN</b> =WaveLinX Wireless Fixture, No Sensor. (A),(G),(H) <b>5LTD</b> =Fifth Light DALI Driver (10%-100% Dimming) <sup>(8),(9)</sup> <b>5LTHD</b> =Fifth Light Dimming Driver (1%-100% Dimming) <sup>(9)</sup> <b>LV1</b> =DLVP Dimming Driver (0%-100% Dimming) <sup>(3)</sup> <b>SD</b> =Step Dimming Driver (50% or 100% Dimming) <sup>(8)</sup> <b>LH</b> =Lutron HiLume (LDE1 series) 1%-100% EcoSystem Driver with Soft-on Fade to Black dimming <sup>(2)</sup> <b>LS</b> =Lutron 5 Series (LDES-Series) 5%-100% EcoSystem Driver <sup>(1)</sup> <b>WZA</b> =White Tuning, 2 ch, Intensity and CCT Control <sup>(9)</sup> <b>SR</b> =Sensor-ready Dimming Driver (1%-100% Dimming)	1=1 Driver	<b>[Blank]</b> =No Sensor <b>WAA</b> =WaveLinX Wireless Integrated Sensor <sup>(10),(A)</sup> <b>WAB</b> =WaveLinX Lite Wireless Integrated Sensor <sup>(10),(B)</sup> <b>SLVDP1</b> =Low-voltage Integrated Sensor <sup>(10),(C)</sup> <b>SVPD1</b> =0-10V Stand-alone Integrated Sensor <sup>(10),(D)</sup>	<b>U</b> =Unit Pack <b>PALC</b> =Job Pack, in carton	<b>EQ-CLIP-U</b> =T-BAR Safety Earthquake Clips <sup>(11)</sup> <b>F2M-14S-W-U</b> =Field Installed Flange Kit <b>DF-14W-U</b> =1' x 4' Drywall Frame Kit <b>SK-14-W-U</b> =Field Install Surface Mount Kit, Tall <b>ISHH-01</b> =Programming Remote for Integrated Sensor <sup>(2)</sup> <b>ISHH-02</b> =Personal Control Remote for Integrated Sensor <sup>(2)</sup>
<b>Flexible Metal Conduit Options</b> Flex options available for 0-10V dimming control, DALI dimming control, emergency and night light functions. 72-inch factory-installed and pre-wired to driver, fitted to luminaire housing access plate with 90° enclosed FMC connector. Not all options may be combined and installation ratings vary by type. <b>A3/8-4/18GDIM series notes:</b> Factory installed dimming option 3/8" flexible metal conduit with 2-#18 power and ground wires and 2-#18 UL-listed jacketed 0-10V +/- control wires. Meets UL 66, 83, 1479, 1569, 1581, 2556, NEC® 250.118, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, 72; Federal Specification A-A-59544 (formerly J-C-308); all applicable OSHA and HUD Requirements. UL Classified 1-, 2-, and 3-hour through penetration with applicable fire stop product (not included). May be surface mounted, fished and/or embedded in plaster. Cable tray and approved raceway rated, install per NEC®; Environmental Air-Handling Space Installation per NEC® 300.22(C).	<b>Notes</b> (8) 2300, 2600 and 3100 Lumen packages not available with Step-Dim (SD) and Fifth Light (5LTD) driver option. (9) White tuning provides correlated color temperatures (CCT) between 3000K (warm) to 5000K (cool) or 2700K (warm) to 6500K (cool). Must be used in conjunction with WZA driver only. Must be used with two (2) 10V dimming control channels, 1 color, 1 intensity. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (A) Consult WaveLinX system pages for additional details and compatibility. (B) WaveLinX Lite devices are not currently compatible with the WaveLinX Wireless Area Controller. Consult WaveLinX Lite system pages for additional details and compatibility. (C) Consult DLVP system pages for additional details and compatibility. (D) Consult SVPD series system pages for additional details and compatibility. (E) Consult Fifth Light system pages for additional details and compatibility. (F) Consult Marketplace Options - Lutron system pages for additional details and compatibility. Compatible only with driver series shown, and may require two or more drivers. Requires field commissioning to operate or dim. Contact Lutron at www.lutron.com. (G) Not compatible with GTR, ETRD, or integrated sensor options. (H) Available with UNV voltage only.		<b>Notes</b> (10) WZA driver only available with WAA sensor. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (A) Consult WaveLinX system pages for additional details and compatibility. (B) WaveLinX Lite devices are not currently compatible with the WaveLinX Wireless Area Controller. Consult WaveLinX Lite system pages for additional details and compatibility. (C) Consult DLVP system pages for additional details and compatibility. (D) Consult SVPD series system pages for additional details and compatibility.		<b>Notes</b> (11) An EQ Grid Clip is recommended for all 9/16" ceiling systems. Four required per fixture. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (D) For use with SVPD sensor only. Consult SVPD series system pages for additional details and compatibility.

## Product Specifications

### Construction

- 5-5/8" housing constructed of die-formed, code gauge cold rolled steel
- Full length die-formed stiffeners and unibody endplate for added strength
- Four auxiliary fixture end suspension points provided
- Wireway cover removable without tools
- Endplates provided with Grid-Lock feature for safety

### Integrated Controls

- 0-10V dimming to 1% standard
- WaveLinX wireless fixture for sensor-less wireless control
- WaveLinX wireless sensor compatible for standalone, controlled, connected, and IoT capability
- SVPD sensor compatible for standalone functionality
- Low-voltage sensor and driver compatible for DLVP applications
- DALI 2.0, Lutron, and step-dimming available

### LED and Light Engine

- LED's available in 3000K, 3500K, or 4000K at 80 CRI minimum and 90 CRI minimum
- Color accuracy  $\leq 3$ -Step MacAdam ellipse (SDCM)
- TM21 life at 60,000 hours up to L92 and calculated L70 exceeds 290,000 hrs.

- Drivers available in 120-277V and 347V
- Tunable white options available with Cooper Lighting Solutions' VividTune

### Emergency Battery Options

- Optional 120-277V emergency battery available in 7W or 14W
- 90-minute backup period for code compliance
- Test switch with laser pointer and testing from floor feature for ease of use
- EZ Key feature prevents accidental discharge during construction
- Generator transfer options available

### Finish

- Multistage, iron phosphate pretreatment
- 90% reflective, matte white enamel finish
- Full fixture housing painted after fabrication

### Hinging/Latching

- Positive cam action steel latches with baked white enamel finish
- Safety-lock T-hinges allow hinging and latching either side
- Door assembly hinges down for easy access to driver and LEDs from below

### Frame/Sheilding

- Die formed, heavy gauge flat steel door
- Mitered corners and painted after fabrication
- Baked matte white enamel finish
- Positive light seals
- Acrylic frosted lens

### Compliance


- IC rated for insulation contact
- cULus listed for damp locations
- RoHS compliant
- Tested to IESNA LM-79 and LM-80
- Stated life tested to TM21 standards
- Can be used for State of California Title 24 high efficacy luminaire

### Warranty


- Five year warranty standard. Optional ten year warranty available.

## Photometric Data

[View IES files](#)



**14RLN-LD5-26-UNV-L835-CD1-U**  
 Electronic Driver  
 Linear LED 3500K  
 Spacing criterion: (H) 1.21 x mounting height,  
 (L) 1.2 x mounting height  
 Lumens: 2647.5  
 Input Watts: 24.7W  
 Efficacy: 107.2 lm/W  
 Test Report: 14RLN-LD5-26-UNV-L835-CD1-U.IES



**14RLN-LD5-35-UNV-L835-CD1-U**  
 Electronic Driver  
 Linear LED 3500K  
 Spacing criterion: (H) 1.21 x mounting height,  
 (L) 1.21 x mounting height  
 Lumens: 3584.6  
 Input Watts: 35.6W  
 Efficacy: 100.7 lm/W  
 Test Report: 14RLN-LD5-35-UNV-L835-CD1-U.IES

## Energy and Performance Data

Stock or MTO	Catalog Logic (Rectilinear Shielding)	Delivered Lumens	Watts	Efficacy (lm/W)
MTO	14RLN-LD5-23-UNV-L830-CD1-U	2278	21.9	104
MTO	14RLN-LD5-23-UNV-L835-CD1-U	2373	21.9	108
MTO	14RLN-LD5-23-UNV-L840-CD1-U	2373	21.9	108
MTO	14RLN-LD5-26-UNV-L830-CD1-U	2541	24.7	103
MTO	14RLN-LD5-26-UNV-L835-CD1-U	2647	24.7	107
MTO	14RLN-LD5-26-UNV-L840-CD1-U	2647	24.7	107
MTO	14RLN-LD5-31-UNV-L830-CD1-U	3034	30.6	99
MTO	14RLN-LD5-31-UNV-L835-CD1-U	3160	30.6	103
MTO	14RLN-LD5-31-UNV-L840-CD1-U	3160	30.6	103
MTO	14RLN-LD5-35-UNV-L830-CD1-U	3442	35.6	97
MTO	14RLN-LD5-35-UNV-L835-CD1-U	3585	35.6	101
MTO	14RLN-LD5-35-UNV-L840-CD1-U	3585	35.6	101
MTO	14RLN-LD5-40-UNV-L830-CD1-U	3907	41.9	93
MTO	14RLN-LD5-40-UNV-L835-CD1-U	4070	41.9	97
MTO	14RLN-LD5-40-UNV-L840-CD1-U	4070	41.9	97

### Lumen Maintenance

Ambient Temperature	TM-21 Lumen Maintenance (60,000 hours) <sup>(1)</sup>	Theoretical L70 (Hours) <sup>(2)</sup>
25°C	> 92%	> 267,500

Notes: (1) Supported by IES TM-21 standards. (2) Theoretical values represent estimations commonly used; however, refer to the IES position on LED Product Lifetime Prediction, IES PS-10-18, that explains proper use of IES TM-21 and LM-80.

### 90 CRI

Lumen Adjustment Factors 80->90 CRI	
3000K	0.865
3500K	0.861
4000K	0.0883
5000K	n.a.

### Example of Lumen Adjustment Calculation

14RLN-LD5-35-UNV-L935-CD1-U  
 at 90CRI at 3500K

Lumen Adjustment Factor = 0.861

Total Light Output =  
 $3,585 \text{ lm} \times 0.861 = 3,086 \text{ lm}$

Efficacy =  $\frac{3,086 \text{ lm}}{35.6 \text{ W}} = 86.6 \text{ lm/W}$

### Shipping Data

Catalog No.	Wt.
14RLN-LD5-26	19 lbs.
14RLN-LD5-35	19 lbs.

## Control Systems

- WaveLinx Wireless
- WaveLinx Wired
- WaveLinx Lite
- DLVP
- VividTune




Connected Systems  
[CLICK HERE](#)

The RLN with Integrated Sensor technology provides automatic energy savings without sacrificing performance. The RLN delivers superior lighting with integrated occupancy and daylighting controls.


For standalone and controlled applications, the WaveLinx Lite integral sensor provides out-of-the-box functionality with no gateways required and factory startup is not needed.

When more connectivity is required, the WaveLinx Wireless sensor meets modern code and utility requirements, delivers energy and cost savings, while enabling buildings to become smart buildings.


The WaveLinx Wireless Connected Lighting System combined with Trellix provides an open IoT platform and infrastructure that connects intelligent sensors leveraging the real-estate of the physical light fixture to solve higher complexity problems to deliver actionable insights through the aggregation of valuable data.



TOP VIEW:




SIDE VIEW:



**Note:** Installation of integrated sensors within 3-ft (1m) of HVAC air vents is not recommended. The pattern shown is intended solely as a general guide and is not to scale.

## Systems comparison chart

Cooper Lighting Solutions provides many lighting system solutions designed to satisfy code requirements and meet the unique needs of any project.



**Standalone**



**Controlled**  
WaveLinx Lite



**Connected**  
WaveLinx Wireless



**Enterprise**  
Trellix

	Standalone	Controlled WaveLinx Lite	Connected WaveLinx Wireless	Enterprise Trellix
<b>Occupancy</b>	Yes	Yes	Yes	Yes
<b>Daylighting</b>	Yes	Yes	Yes	Yes
<b>Gateways</b>	-	-	1 WAC	300 WACs
<b>Devices</b>	-	50 per Area (1400 per site)	150 per WAC	45,000 per Core Enterprise
<b>Software</b>	-	WaveLinx Lite Mobile App	WaveLinx Mobile App	Trellix Core
<b>Areas</b>	-	28 per Site	16 per WAC	up to 4,800
<b>Zones</b>	-	16 per Area	16 per Area	up to 76,800
<b>Scheduling</b>	-	-	Local	Global
<b>VividTune™</b>	-	-	Yes	Yes
<b>Plug-Load Control</b>	-	-	Yes	Yes
<b>Integration</b>	-	-	-	BACnet, API
<b>Dashboards</b>	-	-	-	Energy, Occupancy
<b>Configuration</b>	-	Installer	Technician	Technician / IT

## SCALABILITY

devices

areas


floors

buildings



14RLN LED with VividTune Tunable White

VividTune tunable white luminaires from Cooper Lighting Solutions deliver high-quality light in a broad range of continuously variable color temperatures and intensities. Create a dynamic environment by adjusting the ambient light warmer or cooler to influence mood, support the task at hand, or create a dramatic ambience. The ability to control correlated color temperature and intensity separately using simple controls is the next evolution of LED lighting for the commercial, educational, healthcare and hospitality space. The unparalleled flexibility and number of available lighting environments enable users to find the right light with tunable white.




Performance Data\*

Tunable White - Lumen Adjustment Factors (example only)				
CCT	3000K-5000K		2700K-6500K	
	80 CRI	90 CRI	80 CRI	90 CRI
2700K	-	-	0.922	0.787
3000K	0.949	0.781	0.948	0.818
3500K	1.004	0.853	0.981	0.859
4000K	1.054	0.922	1.002	0.887
4500K	1.064	0.938	1.020	0.910
5000K	1.064	0.938	1.034	0.928
6500K	-	-	1.049	0.953

1' x 4' RLNLED - Example of Approximate Lumen Calculation			
	Standard Catalog #	VividTune 80 CRI Catalog #	VividTune 90 CRI Catalog #
CCT Setting	14RLN-LD5-35-UNV-L835-CD1-U	14RLN-LD5-35-UNV-L83050-W2A1-U	14RLN-LD5-35-UNV-L93050-W2A1-U
3000K	-	3402	2800
3500K	3585	3599	3058
4000K	-	3779	3305
4500K	-	3814	3363
5000K	-	3814	3363

Controlling VividTune Tunable White

VividTune luminaires make tunable white more accessible by using simple and familiar controls. From wall dimmers to wireless controls, VividTune tunable white luminaires are compatible with industry standard 0-10V dimming controls. A single 0-10V dimming input is used to control intensity (brightness) while a second 0-10V dimming input is used to adjust CCT. For suggested control configurations, go to [www.cooperlighting.com](http://www.cooperlighting.com) for tunable white application guides.



Example of Lumen Adjustment Calculation

14RLN-LD5-35-UNV-L83050-W2A1-U at 80 CRI tuned to 3500K

Adjusted Lumen = published lm x adjusted lm factor

Adjusted Lumen = 3585 x 1.004

Adjusted Lumen = 3599 lm

\* Lumen adjustment factors are for reference and may be different for each product selected. Refer to IES files for actual performance data on each.