


Portfolio 6" LED Downlighting

VividTune tunable white luminaires from Eaton deliver high-quality light in a broad range of continuously variable color temperatures and intensities. Create a dynamic environment by adjusting the ambient light warmer or cooler to influence mood, support the task at hand, or create a dramatic ambience. The ability to control correlated color temperature and intensity separately using simple controls is the next evolution of LED lighting for the commercial, educational, healthcare and hospitality space. The unparalleled flexibility and number of available lighting environments enable users to find the right light with tunable white.



Energy and Performance Data

| Tunable White - LED Light Level Outputs | | | | | |
|---|--------|-----------------------|-----------------------|---------|------|
| Distribution | Lumens | Delivered lumens 2050 | Delivered lumens 2765 | Wattage | LPW |
| Medium | 1000 | 833 | 922 | 14 | 65.9 |
| | 1500 | 1201 | 1359 | 22 | 61.8 |
| | 2000 | 1466 | 1655 | 28 | 59.1 |
| Wide | 1000 | 936 | 1035 | 14 | 73.9 |
| | 1500 | 1350 | 1527 | 22 | 69.4 |
| | 2000 | 1647 | 1860 | 28 | 66.4 |
| Shallow | 1000 | 926 | 1025 | 14 | 73.2 |
| | 1500 | 1336 | 1512 | 22 | 68.7 |
| | 2000 | 1630 | 1841 | 28 | 65.8 |

| Tunable White - Lumen Adjustment Factors | | |
|--|-------------|-------------|
| CCT | 3000K-5000K | 2700K-6500K |
| | 90 CRI | 90 CRI |
| 2000K | 0.732 | - |
| 2700K | 0.902 | 0.854 |
| 3000K | 0.900 | 0.999 |
| 3500K | 0.918 | 1.000 |
| 4000K | 0.963 | 0.975 |
| 4500K | 0.994 | 0.992 |
| 5000K | 1.008 | 1.011 |
| 6500K | - | 1.033 |

Controlling VividTune Tunable White

VividTune luminaires make tunable white more accessible by using simple and familiar controls. From wall dimmers to wireless controls, VividTune tunable white luminaires are compatible with industry standard 0-10V dimming controls. A single 0-10V dimming input is used to control intensity (brightness) while a second 0-10V dimming input is used to adjust CCT. For suggested control configurations, go to www.eaton.com/lighting for tunable white application guides.

