| Project | Catalog # | Туре | |
|-------------|-----------|------|--|
| Prepared by | Notes | Date | |



Interactive Menu

- Order Information page 2
- Photometric Data page 3
- Control Solutions page 5
- VividTune[™] Color Tuning Solutions page 6
- BioUp Melanopic Lighting page 7
- · Product Warranty

Metalux

Cruze ST 22CZ2

2' x 2' LED Specification Grade Troffer

Typical Applications

Office • Education • Healthcare • Hospitality • Retail

Product Certification















Product Features























Top Product Features

- Latch-less design provides clean architectural look
- BioUp melanopic lighting options for 30% circadian boost and earn WELL Building Standard points
- VividTune CCT tuning options from 3000K-5000K or 2700K-6500K
- · Designers delight ribbed, smooth and round perforated lens options
- · High performance efficacy up to 151 lm/W
- · Integrated sensor systems occupancy, daylight and IoT connectivity
- · Options to meet Build America, Buy America, Buy American and other domestic preference requirements

Dimensional and Mounting Details






Shielding





Ceiling Compatibility



Trim

Type

Standard

Standard

Order Information

SAMPLE ORDER NUMBER: 22CZ2-34HE-UNV-L835-CD1-U

| Domestic Preferences (1) | Rating | Series | Air | Lumen Level / Efficacy Option | | y Option |
|--|---|-----------------------|--|---|---|--|
| [Blank]=Standard BAA=Buy American Act TAA=Trade Agreements Act BABA=Build America Buy America Act | [Blank]=Standard ATW-SW4= Chicago Rated | 22CZ2=2x2 Cruze ST | [Blank]=Standard A=Air (Vented) ⁽²⁾ | Standard [Blank] 20=2000 Lumens (4) 24=2400 Lumens (3) 32=3200 Lumens (3) 39=3900 Lumens (3) 44=4400 Lumens (3) | High Efficacy [HE] 49, 49 20HE=2000 Lumens 24HE=2400 Lumens 29HE=2900 Lumens 34HE=3400 Lumens 39HE=3900 Lumens 44HE=4400 Lumens | Very High Efficacy [VHE] 20VHE=2000 Lumens 24VHE=2400 Lumens 29VHE=2900 Lumens 34VHE=3400 Lumens 39VHE=3900 Lumens 50VHE=5000 Lumens 55VHE=5500 Lumens 65VHE=6500 Lumens 65VHE=6500 Lumens 65VHE=6500 Lumens 65VHE=6500 Lumens 65VHE=5500 Lumens 65VHE=5500 Lumens 63.60 75VHE=7500 Lumens 63.60 90VHE=9000 Lumens 63.60 90VHE=9000 Lumens 63.60 90VHE=9000 Lumens 63.60 100VHE=10000 Lumens 63.60 |
| Notes | | | Notes | | Notes | |
| (1) Only product configurations with these prefixes are built to be compliant with the Buy American Act of 1933 (BAA), Trade Agreements Act of 1979 (TAA), or the Build America Buy America Act (BABA). BABA is the minimum Government compliance requirement for the Build America Buy America standards which is part of the Infrastructure and Investment Jobs Act (IIJA). Individual Government Agencies may have more stringent compliance standards. Please refer to <u>DOMESTIC PREFERENCES</u> website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements. | | | (2) Air version is intended for air return through plenum. See air return data table for air flow volumes. Air option not available with ATW-SW4. Air requires "PAF" option. | (3) VividTune white tuning and BioUp static and dynamic options are not available with these lumen/efficacy selections. (4) BioUp lumen option. (5) Vividtune lumen option. (6) Available with CD and HCD drivers only. | | |

| Shielding | Voltage (5) | Options | Emergency Options |
|--|---|---|--|
| [Blank]=Ribbed Frosted Acrylic Lens (standard) S=Smooth Frosted Acrylic Lens HRP=High-Efficiency Round Perf Inlay SQR=Square Ribbed Frosted Acrylic Lens | UNV=Universal Voltage 120-277 347V=347 Volt | GL=Single Element Fuse GM=Double Element Fuse PAF=Painted After Fabrication | [Blank]=No emergency LTW=7-watt 120V-277V emergency battery pack (6) EL10W=10-watt 120V-277V emergency battery pack (6) EL14W=14-watt 120V-277V emergency battery pack (6) EL14W=14-watt 120V-277V emergency battery pack (8) EL14WSD=14W emergency battery pack with self-diagnostic installed (6), (8) EL14WSD=14W emergency battery pack with self-diagnostic installed (6), (8) ETR0=Emergency Transfer Relay with dimming control (7) RRU=LVS Controls Emergency Transfer Relay with dimming control (7) UEL1W=UL924 Listed luminaire, 14-watt 120V-277V emergency battery pack (6), (10) UEL10WSD=Bodine 10W emergency battery pack with self diagnostic installed (6), (8), (10) UETR0=UL924 Listed luminaire, Emergency Transfer Relay with dimming control (7), (10) UETR0=UL924 Listed luminaire, LVS Controls Emergency Transfer Relay with dimming control (7), (10) URRU=UL924 Listed luminaire, LVS Controls Emergency Transfer Relay with dimming control (7), (10) WNPS=WaveLinx wireless Normal Power Sensing (NPS) capable device (22) |
| | Notes (5) Products also available in non-US voltages and frequencies for international markets. | | Notes (6) Factory installed with integral test switch/indicator/laser test. For approximate delivered lumens multiply the lumens per watt of the desired fixture by the wattage of the emergency battery pack (100 lm/W x 7=700 lumens). IES-format photometry for luminaire under emergency operation available. Battery option increases total height by 1 inch. (7) Used to bypass local contouring outage. Must be used in conjunction with U.1 1008 device (provided by others). Devices are universal voltage (UNV). 347 not available. (8) EL10WSD and tall and available with 347V. (9) UEL10WSD not available with 347V. (10) Cannot be used with BioUP objects. (23) Must be ordered with WLS or WPS sensor. WNPS cannot be ordered with emergency or relay options such as ETRD, GTR2, ELxxx or GTDU. |

| CRI/CCT | Flex |
|--|--|
| L830=80CRI, 3000K L830=80CRI, 3500K L840=80CRI, 4000K L850=80CRI, 5000K L930=90CRI, 3000K L935=90CRI, 3000K L940=90CRI, 4000K L950=90CRI, 5000K L950=90CRI, 5000K L950=90CRI, 5000K L93050=90CRI 3000K-5000K White Tuning (*2) L93050=90CRI 3000K-5000K White Tuning (*2) L92765=80CRI 2700K-6500K White Tuning (*2) B35=BioUp Static 3500K (*3) B40=BioUp Static 3500K (*3) B40=BioUp Static 4000K (*3) B50=BioUp Static 5000K (*3) B2750=BioUp Tunable 2700K-5000K (*4) | [Blank]=No Flex A3/8-4/18GDIM=3/8" Flex with 0-10V Dimming Leads A3/8-2/18G=3/8" Flex with line and common A3/8-5/18GDIM=Flex with 0-10V Dimming leads and Blue for alternate wiring. See below for details. |
| Notes | Flexible Metal Conduit Options |
| (12) VividTune provides correlated color temperatures (CCT) between 3000K (warm) to 5000K (cool) or 2700K (warm) to 6500K (cool). Must be used in conjunction with W2A driver only. Must be used with two (2) 10V dimming control channels, 1 cct, 1 intensity, May be combined with Mavelinx sensor control systems. (13) BioUp Static to be used with HCD driver. (14) BioUp Tunable provides correlated color temperatures (CCT) between 2700K (warm) to 5000K (cool). Must be used with W2A (for two channel 0-10V Control) or W2D (for 2 channel Dali Control) driver. See BioUp page for more information. | Flex options available for 0-10V dimming control, DALI dimming control, emergency and night light functions. 72-inch factory-installed and pre-wired to driver, fitted to luminaire housing access plate with 90° enclosed FMC connector. Not all options may be combined and installation ratings vary by type. See online configurator for all filex options. A318-4/186DIM series notes: Factory installed dimming option 3/8° flexible metal conduit with 2-#18 power and ground wires and 2-#18 UL-listed jacketed 0-10V 4-/ control wires. Meets UL 66, 83, 14/9, 1569, 1581, 2556. NEC® 250.118, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, 72; Federal Specification A4-59544 (formerly J-C-30B); all applicable OSHA and HUD Requirements. UL Classified 1-, 2-, and 3-hour through penetration with applicable fire stop product (not included). May be surface mounted, fished and/or embedded in plaster. Cable tray and approved raceway rated, install per NEC®; Environmental Air-Handling Space Installation per NEC® 300.22(C). |

continued next page



Order Information CONTINUED

| Driver Type | No. of Drivers | Integrated Sensing Systems (17) | Packaging | Accessories (order separately) (21) |
|--|----------------|--|--|---|
| CD=0-10V Driver (10%-100% Dimming) (22) CDW=NonProgrammable Driver, Limited Lumen Packages, 0-10V Dimming (10%-100%) HCD=0-10V Driver (1%-100% Dimming) (22) SLTD=DALI Driver (5%-100% Dimming) SLTHD=DALI Driver (11-100% Dimming) SD=Step Dimming Driver (50%-100% Dimming) LH=Lutron HiLume 1% EcoSystems (LDE1) (9) W2A=White Tuning, 2 c.b, Analog 0-10V (1%-100% Dimming) (15). (22) W2D=White Tuning, DALI Type 8 (1%-100% Dimming) (16) | 1=1 Driver | [Blank]=No Sensor WLS (formerly WAB)=WaveLinx LITE Wireless Sensor, Occupancy w/ photocell, Independent & Networked (19,(8)) WPS (formerly WAA)=WaveLinx RD Wireless Sensor, Occupancy w/ photocell, Networked (18),(A) WLN=WaveLinx LITE Wireless Control Node, without sensor (19),(8) WPN=WaveLinx PRO Wireless Control Node, without sensor (18),(A) | U=Unit Pack PAL=Job Pack, out of carton PALC=Job Pack, in carton | CZ2-EQCLIP-U PK="CZ2" Earthquake Clip Kit (4 clips per bag kit) (20) DF-22W-U=2' x 2' Drywall Frame Kit SMK-22-W=4" Tall Surface Mount Kit, 2' x 2' |
| Notes (15) W2A used with two (2) 10V dimming control channels - CCT and intensity. (16) W2D for use with BioUp options only. White tuning CCT between 2700K and 5000K. Must be used with DAL controls, one address to control two channels - intensity and CCT. May not be used with sensing systems. For Emergency options ONLY EL10WSD can be used. (22) When selecting 0-10V driver with Integrated Sensing System a 0-10V driver might be susbstituted with another type. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (F) Consult Marketplace Options - Lutron system pages for additional details and compatibility. Compatible only with driver series shown, and may require two or more drivers. Requires field commissioning to operate or dim. Contact Lutron at www.lutron.com. | | Notes (17) Matching width lens band on other side of sensor band may be supplied for symmetrical appearance. Required for use with sensor and emergency combination. Add "D" to sensor ordering as shown - WPSD, MLSD. (18) WPS sensor and WPN node to be used with CD, HCD or W2A driver. (19) WLS sensor and WNN node to be used with CD or HCD driver. Integrated options must be used in conjunction with the associated system and may not be compatible with other options or accessories. Please refer to the following: (A) Consult WaveLinx PRO system pages for additional details and compatibility. (B) Consult WaveLinx LITE system pages for additional details and compatibility. | | Notes (20) An EQ Grid Clip is recommended for all 9/16' ceiling systems. Four required per fixture. (21) Accessories sold separately will be separately will be separately analyzed under domestic preference requirements. Consult factory for further information. |



Product Specifications

Construction

- Die formed of code gauge prime cold rolled steel with full length die-formed stiffeners
- Unibody endplates attached with interlocking tabs and screws
- · Hemmed side flanges
- · Four auxiliary fixture end suspension points
- · Integral Grid-lock feature for endplates for added
- · Optional earthquake clips available

Integrated Controls

- Standard with 0-10V dimming driver (10% standard, 1% optional)
- · Integrated WaveLinx options provide wireless individual fixture control and enable code compliance, increased energy savings, grouping of fixtures, and connection to WaveLinx control systems
- DALI 2.0, Lutron, and step-dimming available

LED and Light Engine

- LED's available in 3000K, 3500K, 4000K, or 5000K at 80 CRI minimum and 90 CRI minimum
- Color accuracy ≤3-Step MacAdam ellipse (SDCM)
- TM21 life at 60,000 hours up to L90 and calculated L70 exceeds 203,000 hrs.
- · Drivers available in 120-277V and 347V
- Tunable white options available with Cooper Lighting Solutions' VividTune
- BioUp melanopic lighting options available in static or tunable white

Emergency Options

- 120V-277V integral emergency battery pack comes in 7-watts, 10-watt, or 14-watts
- Self-diagnostic emergency battery available in 10 or 14-watts (NFPA 101® Life Safety Code®)
- · Constant power to the LED system for controlled, predictable discharge
- Integrated test switch/indicator light visible from floor
- · Min. 90-minute backup period for code compliance
- · Integral emergency transfer relay available for generator equipped power systems
- WNPS enables Normal Power Sensing (NPS) functionality, allowing detection of normal power availability as part of a WaveLinx EM solution
- · NPS must be ordered with Wavelinx LITE or PRO sensor to enable wireless sensing EM solution
- Order standard product with compatible emergency control device (ESP-P) when pairing NPS enabled luminaires in any space
- · NPS luminaires meet requirements

Shielding

- · Ribbed acrylic frosted lens standard
- · Optional smooth acrylic frosted lens (S)
- · Optional square ribbed frosted acrylic lens (SQR)
- · Optional High-Efficiency Round Perf Inlay (HRP)
- · Replacement lenses available, contact factory
- Lens is acrylic with features on the face and sides to optimize the direct and indirect lighting contributions for improved glare and efficacy

Compliance

- IC rated for insulation contact
- cULus listed for damp locations
- RoHS compliant
- · Tested to IESNA LM-79 and LM-80
- · Stated life tested to TM21 standards
- Can be used for State of California Title 24 high efficacy luminaire

BABA Domestic Preference Compliance


· This Cooper product is manufactured in the US and meets the BABA cost of components rule. To verify a configured product with specific accessories and options meets BABA Domestic Preference Requirements; submit this catalog number to Cooper Lighting Quotation team for validation by our Engineering and Manufacturing teams. Our BABA designation is based on the minimum compliance requirement for BABA. Individual Government Agencies may have more stringent compliance standards. Please refer to the **DOMESTIC** PREFERENCES website or consult the CLS Domestic Preferences team for more information. Components shipped separately may be separately analyzed under domestic preference requirements.

· Five-year limited warranty standard. Optional ten year limited warranty available.

- · Multistage, iron phosphate pretreatment
- · 90% reflective, matte white enamel finish
- Full fixture housing pre-painted matte white (choose PAF option for "Paint after Fabrication")

Photometric Data






22CZ2-24-UNV-L830-CD1-U

Dimming Driver Linear LED 3000K

Spacing criterion: (II) 1.2 x mounting height, 1.28 x mounting height

Lumens: 2437 Input Watts: 21.9W Efficacy: 111.3 LPW

Test Report: 22CZ2-24-UNVL830-CD1-U.IES



22CZ2-24HE-UNV-L830-CD1-U

Dimming Driver Linear LED 3000K

Spacing criterion: (II) 1.19 x mounting height, (\bot) 1.27 x mounting height

Lumens: 2402 Input Watts: 19.2W Efficacy: 125.1 LPW

Test Report: 14CZ2-29-UNV-L830-CD1-U.IES

Energy and Performance Data

Standard Efficacy Versions – Single Row of LEDs Default CCT/Lumen Setting: 3500K/Med

| Catalog Number | Lumens | Watts | lm/W |
|-------------------------|--------|-------|------|
| 22CZ2-20-UNV-L835-CD1-U | 2142 | 16.2 | 132 |
| 22CZ2-24-UNV-L835-CD1-U | 2454 | 18.5 | 133 |
| 22CZ2-32-UNV-L835-CD1-U | 3272 | 24.2 | 135 |
| 22CZ2-39-UNV-L835-CD1-U | 3953 | 31 | 128 |
| 22CZ2-44-UNV-L835-CD1-U | 4462 | 33 | 134 |

High Efficacy Versions - Two Rows of LEDs

| Catalog Number | Lumens | Watts | lm/W |
|---------------------------|--------|-------|------|
| 22CZ2-20HE-UNV-L835-CD1-U | 2030 | 15.0 | 135 |
| 22CZ2-24HE-UNV-L835-CD1-U | 2474 | 18.1 | 137 |
| 22CZ2-29HE-UNV-L835-CD1-U | 2982 | 20.9 | 143 |
| 22CZ2-34HE-UNV-L835-CD1-U | 3426 | 24.3 | 141 |
| 22CZ2-39HE-UNV-L835-CD1-U | 3997 | 28.5 | 140 |
| 22CZ2-44HE-UNV-L835-CD1-U | 4567 | 32.8 | 139 |

Very High Efficacy Versions - Three Rows of LEDs

| Catalog Number | Lumens | Watts | lm/W |
|-----------------------------|--------|-------|------|
| 22CZ2-20VHE-UNV-L835-CD1-U | 2008 | 14.2 | 141 |
| 22CZ2-24VHE-UNV-L835-CD1-U | 2501 | 17.5 | 143 |
| 22CZ2-29VHE-UNV-L835-CD1-U | 3114 | 21.7 | 144 |
| 22CZ2-34VHE-UNV-L835-CD1-U | 3598 | 25.1 | 143 |
| 22CZ2-39VHE-UNV-L835-CD1-U | 4078 | 28.6 | 143 |
| 22CZ2-44VHE-UNV-L835-CD1-U | 4620 | 32.6 | 142 |
| 22CZ2-50VHE-UNV-L835-CD1-U | 5095 | 36.2 | 141 |
| 22CZ2-55VHE-UNV-L835-CD1-U | 5530 | 39.4 | 140 |
| 22CZ2-60VHE-UNV-L835-CD1-U | 6110 | 44.1 | 139 |
| 22CZ2-65VHE-UNV-L835-CD1-U | 6559 | 47.9 | 137 |
| 22CZ2-70VHE-UNV-L835-CD1-U | 7017 | 50.3 | 140 |
| 22CZ2-75VHE-UNV-L835-CD1-U | 7557 | 54.7 | 138 |
| 22CZ2-80VHE-UNV-L835-CD1-U | 8092 | 59.1 | 137 |
| 22CZ2-85VHE-UNV-L835-CD1-U | 8615 | 63.6 | 136 |
| 22CZ2-90VHE-UNV-L835-CD1-U | 9125 | 68.2 | 134 |
| 22CZ2-95VHE-UNV-L835-CD1-U | 9610 | 72.7 | 132 |
| 22CZ2-100VHE-UNV-L835-CD1-U | 10108 | 77.7 | 130 |
| 22CZ2-110VHE-UNV-L835-CD1-U | 11065 | 87.7 | 126 |

Shielding

| | Lumen Adjustment Factors | | | | | |
|---|--------------------------|------|------|--|--|--|
| | S | HRP | SQR | | | |
| ſ | 1.05 | 0.80 | 0.96 | | | |

Lumen Calculator

| CCT Multiplier | 80 CRI | 90 CRI ⁽¹⁾ | BioUp Static |
|-------------------|--------|-----------------------|--------------|
| 3000K | 0.965 | 0.827 | - |
| 3500K | 1.000 | 0.847 | 0.912 |
| 4000K | 1.019 | 0.856 | 0.899 |
| 5000K | 1.019 | 0.909 | 0.879 |

 $\textbf{Notes:} \ (1) \ \text{Input} \ \text{wattages for 90 CRI versions may vary. Refer to published IES-format photometry or LM-79 reports for more details.}$

Example of Lumen Adjustment Calculation

22CZ2-32-UNV-L935-CD1-U at 90CRI at 3500K Lumen Adjustment Factor = 0.845 Total Light Output = $3,280 \text{ Im } \times 0.845 = 2,772 \text{ Im}$ Efficacy = $\frac{2,772 \text{ Im}}{26.7W} = 103.8 \text{ Im/W}$

Lumen Maintenance

| Version | TM-21 Lumen Maintenance (60,000 hours) ⁽²⁾ | Theoretical L70 (Hours) ⁽³⁾ |
|----------------------|---|---|
| Standard | > 85% | > 151,000 |
| High Efficiency | > 90% | > 203,000 |
| Very High Efficiency | > 90% | > 203,000 |

Notes: (2) Supported by IES TM-21 standards. (3) Theoretical values represent estimations commonly used; however, refer to the IES position on LED Product Lifetime Prediction, IES PS-10-18, that explains proper use of IES TM-21 and LM-80.

Load Data (Stock Product)

| Thd | 6% |
|-----------------|-------|
| Power Factor | 0.99 |
| Weight (lbs.) | 10.6 |
| Low Temp. Start | -20°C |

Shipping Data

| Catalog No. | Wt. | Pallet 49"L x 52"W x 55"H | | |
|-------------|-----------|------------------------------|--|--|
| 2' x 2' | 12.5 lbs. | 48 | | |

Air Return Volume

| Negative Static Pressure (Inches H ₂ 0) | Return Air Volume (CFM) | | |
|---|----------------------------|--|--|
| 0.05 | 79 | | |
| 0.1 | 112 | | |
| 0.2 | 161 | | |
| 0.25 | 177 | | |
| 0.3 | 198 | | |
| 0.45 | 239 | | |






Control Solutions

- WaveLinx LITE wireless
- · WaveLinx PRO wireless
- · WaveLinx CAT wired
- · WaveLinx Wired



Integrated Sensor Coverage Pattern



Note: Installation of integrated sensors within 3-ft (1m) of HVAC air vents is not recommended. The pattern shown is intended solely as a general guide and is not to scale.

The Cruze ST with WaveLinx offers no-hassle lighting control with multiple luminaire level control solutions




WaveLinx PRO is a wireless lighting control solution, for connected spaces, that significantly reduces a building's energy consumption. From a single floor to an entire campus, WaveLinx PRO connects more than lighting assets; it shares aggregated sensor data with the WaveLinx CORE platform and other building systems, so building owners can improve operations, spaces environment, and tenants' experience. WaveLinx PRO offers a rich portfolio of wireless devices, WaveLinx PRO-enabled luminaires, and an intuitive WaveLinx mobile app for office, education, warehouse, and parking garage applications.



WaveLinx LITE is a cost effective, wireless digital lighting control solution, with out-of-the-box functionality, that saves energy and meets code. It's designed for applications that require occupancy-based, daylighting, or manual light control. Customize installations for office, education, warehouse and parking garages using the secure, simple mobile app.

With Integrated WaveLinx Sensor



Add a hidden WaveLinx sensor node (WPN, WLN) to your space lighting design!

Allows to:

- Keeps luminaire aesthetics
- · Connect fixtures without the realestate to include sensor option such as downlights
- · Connect sealed fixtures without a standard sensor option such as products for clinical space.

| Integrated Controls Options | | | | | | |
|-----------------------------|---------------------------------|---|---|---|---|--|
| Option | Out of the Box Functionality | 3 | | | | |
| WLS | X | x | Х | Х | | |
| WLN | | X | | | | |
| WPS | | X | Х | Х | Х | |
| WPN | _ | X | | | Х | |

Note: *WaveLinx utilizes scenes to allow users to change an area's fixtures Correlated Color Temperature (CCT) and intensity using a commissioned wireless wallstation scene controller. To enable CCT adjustments through WaveLinx, include WPS or WPN devices in addition to VividTune or BioUp technologies for integrated fixture control. WPS with CCT controls the intensity of the fixture; an additional, externally mounted control device is needed to control the CCT. See RSP-P-010-347 The WNPS option is available with WLS or WPS sensors. Must be specified when ordered. Also note that WLS and WPS are also compatible with ESP-L-010-347 and ESP-P-010-347, respectively. Learn more about WaveLinx EM here.

Systems comparison chart

Cooper Lighting Solutions provides many lighting system solutions designed to satisfy code requirements and meet the unique needs of any project.












| • | | | | | |
|-------------------|----------------------------------|---------------------------------------|--------------------------------------|-------------------------------------|--------------------------------|
| | Luminaire with standalone sensor | Standalone Spaces WaveLinx LITE | Standalone Spaces WaveLinx CAT | Networked Spaces WaveLinx PRO | Enterprise WaveLinx CORE |
| Occupancy | Yes | Yes | Yes | Yes | Yes |
| Daylighting | Yes | Yes | Yes | Yes | Yes |
| Wallstations | - | Yes | Yes | Yes | Yes |
| Gateways | - | - | - | 1 WAC | 300 WACs |
| Devices (MAX) | - | 40 per Area (1120 per space) | 40 per Area | 200 per WAC2 | 32,500 per CORE Enterprise |
| Software | - | WaveLinx LITE Mobile App | WaveLinx CAT Mobile App | WaveLinx Mobile App | CORE |
| Areas | - | 28 per Space | Unlimited | 50 per WAC2 | up to 3,000 |
| Zones | - | 16 per Area | 16 per Area | 16 per Area | up to 9,000 |
| Scheduling | - | - | - | Local | Global |
| VividTune™ | - | - | - | Yes | Yes |
| Plug-Load Contro | I - | Yes | Yes | Yes | Yes |
| Low-Voltage Power | er – | - | Yes | Yes | Yes |
| Integration | - | - | - | - | BACnet, API |
| Dashboards | - | - | - | - | Energy, Occupancy |
| Configuration | - | Installer | Installer | Technician | Technician / IT |



22 Cruze ST LED with VividTune Tunable White

VividTune tunable white luminaires from Cooper Lighting Solutions deliver high-quality light in a broad range of continuously variable color temperatures and intensities. Create a dynamic environment by adjusting the ambient light warmer or cooler to influence mood, support the task at hand, or create a dramatic ambience. The ability to control correlated color temperature and intensity separately using simple controls is the next evolution of LED lighting for the commercial, educational, healthcare and hospitality space. The unparalleled flexibility and number of available lighting environments enable users to find the right light with tunable white.



3000K - 5000K 2700K - 6500K


Energy and Performance Data

| Tunable White - Lumen Adjustment Factors | | | | | | |
|--|--------------------------|--------|--------------------------|--------|------------------------------------|---------------------|
| сст | VividTune 3000K-5000K | | VividTune 2700K-6500K | | BioUp Tunable White 2700K-5000K | |
| | 80 CRI | 90 CRI | 80 CRI | 90 CRI | CRI | Lumen Adjustment |
| 2700K | - | - | 0.903 | 0.771 | 95 | 0.938 |
| 3000K | 0.929 | 0.765 | 0.928 | 0.801 | 94 | 0.929 |
| 3500K | 0.983 | 0.836 | 0.961 | 0.842 | 90 | 0.912 |
| 4000K | 1.033 | 0.903 | 0.981 | 0.868 | 87 | 0.899 |
| 4500K | 1.042 | 0.918 | 0.999 | 0.891 | 85 | 0.890 |
| 5000K | 1.042 | 0.918 | 1.013 | 0.909 | 84 | 0.879 |
| 6500K | - | - | 1.028 | 0.933 | - | - |

| 2' x 2' Cruze ST LED - Example of Approximate Lumen Calculation | | | | | | |
|---|-------------------------------|---|----------------------------------|---------------------------------|--|--|
| | Standard Catalog # | VividTune 80 CRI Catalog # VividTune 90 CRI Catalog # | | BioUp Tunable White | | |
| CCT Setting | 22CZ2-34HE-UNV- L835-CD1-U | 22CZ2-34HE-UNV- L83050-W2A1-U | 22CZ2-34HE-UNV- L93050-W2A1-U | 22CZ2-34HE-UNV- B2750-W2A1-U | | |
| 2700K | - | 3058 | 2611 | 3176 | | |
| 3000K | - | 3026 | 2491 | 3146 | | |
| 3500K | 3386 | 3202 | 2722 | 3088 | | |
| 4000K | - | 3362 | 2940 | 3044 | | |
| 4500K | - | 3394 | 2991 | 3014 | | |
| 5000K | - | 3394 | 2991 | 2976 | | |
| 6500K | - | 3481 | 3159 | - | | |

Controlling VividTune and BioUp Tunable White

From wall dimmers to wireless controls, tunable white luminaires are compatible with industry standard 0-10V and DALI controls. One channel to control intensity (brightness) and a second channel to adjust CCT.



Example of Lumen Adjustment Calculation

22CZ2-34HE-UNV-L83050-W2A1-U at 80 CRI tuned to 3500K

Adjusted Lumen = published Im x adjusted Im factor

Adjusted Lumen = 3386×0.946

Adjusted Lumen = 3202 lm

* Lumen adjustment factors are for reference and may be different for each product selected. Refer to IES files for actual performance data on each.

Proven Research. Industry Recognized.











See BioUp brochure for more details



ANSI/IES RP-46-23 / TM18 published March 2024 based on over 40 years of research.

"...circadian clock synchronization is paramount to the body's efficient and appropriate functioning." - TM18



BioUp solutions maximize WELL points for Circadian Lighting Design (L03):



Use BioUp to achieve Equivalent Melanopic Lux (EML) thresholds for circadian design and earn nearly 20% of WELL building lighting points



MDER, M-EDI and EML are key metrics used to quantify nonvisual performance of indoor lighting systems.




See BioUp white paper for more details


MDER - Melanopic Daylight Efficacy Ratio (MDER) measures the amount of light stimulating to the melanopsin receptors.

Standard 4000K LED

MDER = .62



BioUp 4000K LED MDER = .82



30% boost Biological impact

compared to traditional LED sources

| | LED MDER | BioUp Static | | BioUp Dynamic | |
|-------|----------|--------------|-----|---------------|-----|
| ССТ | ~83 CRI | MDER | CRI | MDER | CRI |
| 2700K | 0.44 | - | - | 0.43 | 95 |
| 3000K | 0.49 | - | - | 0.54 | 94 |
| 3500K | 0.56 | 0.71 | 90 | 0.71 | 90 |
| 4000K | 0.64 | 0.84 | 87 | 0.82 | 87 |
| 5000K | 0.77 | 0.98 | 84 | 0.98 | 84 |

BioUp enhances the LED spectrum with cyan light at 475nm increasing the biological impact of the light to enhance our circadian rhythm which regulates our sleep/ wake cycle, daytime engagement, and mood

all without distorting visual color impression.


Static (non-tunable)

Static BioUp is used when simple Melanopic Lighting is desired at all times.

Arrow in graph shows BioUp spectrum boost is at 475nm where nonvisual biological response is enhanced.

Dynamic - (Tunable)

Dynamic BioUp is used when Melanopic Lighting is desired to adjust during the day.



no CCT control needed

Evening **Daytime** MDER = 0.43 MDER = 0.98 Cooler Light With Warmer CCT Without Cvan content Cvan content 2700K - 5000K ССТ Control Dimmina Control > Control with Wavelinx, 2ch 0-10V, or DALI